PHILIPS

LED lighting

REAL PROs REAL QUALITY

Professional LED lighting **catalog**

Discover our wide portfolio of smart and efficient LED lighting solutions for both indoor and outdoor application areas.

May
2020

Why choose Philips
for lighting solutions

An **LED light** for every need,
from the **world leader** in lighting

Best products:

Our LED lighting provides you with:

Unbeatable quality
Industry-leading quality and reliability ensure our lights keep their output and light quality over the full warranted lifetime.

Easy-to-install
The efficient design of the CoreLine fixtures enables replacement of existing lights, with no need for expensive re-wiring or new ceiling configurations. Our LED lamps are compatible with most dimmers and transformers for easy installation, retaining their full specifications and lifetimes for lowest Total Cost of Ownership.

Leading the way
With Philips lighting you get much more than high quality and easy-to-install lighting solutions – you get LED lighting that's setting the reference in the industry. It has never been easier to bring the power of connected lighting to small- and medium-sized enterprises thanks to our Interact Ready range that works seamlessly with the intuitive Interact Pro software.

Best partner:

Close cooperation before, during and after projects is important to us:

"They really managed to satisfy our needs well. They really have cared a lot and showed a lot of commitment..."

Technical consulting and intense customer support:

"Quick and competent responses to questions"

Close cooperation with local wholesalers was a key element of assuring on-time product availability:

"Philips is flexible to offer different delivery options"

Best portfolio:

We offer the right lighting for every application.

Our Philips CoreLine range consists of a full range of luminaire types that offer innovative, high quality and easy-to-install lighting for every project where light really matters. Philips Ledinaire is our essential range of trusted luminaires for everyday lighting jobs that need good performance. And that for a price that's on your side! Our LED tubes offer best in class lighting and ultimate compatibility. And we offer a full range of LED lamps, in any form and shape, that allow you to create the perfect ambience while saving energy.

For the full dimmer and transformer compatibility list, visit:
www.lighting.philips.com/main/products/ledlamps

For our warranty document, visit:
www.lighting.philips.com/main/support/support/warranty.html

Select the right LED luminaire or lamp

A partner that understands the challenges you face, saves you time.
Which is why we offer a comprehensive portfolio of LED luminaires and lamps.
The right product, for every job. For more information and online tools, check:
www.lighting.philips.com/main/support/purchase/installer.

	CorePro	MASTER Value	MASTER	MasterConnect interact ready.
Solution	Simple replacement of fluorescent tubes for average use	Strong performance in demanding applications with intense usage	Best in class performance for very demanding applications	For smart lighting applications with personal/automated light control
Performance				
Price	€ € € € € €	€ € € € € €	€ € € € € €	€ € € € € €
Products	167 types	60 types	132 types	1 type
Life span	30,000	50,000	50,000 - 70.000	50,000 + insight into remaining life span
Warranty	3 years	5 years	5 years	5 years

	Ledinaire	CoreLine	CoreLine Interact Ready interact ready.
Solution	Essential range of trusted products	Suitable for every project where light really matters	For smart lighting applications with personal/automated light control
Performance			
Price	€ € € € € €	€ € € € € €	€ € € € € €
Products	13 types	17 types	6 types
Life span	50,000 L65/L70	50,000 L70/L80	50,000 + insight into remaining life span
Warranty	3 years	5 years	5 years

Contents

6 Interact Ready

7 CoreLine Interact Ready waterproof
8 CoreLine Interact Ready recessed luminaire
9 CoreLine Interact Ready panel
10 CoreLine Interact Ready surface-mounted luminaire
11 CoreLine Interact Ready downlight
11 CoreLine Interact Ready slim downlight
12 CoreLine batten
12 Smart wall-switch
13 Smart sensor
13 Interact Pro - Gateway
14 MASTERConnect Interact Ready LEDtubes

15 CoreLine LED luminaires

16 CoreLine recessed luminaire
18 CoreLine panel
21 CoreLine surface-mounted luminaire
23 CoreLine wall-mounted luminaire
25 CoreLine waterproof
27 CoreLine slim downlight
28 CoreLine downlight
30 CoreLine recessed spot
33 CoreLine projector
34 CoreLine bollard
35 CoreLine highbay
36 CoreLine batten
37 CoreLine trunking
40 CoreLine tempo
43 CoreLine malaga

45 Ledinaire LED luminaires

46 Ledinaire panel
46 Ledinaire recessed and surface-mounted
47 Ledinaire wall-mounted
48 Ledinaire downlight and surface-mounted
49 Ledinaire Zadora LED
50 Ledinaire ClearAccent
50 Ledinaire slim waterproof
51 Ledinaire waterproof
52 Ledinaire floodlight
53 Ledinaire batten
54 Ledinaire Pentura mini LED
54 Ledinaire highbay

55 LED lamps and tubes

57 LED spot GU10
59 LED spot GU5.3
61 LED spot LV AR111
62 LED spot LV MR11
62 LED spot PAR20
63 LED spot PAR30S
63 LED spot PAR30L
64 LED spot PAR38
64 LED spot MV R39
65 LED spot MV R50
65 LED spot MV R63
66 LED spot MV R80
67 LED linear R7S
67 LED capsules LV G4
68 LED capsule MV G9
69 LED bulb & LED stick E27
72 Classic LEDbulb E27
73 Classic LEDbulb ST64
73 Classic LEDbulb spiral
74 A-Shape LED
75 Classic LEDglobe, giant & eyecatchers
76 LED candle
77 Classic LEDcandle
79 Classic LEDluster
81 LED luster
83 LED tubes T8
87 LED tube T5
89 LED tube starter
89 LED PL-C
90 LED PL-L
91 LED PL-S
91 LED tube Circular
94 TrueForce

The future **is connected**

The future starts now, are you ready for it?
Combine Philips Interact Ready lamps and luminaires with Interact Pro software, to create smart lighting systems for your customers.

Philips Interact Ready lighting works with the Interact Pro dashboard and app.

Get connected in **5 simple steps**



1. Unbox



2. Install
Interact Pro gateway and Interact Ready lighting

3. Download
Interact Pro app

4. Configure
system with Interact Pro app

5. Manage
monitor and modify via Interact Pro dashboard

The Interact Pro dashboard and app work with a range of Philips luminaires and lamps and a set of wireless switches and sensors that are Interact Ready.

You can customize the software's settings for specific workspaces. Whether you're connecting 20 light points or 200, Interact Pro helps everyone to work smarter.

Overview of most popular **Interact Ready** lamps and luminaires

Philips Interact Ready lighting

interact ready.

CoreLine
Waterproof Interact Ready

MasterConnect LEDtube T8
Ultra Output

CoreLine SlimDownlight
Interact Ready

CoreLine panel
Interact Ready

CoreLine batten
Interact Ready

works with

Interact Pro software

interact Pro

Interact Pro gateway



Interact Pro app



Interact Pro dashboard

Overview Interact Ready CoreLine products

Now that more and more products are being connected to the internet, they are becoming smarter. This provides more flexibility, saves extra costs and offers more comfort. This means there is an opportunity for the installation sector to be part of the smart lighting on the internet, to offer a better experience for the end user. So far, small and medium-sized enterprises (SMEs) have remained excluded from these developments, but that is now a thing of the past. The luminaires and lamps from the list below are the first Interact Ready LED products and work seamlessly with the intuitive Interact Pro app and dashboard.

CoreLine waterproof

www.philips.com/interact-ready

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT120C G2 LED40S/840 IA1 L1200	30	4000	4000	IP65	39713500
WT120C G2 LED40S/840 IA1 ELB3 L1200	34.5	4000	4000	IP65	39980100
WT120C LED40S/840 IA1 L1200	36.5	4100	4000	IP65	39713500
WT120C G2 LED60S/840 IA1 L1500	45.5	6000	4000	IP65	39714200
WT120C LED60S/840 IA1 L1500	49.5	6000	4000	IP65	39714200
WT120C G2 LED60S/840 IA1 ELB3 L1500	50	6000	4000	IP65	39981800

Overview Interact Ready CoreLine products

CoreLine recessed luminaire – Non Office Compliant (NOC)

www.philips.com/interact-ready

interact ready.

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED37S/840 W60L60 IA1 NOC	35.4	3700	4000	IP20/44	99649200
RC134B LED37S/840 W30L120 IA1 NOC		3700	4000	IP20/44	99653900
RC134B LED37S/830 W30L120 IA1 NOC		3700	3000	IP20/44	99657700
RC134B LED37S/830 W60L60 IA1 NOC		3700	3000	IP20/44	99650800

CoreLine recessed luminaire – Office Compliant (OC)

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED37S/840 W30L120 IA1 OC	35.4	3700	4000	IP20/44	99654600
RC134B LED37S/840 W60L60 IA1 OC		3700	4000	IP20/44	99648500
RC134B LED37S/830 W60L60 IA1 OC		3700	3000	IP20/44	99651500
RC134B LED37S/830 W30L120 IA1 OC		3700	3000	IP20/44	99656000

Overview Interact Ready CoreLine products

CoreLine panel – Non Office Compliant (NOC)

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC132V LED36S/840 W60L60 IA1 NOC	34	3600	4000	IP20/44	38516300
RC132V LED34S/830 W60L60 IA1 NOC		3400	3000	IP20/44	38517000
RC132V LED36S/840 W30L120 IA1 NOC		3600	4000	IP20/44	38519400
RC133V LED36S/840 W62L62 IA1 NOC		3600	4000	IP20/44	38518700
RC132V LED36S/840 W30L120 ELB3 IA1 NOC	36	3600	4000	IP20/44	40134400
RC132V LED36S/840 W60L60 ELB3 IA1 NOC		3600	4000	IP20/44	40133700

CoreLine panel – Office Compliant (OC)

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC132V LED36S/840 W60L60 IA1 OC	34	3600	4000	IP20/44	38520000
RC132V LED34S/830 W60L60 IA1 OC		3400	3000	IP20/44	38521700
RC132V LED36S/840 W30L120 IA1 OC		3600	4000	IP20/44	38523100
RC133V LED36S/840 W62L62 IA1 OC		3600	4000	IP20/44	38522400
RC132V LED36S/840 W30L120 ELB3 IA1 OC	36	3600	4000	IP20/44	40136800
RC132V LED36S/840 W60L60 ELB3 IA1 OC	40	3600	4000	IP20/44	40135100

Overview Interact Ready CoreLine products

CoreLine surface-mounted luminaire – Non Office Compliant (NOC)

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED37S/840 W60L60 IA1 NOC	35.4	3700	4000	IP20	99665200
SM134V LED37S/840 W20L120 IA1 NOC		3700	4000	IP20	99662100
SM134V LED37S/830 W60L60 IA1 NOC		3700	3000	IP20	99668300
SM134V LED37S/830 W20L120 IA1 NOC		3700	3000	IP20	99664500

CoreLine surface-mounted Luminaire – Office Compliant (OC)

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED37S/840 W60L60 IA1 OC	35.4	3700	4000	IP20	99667600
SM134V LED37S/840 W20L120 IA1 OC		3700	4000	IP20	99663800
SM134V LED37S/830 W60L60 IA1 OC		3700	3000	IP20	99669000
SM134V LED37S/830 W20L120 IA1 OC		3700	3000	IP20	99666900

Overview Interact Ready CoreLine products

CoreLine downlight

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN140B LED20S/830 C IA1	22	2200	3000	IP20	32614600
DN140B LED20S/830 WR IA1		2200	3000	IP20	32612200
DN140B LED20S/840 C IA1		2200	4000	IP20	32615300
DN140B LED20S/840 WR IA1		2200	4000	IP20	32613900

CoreLine SlimDownlight

50000h 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN135B LED20S/830 IA1 WH	27	2000	3000	IP44	38922299
DN135B LED20S/840 IA1 WH		2000	4000	IP44	38924699

Interact Ready products

CoreLine batten *

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BN124C LED41S/840 IA1 TW1 L1200	36	4100	4000	IP20	33733399
BN124C LED53S/840 IA1 TW1 L1500	44	5300	4000	IP20	33734099

* Current (Gen 2 – BN124C) portfolio, available until stocks last.

Smart wall-switch

1 PACK

Product Type	EOC code
UID8450/10 ZGP Switch Dim 2B	44931800

Interact Ready products

Smart sensor

10 PACK

Product Type	IP rating	EOC code
OCC Sensor IA CM IP42 WH (only presence detection)	IP42	77752700
OCC-DL SENSOR IA CM IP42 WH (presence + daylight detection)	IP42	77754100

Interact Pro – Gateway

interact Pro

1 PACK

Product Type	EOC code
LCN1840/05 Wireless Gateway EU	77579000

MasterConnect LEDtube

MasterConnect LED tubes are the first LED tubes that are Interact Ready and work seamlessly with the intuitive Interact Pro app and dashboard to bring the power of connected lighting to small and medium-sized enterprises. Sensors and wall switches are interoperable and upgradeable, meaning you are prepared for any changes in the future. Lights can dim or go off automatically when they're not needed. Employees can personalize lighting settings. Business owners can pick up a whole stream of information on how much energy they are using and start saving energy straight away.

MasterConnect LEDtube T8 Ultra Output

50000h 10 PACK

Product Type	LED	Lumen Output	Dimmable	Beam angle	CRI	Color Temp.	EEL	EOC code
	W	lm				K		
MAScon LEDtube IA 1200mm UO 16.5W830 T8	16.5	2300	Wireless Dim	160 °	83	3000	A++	77342000
MAScon LEDtube IA 1200mm UO 16.5W840 T8		2500	Wireless Dim	160 °	83	4000	A++	77344400
MAScon LEDtube IA 1200mm UO 16.5W865 T8		2500	Wireless Dim	160 °	83	6500	A++	77346800
MAScon LEDtube IA 1500mm UO 25.5W830 T8	25.5	3400	Wireless Dim	160 °	83	3000	A++	77348200
MAScon LEDtube IA 1500mm UO 25.5W840 T8		3700	Wireless Dim	160 °	83	4000	A++	77350500
MAScon LEDtube IA 1500mm UO 25.5W865 T8		3700	Wireless Dim	160 °	83	6500	A++	77352900

Philips **CoreLine**

The reference for innovative good quality, easy-to-use lighting solutions for every project where light really matters

Find the **right** solution in our range using the **Selector tool** productfinder.lighting.philips.com

Find out **more** about **all 16** different CoreLine luminaires on **philips.com/coreline**

Now with **5 years** warranty!

Innovative | Easy to install | High Quality

CoreLine **Waterproof**

interact ready.

- New, robust design with improved mechanical and electrical design for a faster and more flexible installation
- Wide-beam light distribution for more effective lighting
- Energy savings (up to 140lm/W) and longer lifetime (50k hrs L75) to reduce operating costs

CoreLine **panel**

interact ready.

- New option: Warm and cool white light, as well as four lumen packages in one luminaire
- New connector and accessory design for simpler and faster installation
- Wieland cable versions available for easy connection
- Color coded labeling for easy type identification

CoreLine **batten**

interact ready.

- Ideal for setting up seamless and aesthetic light-lines creations
- Smart product architecture for tool-free and flexible installation, with through-wiring possibility
- Perfect replacement with different lengths and lumen options
- Optional integrated wireless connectivity (Interact Ready), that works with Interact Pro
- Optionally available: DALI and Emergency Lighting (3h)

CoreLine

Philips CoreLine offers a full range of LED lighting solutions that keeps installation time to a minimum, while saving a maximum of energy. Whether old or new, optimal lighting can transform a building into something truly special and turn it into a place where people enjoy working and living. Give your customers that “wow” moment with Philips CoreLine: the complete range of high quality LED lighting that’s setting the reference in the market. Because when light really matters, you don’t want to take a chance.

CoreLine recessed luminaire

www.philips.com/coreline

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED27S/840 PSD W30L120 OC	22	2700	4000	IP44	34812000
RC134B LED27S/840 PSD W60L60 OC		2700	4000	IP44	34810600
RC134B LED27S/830 PSD W30L120 OC	23	2700	3000	IP44	34816800
RC134B LED27S/830 PSD W60L60 OC		2700	3000	IP44	34814400
RC134B LED27S/840 PSD W30L120 ELB3 OC	25.5	2700	4000	IP44	34837300
RC134B LED27S/840 PSD W60L60 ELB3 OC		2700	4000	IP44	34822900
RC134B LED27S/840 PSD W30L120 NOC	26.5	2700	4000	IP44	34826700
RC134B LED27S/840 PSD W60L60 NOC		2700	4000	IP44	34825000
RC134B LED27S/840 PSU W30L120 NOC	27	2700	4000	IP44	34824300
RC134B LED27S/840 PSU W60L60 NOC		2700	4000	IP44	34823600
RC134B LED27S/830 PSU W30L120 NOC	28.5	2700	3000	IP44	34797000
RC134B LED27S/830 PSU W60L60 NOC		2700	3000	IP44	34795600
RC134B LED27S/830 PSD W30L120 NOC	30.5	2700	3000	IP44	34803800
RC134B LED27S/830 PSD W60L60 NOC		2700	3000	IP44	34801400
RC134B LED27S/840 PSD W30L120 ELB3 NOC		2700	4000	IP44	34835900
RC134B LED27S/840 PSD W60L60 ELB3 NOC		2700	4000	IP44	34828100
RC134B LED27S/840 PSU W30L120 ELB3 NOC		2700	4000	IP44	34833500
RC134B LED27S/840 PSU W60L60 ELB3 NOC		2700	4000	IP44	34827400
RC134B LED37S/840 PSU W30L120 OC		3700	4000	IP44	34830400
RC134B LED37S/840 PSU W60L60 OC		3700	4000	IP44	34829800
RC134B LED37S/830 PSD W30L120 OC	31.5	3700	3000	IP44	34815100
RC134B LED37S/830 PSD W60L60 OC		3700	3000	IP44	34813700
RC134B LED37S/840 PSD W30L120 OC		3700	4000	IP44	34811300
RC134B LED37S/840 PSD W60L60 OC		3700	4000	IP44	34804500
RC135B LED37S/840 PSD W62L62 OC		3700	4000	IP44	34845800
RC134B LED27S/830 PSU W30L120 ELB3 NOC	32	2700	3000	IP44	34839700

CoreLine

CoreLine recessed luminaire – Continued

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC134B LED27S/830 PSD W30L120 ELB3 NOC	34	2700	3000	IP44	34841000
RC134B LED37S/830 PSU W30L120 NOC		3700	3000	IP44	34796300
RC134B LED37S/830 PSU W60L60 NOC		3700	3000	IP44	34794900
RC134B LED37S/840 PSU W30L120 NOC		3700	4000	IP44	34818200
RC134B LED37S/840 PSU W60L60 NOC		3700	4000	IP44	34817500
RC134B LED37S/830 PSU W30L120 OC	34.5	3700	3000	IP44	34832800
RC134B LED37S/830 PSU W60L60 OC		3700	3000	IP44	34831100
RC134B LED37S/830 PSD W30L120 ELB3 OC	35	3700	3000	IP44	34843400
RC134B LED37S/840 PSD W30L120 ELB3 OC		3700	4000	IP44	34838000
RC134B LED37S/840 PSD W60L60 ELB3 OC		3700	4000	IP44	34821200
RC135B LED37S/840 W62L62 IA1 NOC	35.4	3700	4000	IP20/44	99655300
RC135B LED37S/840 W62L62 IA1 OC		3700	4000	IP20/44	99652200
RC134B LED37S/830 PSD W30L120 NOC	35.5	3700	3000	IP44	34802100
RC134B LED37S/830 PSD W60L60 NOC		3700	3000	IP44	34800700
RC134B LED37S/840 PSD W30L120 ELB3 NOC		3700	4000	IP44	34836600
RC134B LED37S/840 PSD W30L120 NOC		3700	4000	IP44	34799400
RC134B LED37S/840 PSD W60L60 NOC		3700	4000	IP44	34798700
RC135B LED37S/840 PSD W62L62 NOC		3700	4000	IP44	34850200
RC134B LED37S/830 PSU W30L120 ELB3 NOC	38	3700	3000	IP44	34840300
RC134B LED37S/840 PSU W30L120 ELB3 NOC		3700	4000	IP44	34834200
RC134B LED37S/840 PSU W60L60 ELB3 NOC		3700	4000	IP44	34819900
RC134B LED37S/830 PSD W30L120 ELB3 NOC	39	3700	3000	IP44	34842700
RC134B LED37S/840 PSD W60L60 ELB3 NOC		3700	4000	IP44	34820500

CoreLine

CoreLine recessed luminaire – Accessories

1 PACK

Product Type	EOC code
RC134Z CFRM-PLC WH W60L60	98722300
RC134Z CFRM-PLC WH W30L120	98724700

CoreLine panel – Non Office Compliant (NOC)

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC132V G4 LED36S/840 PSU W60L60 NOC		3600	4000	IP20/44	36035500
RC133V G4 LED36S/840 PSU W62L62 NOC		3600	4000	IP20/44	36038600
RC133V G4 LED34S/830 PSU W62L62 NOC	29	3400	3000	IP20/44	36039300
RC132V G4 LED34S/830 PSU W60L60 NOC		3400	3000	IP20/44	36036200
RC132V G4 LED36S/840 PSU W30L120 NOC		3600	4000	IP20/44	36040900
RC132V G4 LED43S/840 PSU W60L60 NOC	34.5	4300	4000	IP20/44	36037900

CoreLine

CoreLine panel – Office Compliant (OC)

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC133V G4 LED36S/840 PSD W62L62 OC	29	3600	4000	IP20/44	36048500
RC132V G4 LED34S/830 PSD W30L120 OC		3400	3000	IP20/44	36052200
RC132V G4 LED36S/840 PSU W30L120 OC		3600	4000	IP20/44	36044700
RC133V G4 LED36S/840 PSU W62L62 OC		3600	4000	IP20/44	36043000
RC132V G4 LED34S/830 PSD W60L60 OC		3400	3000	IP20/44	36046100
RC132V G4 LED36/840 PSU W60L60 OC TP(a)		3600	4000	IP20/44	36053900
RC133V G4 LED34S/830 PSD W62L62 OC		3400	3000	IP20/44	36049200
RC132V G4 LED34S/830 PSU W60L60 OC		3400	3000	IP20/44	36042300
RC132V G4 LED36S/840 PSD W60L60 OC		3600	4000	IP20/44	36045400
RC132V G4 LED36S/840 PSU W60L60 OC		3600	4000	IP20/44	36041600
RC132V G4 LED36S/840 PSD W30L120 OC		3600	4000	IP20/44	36051500
RC132V G4LED34_43S/830_840 PSU W60L60 OC	30 ~ 35	3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36054600
RC133V G4LED34_43S/830_840 PSU W62L62 OC		3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36055300
RC132V G4LED34_43S/830_840 PSUW30L120 OC		3400, 3600, 4000, 4300	3000 and 4000	IP20/44	36056000
RC132V G4 LED36/840 PSU W60L60 OC TP(a)E	32	3600	4000	IP20/44	96722200
RC132V G4 LED36S/840 PSU W30L120 OC ELB3		3600	4000	IP20/44	96714700
RC132V G4 LED36S/840 PSU W60L60 OC ELB3		3600	4000	IP20/44	96711600
RC132V G4 LED36S/840 PSD W30L120 OC ELB3		3600	4000	IP20/44	96715400
RC132V G4 LED36S/840 PSD W60L60 OC ELB3		3600	4000	IP20/44	96710900
RC133V G4 LED43S/840 PSD W62L62 OC	34.5	4300	4000	IP20/44	36050800
RC132V G4 LED43S/840 PSD W60L60 OC		4300	4000	IP20/44	36047800
RC132V G4 LED43S/840 PSD W60L60 OC ELB3	38	4300	4000	IP20/44	96719200

CoreLine

CoreLine panel – Accessories

1 PACK

Product Type	EOC code
RC132Z SC - safety cable	36268799
RC132Z SME-3 WH Suspension set for 3 core wires for PSU luminaire	36270099
RC132Z SME-4 WH Suspension set with 4 core wires for PSD (dali) luminaires	36271799
RC132Z SMB W60L60 Surface Mounted Bracket	07330899
RC133Z SMB W62L62 Surface Mounted Bracket	07331599
RC132Z SMB W30L120 Surface Mounted Bracket	07332299
RC132Z SMB-PLC Plaster Ceiling Bracket	36269499

CoreLine

CoreLine surface-mounted luminaire – Non Office Compliant (NOC)

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED27S/840 PSD W60L60 NOC	26.5	2700	4000	IP20	34877900
SM134V LED27S/840 PSD W20L120 NOC		2700	4000	IP20	34878600
SM134V LED27S/840 PSU W60L60 NOC	27	2700	4000	IP20	34875500
SM134V LED27S/840 PSU W20L120 NOC		2700	4000	IP20	34876200
SM134V LED27S/830 PSU W60L60 NOC	28.5	2700	3000	IP20	34852600
SM134V LED27S/830 PSU W20L120 NOC		2700	3000	IP20	34854000
SM134V LED27S/830 PSD W60L60 NOC	30.5	2700	3000	IP20	34858800
SM134V LED27S/830 PSD W20L120 NOC		2700	3000	IP20	34860100
SM134V LED27S/840 PSU W60L60 ELB3 NOC		2700	4000	IP20	34879300
SM134V LED27S/840 PSD W60L60 ELB3 NOC		2700	4000	IP20	34880900
SM134V LED27S/840 PSU W20L120 ELB3 NOC		2700	4000	IP20	34885400
SM134V LED27S/840 PSD W20L120 ELB3 NOC		2700	4000	IP20	34887800
SM134V LED27S/830 PSU W20L120 ELB3 NOC	32	2700	3000	IP20	34891500
SM134V LED37S/830 PSU W60L60 NOC	34	3700	3000	IP20	34851900
SM134V LED37S/830 PSU W20L120 NOC		3700	3000	IP20	34853300
SM134V LED37S/840 PSU W60L60 NOC		3700	4000	IP20	34869400
SM134V LED37S/840 PSU W20L120 NOC		3700	4000	IP20	34870000
SM134V LED27S/830 PSD W20L120 ELB3 NOC		2700	3000	IP20	34893900
SM134V LED37S/840 PSD W60L60 NOC	35.5	3700	4000	IP20	34855700
SM134V LED37S/840 PSD W20L120 NOC		3700	4000	IP20	34856400
SM134V LED37S/830 PSD W60L60 NOC		3700	3000	IP20	34857100
SM134V LED37S/830 PSD W20L120 NOC		3700	3000	IP20	34859500
SM134V LED37S/840 PSD W20L120 ELB3 NOC		3700	4000	IP20	34888500
SM134V LED37S/840 PSU W60L60 ELB3 NOC	38	3700	4000	IP20	34871700
SM134V LED37S/840 PSU W20L120 ELB3 NOC		3700	4000	IP20	34886100
SM134V LED37S/830 PSU W20L120 ELB3 NOC		3700	3000	IP20	34892200
SM134V LED37S/840 PSD W60L60 ELB3 NOC	39	3700	4000	IP20	34872400
SM134V LED37S/830 PSD W20L120 ELB3 NOC		3700	3000	IP20	34894600

CoreLine

CoreLine surface-mounted luminaire – Office Compliant (OC)

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
SM134V LED27S/840 PSD W60L60 OC	22	2700	4000	IP20	34862500
SM134V LED27S/840 PSD W20L120 OC		2700	4000	IP20	34864900
SM134V LED27S/830 PSD W60L60 OC	23	2700	3000	IP20	34866300
SM134V LED27S/830 PSD W20L120 OC		2700	3000	IP20	34868700
SM134V LED27S/840 PSD W60L60 ELB3 OC	25.5	2700	4000	IP20	34874800
SM134V LED27S/840 PSD W20L120 ELB3 OC		2700	4000	IP20	34889200
SM134V LED37S/840 PSU W60L60 OC	30.5	3700	4000	IP20	34881600
SM134V LED37S/840 PSU W20L120 OC		3700	4000	IP20	34882300
SM134V LED37S/840 PSD W60L60 OC	31.5	3700	4000	IP20	34861800
SM134V LED37S/840 PSD W20L120 OC		3700	4000	IP20	34863200
SM134V LED37S/830 PSD W60L60 OC		3700	3000	IP20	34865600
SM134V LED37S/830 PSD W20L120 OC		3700	3000	IP20	34867000
SM134V LED37S/830 PSU W60L60 OC	34.5	3700	3000	IP20	34883000
SM134V LED37S/830 PSU W20L120 OC		3700	3000	IP20	34884700
SM134V LED37S/840 PSD W60L60 ELB3 OC	35	3700	4000	IP20	34873100
SM134V LED37S/840 PSD W20L120 ELB3 OC		3700	4000	IP20	34890800

CoreLine

CoreLine surface-mounted luminaire – Accessories

1 PACK

Product Type	IP rating	EOC code
SM134Z SME-3	IP20	34897700
SM134Z SME-5	IP20	34895300
SM134Z SMS	IP20	34896000

CoreLine wall-mounted luminaire

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WL130V LED12S/830 PSU WH	12	1200	3000	IP65	38778599
WL130V LED12S/840 PSU WH		1200	4000	IP65	38779299
WL131V LED12S/830 PSED EL3 WH		1200	3000	IP65	40268600
WL131V LED12S/830 PSR EL3 MDU WH		1200	3000	IP65	40282200
WL131V LED12S/840 PSED EL3 WH		1200	4000	IP65	40269300
WL131V LED12S/840 PSR EL3 MDU WH		1200	4000	IP65	40283900
WL131V LED12S/830 PSED WH	13	1200	3000	IP65	38792199
WL131V LED12S/840 PSED WH		1200	4000	IP65	38793899
WL131V LED12S/830 PSR MDU WH	15	1200	3000	IP65	38786099
WL131V LED12S/840 PSR MDU WH		1200	4000	IP65	38787799

CoreLine

CoreLine wall-mounted luminaire – Continued

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WL131V LED12S/830 PSED WH	13	1200	3000	IP65	38792199
WL131V LED12S/840 PSED WH		1200	4000	IP65	38793899
WL131V LED12S/830 PSR MDU WH	15	1200	3000	IP65	38786099
WL131V LED12S/840 PSR MDU WH		1200	4000	IP65	38787799
WL130V LED20S/830 PSU WH	22	2000	3000	IP65	38780899
WL130V LED20S/840 PSU WH		2000	4000	IP65	38781599
WL131V LED20S/830 PSED EL3 WH		2000	3000	IP65	40270900
WL131V LED20S/830 PSR EL3 MDU WH		2000	3000	IP65	40284600
WL131V LED20S/840 PSED EL3 WH		2000	4000	IP65	40271600
WL131V LED20S/840 PSR EL3 MDU WH		2000	4000	IP65	40285300
WL130V LED20S/830 PSU MDU WH	23	2000	3000	IP65	38782299
WL130V LED20S/840 PSU MDU WH		2000	4000	IP65	38783999
WL131V LED20S/830 PSED WH		2000	3000	IP65	38794599
WL131V LED20S/840 PSED WH		2000	4000	IP65	38795299
WL131V LED20S/830 PSR MDU WH	25	2000	3000	IP65	38788499
WL131V LED20S/840 PSR MDU WH		2000	4000	IP65	38789199
WL131V LED34S/830 PSED EL3 WH	36	3400	3000	IP65	40274700
WL131V LED34S/830 PSED WH		3400	3000	IP65	40272300
WL131V LED34S/830 PSR EL3 MDU WH		3400	3000	IP65	40286000
WL131V LED34S/830 PSU WH		3400	3000	IP65	38784699
WL131V LED34S/840 PSED EL3 WH		3400	4000	IP65	40275400
WL131V LED34S/840 PSED WH		3400	4000	IP65	40273000
WL131V LED34S/840 PSR EL3 MDU WH		3400	4000	IP65	40287700
WL131V LED34S/840 PSU WH		3400	4000	IP65	38785399
WL131V LED34S/830 PSR MDU WH	38	2000	3000	IP65	38790799
WL131V LED34S/840 PSR MDU WH		2000	4000	IP65	38791499

CoreLine

CoreLine waterproof

IK08 | 5 J vandal-protected

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT120C G2 LED19S/840 PSU L600	15	1900	4000	IP65	84045900
WT120C G2 LED18S/840 PSU PCO L600		1800	4000	IP65	34976399
WT120C G2 LED19S/840 PSU MDU L600	16	1900	4000	IP65	96244900
WT120C G2 LED19S/840 PSD L600		1900	4000	IP65	88306800
WT120C G2 LED27S/840 PSU L1200	20.5	2700	4000	IP65	84046600
WT120C G2 LED25S/840 PSU PCO L1200		2500	4000	IP65	34977099
WT120C G2 LED27S/840 PSU TW3 L1200	21	2700	4000	IP65	91685800
WT120C G2 LED27S/840 PSU MDU TW3 L1200	22	2700	4000	IP65	96249400
WT120C G2 LED27S/840 PSU MDU L1200		2700	4000	IP65	96248700
WT120C G2 LED27S/840 PSD L1200		2700	4000	IP65	88307500
WT120C G2 LED34S/840 PSU L1500	24.3	3400	4000	IP65	84047300
WT120C G2 LED31S/840 PSU PCO L1500		3100	4000	IP65	34978799
WT120C G2 LED34S/840 PSD L1500	25.5	3400	4000	IP65	88308200
WT120C G2 LED34S/840 PSU TW3 L1500		3400	4000	IP65	91686500
WT120C G2 LED27S/840 PSU ELB3 L1200	26	2700	4000	IP65	85418000
WT120C G2 LED34S/840 PSU MDU TW3 L1500	26.5	3400	4000	IP65	96268500
WT120C G2 LED34S/840 PSU MDU L1500		3400	4000	IP65	96267800
WT120C G2 LED27S/840 PSD ELB3 L1200	27	2700	4000	IP65	88311200
WT120C G2 LED27S/840 PSU MDU ELB3 L1200	28	2700	4000	IP65	96251700
WT120C G2 LED40S/840 PSU L1200	28.6	4000	4000	IP65	84048000
WT120C G2 LED37S/840 PSU PCO L1200		3700	4000	IP65	34979499
WT120C G2 LED40S/840 PSU TW1 WEC L1200	30	4000	4000	IP65	16317400
WT120C G2 LED40S/840 PSU WEC L1200		4000	4000	IP65	16316700
WT120C G2 LED40S/840 PSD L1200		4000	4000	IP65	88309900
WT120C G2 LED40S/840 PSU TW3 L1200		4000	4000	IP65	91687200
WT120C G2 LED34S/840 PSU ELB3 L1500	30.5	3400	4000	IP65	85420300

CoreLine

CoreLine waterproof – Continued

IK08 | 5 J vandal-protected

L75 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT120C G2 LED34S/840 PSD ELB3 L1500	30.5	3400	4000	IP65	88313600
WT120C G2 LED40S/840 PSU MDU TW3 L1200	31	4000	4000	IP65	96257900
WT120C G2 LED40S/840 PSU MDU L1200		4000	4000	IP65	96256200
WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31.5	3400	4000	IP65	96271500
WT120C G2 LED40S/840 PSD ELB3 L1200	35	4000	4000	IP65	88312900
WT120C G2 LED40S/840 PSU ELB3 L1200		4000	4000	IP65	85419700
WT120C G2 LED40S/840 PSU MDU ELB3 L1200	36	4000	4000	IP65	96263000
WT120C G2 LED60S/840 PSU L1500	42.9	6000	4000	IP65	84049700
WT120C G2 LED57S/840 PSU PCO L1500		5700	4000	IP65	34980099
WT120C G2 LED60S/840 PSU WEC L1500	45	6000	4000	IP65	16318100
WT120C G2 LED60S/840 PSU TW1 WEC L1500		6000	4000	IP65	16319800
WT120C G2 LED60S/840 PSU TW3 L1500		6000	4000	IP65	91688900
WT120C G2 LED60S/840 PSD L1500		6000	4000	IP65	88310500
WT120C G2 LED60S/840 PSU MDU L1500	46	6000	4000	IP65	96275300
WT120C G2 LED60S/840 PSU MDU TW3 L1500		6000	4000	IP65	96276000
WT120C G2 LED60S/840 PSU ELB3 L1500	50	6000	4000	IP65	85421000
WT120C G2 LED60S/840 PSU MDU ELB3 L1500	51	6000	4000	IP65	96282100
WT120C G2 LED60S/840 PSD ELB3 L1500		6000	4000	IP65	88314300
WT120C G2 LED80S/840 PSU L1500	57.1	8000	4000	IP65	40928900
WT120C G2 LED75S/840 PSU PCO L1500		7500	4000	IP65	34981799
WT120C G2 LED80S/840 PSU TW3 L1500	61	8000	4000	IP65	40930200
WT120C G2 LED80S/840 PSD L1500		8000	4000	IP65	40929600
WT120C G2 LED80S/840 PSU MDU L1500		8000	4000	IP65	96286900
WT120C G2 LED80S/840 PSU L1500 ELB3	66	8000	4000	IP65	40931900

CoreLine

CoreLine slim downlight

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
Coreline SlimDownlight Recessed					
DN145B LED6S/830 PSU II WH	6.5	650	3000	IP20/44	33945099
DN145B LED6S/840 PSU II WH		650	4000	IP20/44	33946799
DN145B LED10S/830 PSU II WH	11	1100	3000	IP20/44	33947499
DN145B LED10S/840 PSU II WH		1100	4000	IP20/44	33948199
DN145B LED10S/830 PSD-E II WH	13	1100	3000	IP20/44	96100899
DN145B LED10S/840 PSD-E II WH		1100	4000	IP20/44	96101599
DN145B LED20S/830 PSU II WH	21	2100	3000	IP20/44	33949899
DN145B LED20S/840 PSU II WH		2100	4000	IP20/44	33950499
DN145B LED20S/830 PSD-E II WH	22.5	2100	3000	IP20/44	96102299
DN145B LED20S/840 PSD-E II WH		2100	4000	IP20/44	96103999

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
Coreline SlimDownlight Surface Mounted					
DN145C LED10S/830 PSU II WH	11	1100	3000	IP44	33951199
DN145C LED10S/840 PSU II WH		1100	4000	IP44	33952899
DN145C LED20S/830 PSU II WH	21	2100	3000	IP44	33953599
DN145C LED20S/840 PSU II WH		2100	4000	IP44	33954299

CoreLine

CoreLine downlight

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN140B LED10S/830 PSU C IP54 PI6	9.5	1100	3000	IP20/54	32604700
DN140B LED10S/830 PSU C PI6		1100	3000	IP20	32588000
DN140B LED10S/830 PSU WR IP54 PI6		1100	3000	IP20/54	32596500
DN140B LED10S/830 PSU WR PI6		1100	3000	IP20	32580400
DN140B LED10S/840 PSU C IP54 PI6		1100	4000	IP20/54	32605400
DN140B LED10S/840 PSU C PI6		1100	4000	IP20	32589700
DN140B LED10S/840 PSU WR IP54 PI6		1100	4000	IP20/54	32597200
DN140B LED10S/840 PSU WR PI6		1100	4000	IP20	32581100
DN140B LED10S/830 PSD-E C IP54	11.5	1100	3000	IP20/54	32606100
DN140B LED10S/830 PSD-E WR IP54		1100	3000	IP20/54	32598900
DN140B LED10S/840 PSD-E C IP54		1100	4000	IP20/54	32607800
DN140B LED10S/840 PSD-E WR IP54		1100	4000	IP20/54	32599600
DN140B LED10S/840 PSD-E C ELB3	14.5	1100	4000	IP20	32836200
DN140B LED10S/830 PSD-E C ELB3		1100	3000	IP20	32835500
DN140B LED10S/830 PSD-E WR ELB3		1100	3000	IP20	32831700
DN140B LED10S/840 PSD-E WR ELB3		1100	4000	IP20	32832400
DN140B LED20S/830 PSU C IP54 PI6	19	2200	3000	IP20/54	32608500
DN140B LED20S/830 PSU C PI6		2200	3000	IP20	32592700
DN140B LED20S/830 PSU WR IP54 PI6		2200	3000	IP20/54	32600900
DN140B LED20S/830 PSU WR PI6		2200	3000	IP20	32584200
DN140B LED20S/840 PSU C IP54 PI6		2200	4000	IP20/54	32609200
DN140B LED20S/840 PSU C PI6		2200	4000	IP20	32593400
DN140B LED20S/840 PSU WR IP54 PI6		2200	4000	IP20/54	32601600
DN140B LED20S/840 PSU WR PI6		2200	4000	IP20	32585900

CoreLine

CoreLine downlight – Continued

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
DN140B LED20S/830 PSD-E C IP54	20.5	2200	3000	IP20/54	32610800
DN140B LED20S/830 PSD-E WR IP54		2200	3000	IP20/54	32602300
DN140B LED20S/840 PSD-E C IP54		2200	4000	IP20/54	32611500
DN140B LED20S/840 PSD-E WR IP54		2200	4000	IP20/54	32603000
DN140B LED20S/830 PSD-E C ELB3	23.5	2200	3000	IP20	32837900
DN140B LED20S/830 PSD-E WR ELB3		2200	3000	IP20	32833100
DN140B LED20S/840 PSD-E C ELB3		2200	4000	IP20	32838600
DN140B LED20S/840 PSD-E WR ELB3		2200	4000	IP20	32834800

CoreLine

CoreLine recessed spot

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RS140B LED6-32-/827 PSR PI6 ALU	8	650	2700	IP65	38287299
RS140B LED6-32-/827 PSR PI6 WH		650	2700	IP65	38277399
RS140B LED6-32-/830 PSR PI6 ALU		650	3000	IP65	38288999
RS140B LED6-32-/830 PSR PI6 WH		650	3000	IP65	38278099
RS140B LED6-32-/840 PSR PI6 ALU		650	4000	IP65	38289699
RS140B LED6-32-/840 PSR PI6 WH		650	4000	IP65	38279799
RS141B LED6-32-/827 PSR PI6 ALU		650	2700	IP44	38290299
RS141B LED6-32-/827 PSR PI6 WH		650	2700	IP44	38280399
RS141B LED6-32-/830 PSR PI6 ALU		650	3000	IP44	38291999
RS141B LED6-32-/830 PSR PI6 WH		650	3000	IP44	38281099
RS141B LED6-32-/840 PSR PI6 ALU		650	4000	IP44	38292699
RS141B LED6-32-/840 PSR PI6 WH		650	4000	IP44	38282799
RS142B LED6-32-/827 PSR PI6 WH FR		650	2700	IP44	38417399
RS142B LED6-32-/830 PSR PI6 WH FR		650	3000	IP44	38418099
RS140B LED9-32-/830 PSR PI6 ALU	11	900	3000	IP65	38293399
RS140B LED9-32-/830 PSR PI6 WH		900	3000	IP65	38285899
RS140B LED9-32-/840 PSR PI6 ALU		900	4000	IP65	38294099
RS140B LED9-32-/840 PSR PI6 WH		900	4000	IP65	38286599
RS141B LED9-32-/830 PSR PI6 WH		900	3000	IP44	38283499
RS141B LED9-32-/840 PSR PI6 WH		900	4000	IP44	38284199
RS140B LED12-36-/830 PSR PI6 ALU	15	1200	3000	IP65	38423499
RS140B LED12-36-/830 PSR PI6 WH		1200	3000	IP65	38421099
RS140B LED12-36-/840 PSR PI6 ALU		1200	4000	IP65	38424199
RS140B LED12-36-/840 PSR PI6 WH		1200	4000	IP65	38422799
RS141B LED12-36-/830 PSR PI6 WH		1200	3000	IP44	38419799
RS141B LED12-36-/840 PSR PI6 WH		1200	4000	IP44	38420399

CoreLine

CoreLine recessed spot – Accessories

1 PACK

Product Type	IP rating	EOC code
1 Grid light		
RS143Z CFRM GRID 1x1 WH	IP20	38832499
RS143Z CFRM GRID 1x3 WH	IP20	38834899
RS143Z CFRM GRID 1x2 WH	IP20	38833199
2 LED Module		
RS140Z MODULE LED6-32-/827		38295799
RS140Z MODULE LED9-32-/830		38296499
RS140Z MODULE LED6-32-/840		38297199
RS140Z MODULE LED6-32-/830		38298899
RS140Z MODULE LED9-32-/840		38299599
3 Round rim black		
RS140Z CFRM RND-ADJUST D80 BK		38448799
4 Square rim white		
RS140Z CFRM SQR-ADJUST WH		38456299
5 Square rim aluminum		
RS140Z CFRM SQR-ADJUST ALU		38458699
6 Square darklight		
RS140Z CFRM SQR-FIX Darklight		38508899

CoreLine

CoreLine recessed spot

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RS140B LED6-32-/827 PSR PI6 ALU	8	650	2700	IP65	38287299
RS140B LED6-32-/827 PSR PI6 WH		650	2700	IP65	38277399
RS140B LED6-32-/830 PSR PI6 ALU		650	3000	IP65	38288999
RS140B LED6-32-/830 PSR PI6 WH		650	3000	IP65	38278099
RS140B LED6-32-/840 PSR PI6 ALU		650	4000	IP65	38289699
RS140B LED6-32-/840 PSR PI6 WH		650	4000	IP65	38279799
RS141B LED6-32-/827 PSR PI6 ALU		650	2700	IP44	38290299
RS141B LED6-32-/827 PSR PI6 WH		650	2700	IP44	38280399
RS141B LED6-32-/830 PSR PI6 ALU		650	3000	IP44	38291999
RS141B LED6-32-/830 PSR PI6 WH		650	3000	IP44	38281099
RS141B LED6-32-/840 PSR PI6 ALU		650	4000	IP44	38292699
RS141B LED6-32-/840 PSR PI6 WH		650	4000	IP44	38282799
RS142B LED6-32-/827 PSR PI6 WH FR		650	2700	IP44	38417399
RS142B LED6-32-/830 PSR PI6 WH FR		650	3000	IP44	38418099
RS140B LED9-32-/830 PSR PI6 ALU	11	900	3000	IP65	38293399
RS140B LED9-32-/830 PSR PI6 WH		900	3000	IP65	38285899
RS140B LED9-32-/840 PSR PI6 ALU		900	4000	IP65	38294099
RS140B LED9-32-/840 PSR PI6 WH		900	4000	IP65	38286599
RS141B LED9-32-/830 PSR PI6 WH		900	3000	IP44	38283499
RS141B LED9-32-/840 PSR PI6 WH		900	4000	IP44	38284199
RS140B LED12-36-/830 PSR PI6 ALU	15	1200	3000	IP65	38423499
RS140B LED12-36-/830 PSR PI6 WH		1200	3000	IP65	38421099
RS140B LED12-36-/840 PSR PI6 ALU		1200	4000	IP65	38424199
RS140B LED12-36-/840 PSR PI6 WH		1200	4000	IP65	38422799
RS141B LED12-36-/830 PSR PI6 WH		1200	3000	IP44	38419799
RS141B LED12-36-/840 PSR PI6 WH		1200	4000	IP44	38420399

CoreLine

CoreLine grid light – Accessories

1 PACK

Product Type	IP rating	EOC code
RS143Z CFRM GRID 1x1 WH	IP20	38832499
RS143Z CFRM GRID 1x3 WH	IP20	38834899
RS143Z CFRM GRID 1x2 WH	IP20	38833199

CoreLine projector

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
ST150T LED22S-23-/830 PSU BK	24	2200	3000	IP20	79067799
ST150T LED22S-23-/840 PSU BK		2200	4000	IP20	79068499
ST150T LED22S-23-/830 PSU WH		2200	3000	IP20	79069199
ST150T LED22S-23-/840 PSU WH		2200	4000	IP20	79070799
ST150T LED22S-36-/830 PSU BK		2200	3000	IP20	79071499
ST150T LED22S-36-/830 PSU WH		2200	3000	IP20	79073899
ST150T LED22S-36-/840 PSU BK		2200	4000	IP20	79072199
ST150T LED22S-36-/840 PSU WH		2200	4000	IP20	79074599

CoreLine

CoreLine bollard

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BCP155 LED100/NW PSU 220-240V S 7043	12	1000	4000	IP65	38378700
BCP155 LED100/WW PSU 220-240V S 7043		1000	3000	IP65	38377000
BCP155 LED100/NW PSU 220-240V A 7043	13	1000	4000	IP65	38376300
BCP155 LED100/WW PSU 220-240V A 7043		1000	3000	IP65	38375600

CoreLine bollard – Accessories

1 PACK

Product Type	EOC code
ZCP150 ANB L500	38379400

CoreLine

CoreLine highbay

L80 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BY120P G4 LED100S/840 PSU NB	69	10000	4000	IP65	33571100
BY120P G4 LED100S/840 PSU WB		10000	4000	IP65	33570400
BY120P G4 LED100S/865 PSU NB		10000	6500	IP65	33567400
BY120P G4 LED100S/865 PSU WB		10000	6500	IP65	33566700
BY120P G4 LED100S/840 PSD NB	73	10000	4000	IP65	33702900
BY120P G4 LED100S/840 PSD WB		10000	4000	IP65	33703600
BY120P G4 LED100S/865 PSD NB		10000	6500	IP65	33704300
BY120P G4 LED100S/865 PSD WB		10000	6500	IP65	33705000
BY121P G4 LED200S/840 PSU NB	138	20000	4000	IP65	33569800
BY121P G4 LED200S/840 PSU WB		20000	4000	IP65	33568100
BY121P G4 LED200S/865 PSU NB		20000	6500	IP65	33565000
BY121P G4 LED200S/865 PSU WB		20000	6500	IP65	33564300
BY121P G4 LED200S/840 PSD NB	146	20000	4000	IP65	33698500
BY121P G4 LED200S/840 PSD WB		20000	4000	IP65	33699200
BY121P G4 LED200S/865 PSD NB		20000	6500	IP65	33700500
BY121P G4 LED200S/865 PSD WB		20000	6500	IP65	33701200
BY122P G4 LED250S/840 PSU NB	172	25000	4000	IP65	33664000
BY122P G4 LED250S/840 PSU WB		25000	4000	IP65	33665700
BY122P G4 LED250S/865 PSU NB		25000	6500	IP65	33666400
BY122P G4 LED250S/865 PSU WB		25000	6500	IP65	33667100
BY122P G4 LED250S/840 PSD NB	183	25000	4000	IP65	33879800
BY122P G4 LED250S/840 PSD WB		25000	4000	IP65	33880400
BY122P G4 LED250S/865 PSD NB		25000	6500	IP65	33881100
BY122P G4 LED250S/865 PSD WB		25000	6500	IP65	33882800

CoreLine

CoreLine batten

L70 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BN126C LED20S/830 PSU TW1 L600	17	2000	3000	IP20	911401897080
BN126C LED22S/840 PSU TW1 L600		2200	4000	IP20	911401896980
BN126C LED23S/830 PSU TW1 L1200	18	2300	3000	IP20	911401897280
BN126C LED25S/840 PSU TW1 L1200		2500	4000	IP20	911401897180
BN126C LED38S/830 PSU TW1 L1200	31	3800	3000	IP20	911401897480
BN126C LED41S/840 PSU TW1 L1200		4100	4000	IP20	911401897380
BN126C LED60S/830 PSU TW1 L1200	49	6000	3000	IP20	911401897680
BN126C LED64S/840 PSU TW1 L1200		6400	4000	IP20	911401897580
BN126C LED32S/830 PSU TW1 L1500	25.5	3200	3000	IP20	911401897880
BN126C LED35S/840 PSU TW1 L1500		3500	4000	IP20	911401897780
BN126C LED48S/830 PSU TW1 L1500	40	4800	3000	IP20	911401898080
BN126C LED52S/840 PSU TW1 L1500		5200	4000	IP20	911401897980
BN126C LED74S/830 PSU TW1 L1500	59	7400	3000	IP20	911401898280
BN126C LED80S/840 PSU TW1 L1500		8000	4000	IP20	911401898180
BN126C LED60S/830 PSU TW1 L1800	49	6000	3000	IP20	911401898480
BN126C LED64S/840 PSU TW1 L1800		6400	4000	IP20	911401898380
BN126C LED94S/830 PSU TW1 L1800	75	9400	3000	IP20	911401898680
BN126C LED100S/840 PSU TW1 L1800		10000	4000	IP20	911401898580

CoreLine

CoreLine trunking

L80 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
LL121X LED45S/840 1x PSD DA20 7 WH		4500	4000	IP20	88203900
LL121X LED45S/840 1x PSD WB 7 WH	32	4500	4000	IP20	88140700
LL121X LED45S/840 1x PSU DA20 5 WH		4500	4000	IP20	88183400
LL121X LED75S/840 1x PSD O 7 WH		7500	4000	IP20	38102100
LL121X LED76S/830 1x PSU VWB 7 WH		7600	3000	IP20	38169400
LL121X LED80S/840 1x PSD A 7 WH		8000	4000	IP20	38155700
LL121X LED80S/840 1x PSD DA20 7 WH		8000	4000	IP20	38137300
LL121X LED80S/840 1x PSD MB 7 WH		8000	4000	IP20	38124300
LL121X LED80S/840 1x PSD NB 7 WH		8000	4000	IP20	38120500
LL121X LED80S/840 1x PSD VWB 7 WH		8000	4000	IP20	38144100
LL121X LED80S/840 1x PSD WB 7 WH		8000	4000	IP20	38092500
LL121X LED80S/840 1x PSU MB 7 WH		8000	4000	IP20	38145800
LL121X LED80S/840 1x PSU NB 7 WH	54	8000	4000	IP20	38171700
LL121X LED80S/840 1x PSU VWB 7 WH		8000	4000	IP20	38176200
LL121X LED80S/840 1x PSU WB 7 WH		8000	4000	IP20	38157100
LL121X LED80S/840 PSU NB SMB WH KIT		8000	4000	IP20	38079600
LL121X LED80S/840 PSU NB TW3 SMB WH KIT		8000	4000	IP20	38083300
LL121X LED80S/840 PSU WB SMB WH KIT		8000	4000	IP20	38078900
LL121X LED80S/865 1x PSD WB 7 WH		8000	6500	IP20	38160100
LL122X LED80S/840 1x PSD VWB 7 WH		8000	4000	IP20	38146500
LL121X LED76S/830 1x PSD A 7 WH		7600	3000	IP20	38173100
LL121X LED76S/830 1x PSD WB 7 WH		7600	3000	IP20	38118200
LL121X LED76S/830 1x PSU VWB 7 EL3 WH		7600	3000	IP20	38162500
LL121X LED80S/840 1x PSU DA20 7 EL3 WH	56	8000	4000	IP20	38165600
LL121X LED80S/840 1x PSU MB 7 EL3 WH		8000	4000	IP20	38188500
LL121X LED80S/840 1x PSU NB 7 EL3 WH		8000	4000	IP20	38167000

CoreLine

CoreLine trunking – Continued

L80 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
LL121X LED80S/840 1x PSU WB 7 EL3 WH	56	8000	4000	IP20	38123600
LL120X LED90S/840 2x PSD DA20 7 VLC WH	64	9000	4000	IP20	88204600
LL120X LED90S/840 2x PSD NB 7 VLC WH		9000	4000	IP20	88190200
LL120X LED90S/840 2x PSD WB 7 VLC WH		9000	4000	IP20	88141400
LL120X LED160S/840 PSU NB SMB WH KIT	108	16000	4000	IP20	38082600
LL120X LED160S/840 PSU WB SMB WH KIT		16000	4000	IP20	38081900
LL120X LED160S/865 1x PSD MB 7 WH		16000	6500	IP20	38189200
LL120X LED160S/840 2x PSD WB 7 VLC WH		16000	4000	IP20	38087100
LL120X LED160S/840 2x PSD WB 7X2.5 VLC W		16000	4000	IP20	38086400
LL120X LED160S/840 2x PSU WB 5 WH		16000	4000	IP20	38088800
LL120X LED160S/840 2x PSU MB 5 WH		16000	4000	IP20	38091800
LL120X LED160S/840 2x PSU DA20 5 WH		16000	4000	IP20	38093200
LL120X LED160S/840 1x PSD WB 7 WH		16000	4000	IP20	38095600
LL120X LED160S/840 2x PSU NB 5 WH		16000	4000	IP20	38096300
LL120X LED160S/840 1x PSD WB 7X2.5 WH		16000	4000	IP20	38097000
LL120X LED160S/840 2x PSD MB 7 VLC WH		16000	4000	IP20	38098700
LL120X LED160S/840 2x PSD WB 9 VLC WH		16000	4000	IP20	38099400
LL120X LED152S/830 2x PSU WB 5 WH		15200	3000	IP20	38104500
LL120X LED160S/840 2x PSD VWB 7 VLC WH		16000	4000	IP20	38105200
LL120X LED160S/840 1x PSD MB 7 WH		16000	4000	IP20	38108300
LL120X LED160S/840 1x PSD NB 7 WH		16000	4000	IP20	38107600
LL120X LED152S/830 2x PSU VWB 5 WH		15200	3000	IP20	38106900
LL120X LED152S/830 2x PSU DA20 5 WH		15200	3000	IP20	38109000
LL120X LED160S/840 2x PSU WB 7 WH		16000	4000	IP20	38112000
LL120X LED160S/840 2x PSD NB 9 VLC WH		16000	4000	IP20	38110600
LL120X LED160S/840 2x PSD NB 7 VLC WH		16000	4000	IP20	38113700

CoreLine

CoreLine trunking – Continued

L80 at 50000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
LL120X LED160S/840 2x PSU VWB 5 WH		16000	4000	IP20	38117500
LL120X LED152S/830 2x PSD WB 7 VLC WH		15200	3000	IP20	38115100
LL120X LED160S/840 2x PSD A 7X2.5 VLC WH		16000	4000	IP20	38119900
LL120X LED160S/840 2x PSU A 5 WH		16000	4000	IP20	38129800
LL120X LED160S/840 2x PSD MB 9 VLC WH		16000	4000	IP20	38134200
LL120X LED160S/840 2x PSD DA20 7 VLC WH		16000	4000	IP20	38136600
LL120X LED160S/840 2x PSD A 7 VLC WH		16000	4000	IP20	38138000
LL120X LED150S/865 2x PSU O 5 WH	108	15000	6500	IP20	38142700
LL120X LED152S/830 2x PSU A 5 WH		15200	3000	IP20	38140300
LL120X LED152S/830 2x PSD DA20 7 VLC WH		15200	3000	IP20	38151900
LL120X LED160S/840 2x PSU MB 7 WH		16000	4000	IP20	38161800
LL120X LED160S/840 2x PSU NB 7 WH		16000	4000	IP20	38168700
LL120X LED160S/840 2x PSU VWB 7 WH		16000	4000	IP20	38175500
LL120X LED160S/840 2x PSU VWB 5X2.5 WH		16000	4000	IP20	38179300
LL120X LED160S/840 2x PSD VWB 7X2.5 VLC		16000	4000	IP20	38184700
LL120X LED150S/840 2x PSU PCO 5 WH		15000	4000	IP20	98887900
LL120X LED150S/840 2x PSD PCO 7 VLC WH	126	15000	4000	IP20	98766700
LL120X LED150S/840 1x PSD PCO 7 WH		15000	4000	IP20	98765000

CoreLine

CoreLine trunking – Accessories

1 PACK

Product Type	IP rating	EOC code
LL120Z CB WH (5PCS)	-	88161299
LL120Z MB-SW 2xEP CU7 WH	-	88146900
LL120Z SMB WH (5PCS)	-	88156899
LL121X 7 WH BC	IP20	88144500

CoreLine tempo – small

L80 at 75000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP110 LED42/NW A	38	4200	4000	IP65	30635300
BVP110 LED42/NW S		4200	4000	IP65	30636000

CoreLine

CoreLine tempo – medium

L80 at 75000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP125 LED80-4S/740 OFA52	63	8000	4000	IP66	45588000
BVP125 LED80-4S/740 S		8000	4000	IP66	45590300
BVP125 LED120-4S/740 OFA52	95	12000	4000	IP66	45587300
BVP125 LED120-4S/740 S		12000	4000	IP66	45589700

CoreLine tempo – large

IK08 | 5 J vandal-protected

L80 at 75000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP130 LED160-4S/740 A	120	16000	4000	IP66	09641000
BVP130 LED160-4S/740 S		16000	4000	IP66	09644100
BVP130 LED210-4S/740 A	162	21000	4000	IP66	09640300
BVP130 LED210-4S/740 S		21000	4000	IP66	09643400
BVP130 LED260-4S/740 A	217	26000	4000	IP66	09639700
BVP130 LED260-4S/740 S		26000	4000	IP66	09642700

CoreLine

CoreLine tempo - X-large

L80 at 75000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BVP140 LED360-4S 30K6/740 PSU OFA52	225	30600	4000	IP66	87280900
BVP140 LED360-4S 31K3/740 PSU S		31320	4000	IP66	87284700
BVP140 LED360-4S 30K6/740 PSD OFA52 D9		30600	4000	IP66	87288500
BVP140 LED360-4S 31K3/740 PSD S D9		31320	4000	IP66	87292200
BVP140 LED420-4S 35K3/740 PSU OFA52	250	35280	4000	IP66	87279300
BVP140 LED420-4S 36K1/740 PSD S D9		36120	4000	IP66	87291500
BVP140 LED420-4S 36K1/740 PSU S		36120	4000	IP66	87283000
BVP140 LED420-4S 35K3/740 PSD OFA52 D9		35280	4000	IP66	87287800
BVP140 LED480-4S 40K3/740 PSU OFA52	295	40320	4000	IP66	87278600
BVP140 LED480-4S 40K3/740 PSD OFA52 D9		40320	4000	IP66	87286100
BVP140 LED480-4S 41K3/740 PSU S		41280	4000	IP66	87282300
BVP140 LED480-4S 41K3/740 PSD S D9		41280	4000	IP66	87290800

CoreLine

CoreLine malaga

L70 at 70000h

1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BRP101 LED37/740 I DM	29.6	3054	4000	IP65	99815100
BRP102 LED55/740 I DM	39	4600	4000	IP65	99817500
BRP102 LED55/740 II DM		4600	4000	IP65	99818200
BRP102 LED75/740 I DM	56.5	6133	4000	IP65	99819900
BRP102 LED75/740 II DM		6133	4000	IP65	99820500
BRP102 LED110/740 I DM	83	9006	4000	IP65	99821200
BRP102 LED110/740 II DM		9006	4000	IP65	99822900

CoreLine

CoreLine malaga – Accessories

1 PACK

Product Type	EOC code
ZRP220 AD60/60 A5	62134100

Philips
Ledinaire

The essential range of trusted products for everyday lighting jobs that need good performance

Find the **right** solution in our range using the **Selector tool**
productfinder.lighting.philips.com

Find out **more** about **all 12** different Ledinaire luminaires on **philips.com/ledinaire**

Now with **3 years** warranty!

Trusted

Reliable

Great value

Ledinaire **Surface-mounted**

NEW

- Surface downlight solution
- IP44 rating perfect for indoor applications
- Full transparent cover providing homogeneous light effect
- Optional motion detection and daylight sensor

Ledinaire **batten**

- LED tube versions for easy replacement of light sources
- Mounting accessories included
- Trusted performance, low early failures

Ledinaire **waterproof**

- Easy to use: light levels tuned to conventional
- Reliable driver, less early failures
- High efficacy up to 120 lm/W

Ledinaire

Easily make the switch to LED lighting without high investments. The Philips Ledinaire portfolio consists of 9 popular LED luminaires. Choose affordable, reliable and energy-efficient lighting from the leading name in LED.

Ledinaire panel

www.lighting.philips.com/main/products/ledinaire

50000h/L70 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC065B LED34S/840 PSU W60L60 OC	34	3400	4000	IP20	38647499
RC065B LED34S/865 PSU W60L60 OC		3400	6500	IP20	36204599
RC065B LED34S/865 PSU W60L60 NOC		3400	6500	IP20	36206999
RC065B LED34S/840 PSU W60L60 NOC		3400	4000	IP20	79180399
RC066B LED34S/840 PSU W62L62 OC		3400	4000	IP20	36558999

Ledinaire recessed and Ledinaire surface-mounted

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RC060B LED34S/840 PSU W60L60 NOC	34	3400	4000	IP20	06958500
SM060C LED34S/840 PSU W20L120 NOC		3400	4000	IP20	06962200
SM060C LED34S/840 PSU W20L120 OC		3400	4000	IP20	35039400
RC060B LED40S/840 PSU W60L60 NOC	40	4000	4000	IP20	35040000
SM060C LED40S/840 PSU W20L120 NOC		4000	4000	IP20	35041700

Ledinaire

Ledinaire Wall-mounted

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	Motion/Daylight sensor	IP rating	EOC code
	W	lm	K			
1 Ledinaire Square Wall-mounted						
WL055V LED6S/840 PSU MDU WH	6	630	4000	yes	IP65	35064699
WL055V LED6S/830 PSU WH		600	3000	-	IP65	34941199
WL055V LED6S/840 PSU WH		630	4000	-	IP65	34942899
WL055V LED6S/830 PSU MDU WH		600	3000	yes	IP65	35409599
WL055V LED6S/830 PSU EL3 WH	8	600	3000	-	IP65	96774199
WL055V LED6S/840 PSU EL3 WH		630	4000	-	IP65	96773499
2 Ledinaire Wall-mounted						
WL060V LED11S/830 PSU II WH	12	1100	3000	-	IP44	33909299
WL060V LED11S/840 PSU II WH		1100	4000	-	IP44	33910899
WL060V LED17S/830 PSU II WH	18.5	1700	3000	-	IP44	33911599
WL060V LED17S/840 PSU II WH		1700	4000	-	IP44	33912299
WL060V LED17S/830 PSU MDU II WH	19.5	1700	3000	yes	IP44	33913999
WL060V LED17S/840 PSU MDU II WH		1700	4000	yes	IP44	33914699

Ledinaire

Ledinaire downlight DN060B, DN065B, DN029B and the new Ledinaire surface-mounted downlight DN065C

DN060B 1

DN029B D90 2

DN029B D150 2

DN029B D200 2

DN065B 3

DN065C 4

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
Ledinaire downlight					
1 DN060B					
DN060B LED8S/830 PSU WH	9	800	3000	IP20	30662999
DN060B LED8S/840 PSU WH		800	4000	IP20	30664399
DN060B LED18S/830 PSU WH	18	1800	3000	IP20	30661299
DN060B LED18S/840 PSU WH		1800	4000	IP20	30663699
2 DN029B					
DN029B LED8/CCT 8W 220-240V D90 EU	8.5	800	3000, 4300 and 6500	IP20/44	66018500
DN029B LED12/CCT 14W 220-240V D150 EU	14	1200	3000, 4300 and 6500	IP20/44	66020800
DN029B LED20/CCT 24W 220-240V D200 EU	24	2000	3000, 4300 and 6500	IP20/44	66022200
3 DN065B					
DN065B G2 LED20/840 22W 220V D200 RD EU	22	2000	4000	IP20 | Fingerprotected	67945300
DN065B G2 LED10/840 11W 220V D150 RD EU	11	1000	4000		67941500
DN065B G2 LED19/830 22W 220V D200 RD EU	22	1900	3000		67943900
DN065B G2 LED10/840 11W 220V L150 SQ EU	11	1000	4000		67949100
DN065B G2 LED10/830 11W 220V D150 RD EU		950	3000		67939200
DN065B G2 LED10/830 11W 220V L150 SQ EU		950	3000		67947700
Ledinaire surface-mounted downlight					
NEW **4 DN065C**					
DN065C LED10/830 11W 220V D175 RD EU	11	950	3000	IP20/40	72007000
DN065C LED10/840 11W 220V D175 RD EU		100	4000	IP20/40	72011700
DN065C LED20/830 23W 220V D225 RD EU	23	1900	3000	IP20/40	72011700
DN065C LED20/840 23W 220V D225 RD EU		2000	4000	IP20/40	72013100

Ledinaire

Ledinaire Zadora LED

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
RS049B LED-MS-40-5W-2700-GU10 WH 50W		355	2700	IP20	07012399
RS049B LED-MS-40-5W-3000-GU10 WH 50W		365	3000	IP20	07015499
RS049B LED-MS-40-5W-4000-GU10 WH 50W	5	380	4000	IP20	07013099
RS049B LED-MS-40-5W-2700-GU10 ALU 50W		355	2700	IP20	07014799
RS049B LED-MS-40-5W-3000-GU10 ALU 50W		365	3000	IP20	07016199

Ledinaire

Ledinaire ClearAccent

1

2

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
1 RS060B LED5-36-/830 PSR II WH	6	500	3000	IP20	07267799
1 RS060B LED5-36-/840 PSR II WH		500	4000	IP20	07268499
2 RS061B LED5-36-/830 PSR II WH		500	3000	IP20	07269199
2 RS061B LED5-36-/840 PSR II WH		500	4000	IP20	07270799

Ledinaire Slim Waterproof

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT055C LED18S/840 PSU L600	16.5	1800	4000	IP65	79296199
WT055C LED18S/840 PSU TW1 L600		1800	4000	IP65	79297899
WT055C LED36S/840 PSU L1200	33	3600	4000	IP65	79298599
WT055C LED36S/840 PSU TW1 L1200		3600	4000	IP65	79299299
WT055C LED56S/840 PSU L1500	51	5600	4000	IP65	79300599
WT055C LED56S/840 PSU TW1 L1500		5600	4000	IP65	79301299

Ledinaire

Ledinaire waterproof

50000h/L70 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
WT060C LED18S/840 PSU L600	15	1800	4000	IP66	36007299
WT060C LED18S/840 PSU L600	16,5	1800	4000	IP65	38910999
WT060C LED18S/840 PSU TW1 L600		1800	4000	IP65	38911699
WT060C LED25S/840 PSU TW1 L1200	20	2500	4000	IP66	36292299
WT060C LED25S/840 PSU L1200		2500	4000	IP66	36291599
WT060C LED34S/840 PSU L1500	28	3400	4000	IP66	36293999
WT060C LED34S/840 PSU TW1 L1500		3400	4000	IP66	36294699
WT060C LED36S/865 PSU L1200	30	3600	6500	IP66	36015799
WT060C LED36S/840 PSU L1200		3600	4000	IP66	36009699
WT060C LED36S/840 PSU TW1 L1200		3600	4000	IP66	36010299
WT060C LED56S/865 PSU L1500	46	5600	6500	IP66	36017199
WT060C LED56S/840 PSU L1500		5600	4000	IP66	36011999
WT060C LED56S/840 PSU TW1 L1500		5600	4000	IP66	36012699
WT060C LED 80S/840 PSU L1800	65	8000	4000	IP66	36295399

Ledinaire

Ledinaire floodlight

50000h/L70 1 PACK

Product Type	LED	Lumen Output	Color Temp.	Motion/Daylight sensor	IP rating	EOC code
	W	lm	K			
1 BVP154 LED10/830 PSU 10W VWB CE	10	1000	3000	-	IP65	32970399
1 BVP154 LED10/830 PSU 10W VWB MDU CE		1000	3000	yes	IP65	33131799
1 BVP154 LED10/840 PSU 10W VWB CE		1050	4000	-	IP65	32971099
1 BVP154 LED10/840 PSU 10W VWB MDU CE		1050	4000	yes	IP65	33132499
1 BVP154 LED20/830 PSU 20W VWB CE	20	2000	3000	-	IP65	32972799
1 BVP154 LED20/830 PSU 20W VWB MDU CE		2000	3000	yes	IP65	33133199
1 BVP154 LED21/840 PSU 20W VWB CE		2100	4000	-	IP65	32973499
1 BVP154 LED21/840 PSU 20W VWB MDU CE		2100	4000	yes	IP65	33134899
2 BVP154 LED50/830 PSU 50W VWB CE	50	5000	3000	-	IP65	32974199
2 BVP154 LED50/830 PSU 50W VWB MDU CE		5000	3000	yes	IP65	33135599
2 BVP154 LED52/840 PSU 50W VWB CE		5250	4000	-	IP65	32975899
2 BVP154 LED52/840 PSU 50W VWB MDU CE		5250	4000	yes	IP65	33136299
2 BY020P LED100S/840 PSU WB GR	97	10000	4000	-	IP65	33996299
3 BVP155 LED100/840 PSU 100W AWB CE	100	10000	4000	-	IP65	33128799
3 BVP155 LED105/840 PSU 100W VWB CE		10500	4000	-	IP65	33125699
4 BVP155 LED150/840 PSU 150W AWB CE	150	15000	4000	-	IP65	33129499
4 BVP155 LED157/840 PSU 150W VWB CE		15750	4000	-	IP65	33126399
5 BVP155 LED200/840 PSU 200W AWB CE	200	20000	4000	-	IP65	33130099
5 BVP155 LED210/840 PSU 200W VWB CE		21000	4000	-	IP65	33127099
5 BY021P LED200S/840 PSU WB GR	190	20000	4000	-	IP65	33998699

Ledinaire

Ledinaire batten

1

2

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
1 Integrated LED batten					
BN013C LED5S/840 L300	5	500	4000	IP20	34952799
BN013C LED5S/830 L300		475	3000	IP20	34953499
BN013C LED10S/840 L600	10	1000	4000	IP20	34954199
BN013C LED10S/830 L600		940	3000	IP20	34955899
BN013C LED15S/840 L900	15	1500	4000	IP20	34956599
BN013C LED14S/830 L900		1410	3000	IP20	34957299
BN013C LED20S/840 L1200	20	2000	4000	IP20	34958999
BN013C LED19S/830 L1200		1880	3000	IP20	34959699
BN013C LED25S/840 L1500	24	2500	4000	IP20	34960299
BN013C LED24S/830 L1500		2350	3000	IP20	34961999
2 LED tube-based batten					
BN060C 1xTLED16/840 L1200	18	1600	4000	IP20	07007999
BN060C 2xTLED16/840 L1200	36	3200	4000	IP20	07009399

Ledinaire

Ledinaire Pentura mini LED

50000h/L65 1 PACK

Product Type	LED	Lumen Output	Color Temp.	IP rating	EOC code
	W	lm	K		
BN132C LED3S/840 PSU L300	4	350	4000	IP40	07249399
BN132C LED3S/830 PSU L300		350	3000	IP40	07250999
BN132C LED6S/840 PSU L600	7	650	4000	IP40	07247999
BN132C LED6S/830 PSU L600		650	3000	IP40	07248699
BN132C LED9S/840 PSU L900	10	950	4000	IP40	07245599
BN132C LED9S/830 PSU L900		950	3000	IP40	07246299
BN132C LED12S/840 PSU L1200	14	1250	4000	IP40	07243199
BN132C LED12S/830 PSU L1200		1250	3000	IP40	07244899

Ledinaire highbay

50000h/L65 1 PACK

Product Type		LED	Lumen Output	Color Temp.	IP rating	EOC code
		W	lm	K		
BY020P LED100S/840 PSU WB GR		97	10000	4000	-	33996299
BY021P LED200S/840 PSU WB GR		190	19500	4000	-	33998699
BY020Z AC	Reflector used for LED100				-	33992499
BY021Z AC	Reflector used for LED200				-	33994899

Create the perfect ambience **for every space**

MASTER LEDspot ExpertColor features a light spectrum similar to halogens, for a true color experience.

MASTER LEDspot **ExpertColor**

Expert Color

CRI 97

Best-in-class color realization, CRI97

Customized light spectrum similar to halogen

Energy savings up to 85%*

Deep and smooth dimming, below 5%

40,000 hours lifetime

* Compared to halogen lamps

Designed **to be seen**

Today our work spaces need to fulfil multiple functions. We produce, meet, present, sell and require our lighting to be adaptable to meet every need and mood. There is a growing demand for lighting to be decorative and stylish; it needs to be designed to be seen. The Philips Deco collections are highly stylish giant filament LED bulbs, designed to make a statement and accentuate your customer's office or shop interior, or to complement the style in a hotel, bar or restaurant. Complement multiple design preferences with Philips unique filament designs.

Deco LED **Vintage Giant**

Accentuates a traditional warm & cozy vintage atmosphere.

Deco LED **Modern Giant**

Modern, a bright and sleek, fresh, forward design.

Easy to upgrade, simple to install

Both collections get the most out of classic designs, so you're able to select the perfect shape, from a choice of 'Globe', 'Teardrop' or 'Tubular' shaped bulbs. Dimmable and non-dimmable.

LED lamps and tubes

LED lamps save you up to 69% energy and offer the same light quality as conventional lamps. Philips MASTER LED lamps provide you with constant colors, high performance and maximum dimming compatibility. CorePro lamps are good for energy savings of up to 69% and have a lifespan of 30,000 hours. The complete range of Philips LED lamps is designed as a 1-on-1 replacement for currently installed conventional lighting.

LED spot MV GU10

www.philips.com/ledlamps

1 CorePro LED spot GU10

2 MASTER LEDspot ExpertColor MV

3 MASTER LEDspot Value

4 MASTER LEDspot VLE

5 CorePro LED spot GU10

6 CorePro LED spot GU10 550lm

= Dimmable
= Non-dimmable
= DimTone
GU10
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDspot 2.7-25W GU10 827 36D	25	2.7	215	79	470	36	✗	80	2700	15000	A++	75209800
1 CorePro LEDspot 2.7-25W GU10 830 36D		2.7	225	83	490	36	✗	80	3000	15000	A++	72829100
1 CorePro LEDspot 2.7-25W GU10 840 36D		2.7	230	83	500	36	✗	80	4000	15000	A++	72831400
2 MAS LED ExpertColor 3.9-35W GU10 927 25D	35	3.9	265	68	700	25	◯	97	2700	40000	A+	70749400
2 MAS LED ExpertColor 3.9-35W GU10 927 36D		3.9	265	68	540	36	◯	97	2700	40000	A+	70755500
2 MAS LED ExpertColor 3.9-35W GU10 930 25D		3.9	280	72	750	25	◯	97	3000	40000	A+	70751700
2 MAS LED ExpertColor 3.9-35W GU10 930 36D		3.9	280	72	560	36	◯	97	3000	40000	A+	70757900
2 MAS LED ExpertColor 3.9-35W GU10 940 25D		3.9	300	77	800	25	◯	97	4000	40000	A+	70753100
2 MAS LED ExpertColor 3.9-35W GU10 940 36D		3.9	300	77	600	36	◯	97	4000	40000	A+	70759300
3 MAS LEDspot VLE DT 3.7-35W GU10 927 36D		3.7	260	70	500	36	DimTone	90	2200-2700	25000	A+	70809500
3 MAS LEDspot VLE D 3.7-35W GU10 927 36D		3.7	260	70	500	36	◯	90	2700	25000	A+	70773900
3 MAS LEDspot VLE D 3.7-35W GU10 927 60D		3.7	260	70	330	60	◯	90	2700	25000	A+	70779100
3 MAS LEDspot VLE D 3.7-35W GU10 930 36D		3.7	270	73	500	36	◯	90	3000	25000	A+	70775300
3 MAS LEDspot VLE D 3.7-35W GU10 930 60D		3.7	270	73	340	60	◯	90	3000	25000	A+	70781400
3 MAS LEDspot VLE D 3.7-35W GU10 940 36D		3.7	285	77	500	36	◯	90	4000	25000	A++	70777700
3 MAS LEDspot VLE D 3.7-35W GU10 940 60D		3.7	285	77	350	60	◯	90	4000	25000	A++	70783800
1 CorePro LEDspot 4-35W GU10 827 36D DIM		4	250	62	500	36	◯	80	2700	15000	A+	72133900
1 CorePro LEDspot 3.5-35W GU10 827 36D		3.5	255	72	545	36	✗	80	2700	15000	A+	75253100
1 CorePro LEDspot 3.5-35W GU10 830 36D		3.5	265	75	565	36	✗	80	3000	15000	A++	72833800
1 CorePro LEDspot 3.5-35W GU10 840 36D		3.5	275	79	590	36	✗	80	4000	15000	A++	72835200
2 MAS LED ExpertColor 5.5-50W GU10 927 25D	50	5.5	355	65	1000	25	◯	97	2700	40000	A+	70761600
2 MAS LED ExpertColor 5.5-50W GU10 927 36D		5.5	355	65	800	36	◯	97	2700	40000	A+	70767800
2 MAS LED ExpertColor 5.5-50W GU10 930 25D		5.5	375	68	1000	25	◯	97	3000	40000	A+	70763000
2 MAS LED ExpertColor 5.5-50W GU10 930 36D		5.5	375	68	800	36	◯	97	3000	40000	A+	70769200
2 MAS LED ExpertColor 5.5-50W GU10 940 25D		5.5	400	73	1050	25	◯	97	4000	40000	A+	70765400
2 MAS LED ExpertColor 5.5-50W GU10 940 36D		5.5	400	73	850	36	◯	97	4000	40000	A+	70771500

The current dimmer list for high-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot MV GU10 - Continued

1 CorePro LED spot GU10

2 MASTER LEDspot ExpertColor MV

3 MASTER LEDspot Value

4 MASTER LEDspot VLE

5 CorePro LED spot GU10

6 CorePro LED spot GU10 550lm

= Dimmable
= Non-dimmable
= DimTone
GU10
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
3 MAS LEDspot VLE DT 4.9-50W GU10 927 36D	50	4.9	355	72	650	36	DimTone	90	2200-2700	25000	A+	70811800
3 MAS LEDspot VLE D 4.9-50W GU10 927 36D		4.9	355	72	650	36	Dimmable	90	2700	25000	A+	70785200
3 MAS LEDspot VLE D 4.9-50W GU10 927 60D		4.9	355	72	400	60	Dimmable	90	2700	25000	A+	70791300
3 MAS LEDspot VLE D 4.9-50W GU10 930 36D		4.9	365	74	650	36	Dimmable	90	3000	25000	A+	70787600
3 MAS LEDspot VLE D 4.9-50W GU10 930 60D		4.9	365	74	400	60	Dimmable	90	3000	25000	A+	70793700
3 MAS LEDspot VLE D 4.9-50W GU10 940 36D		4.9	380	78	700	36	Dimmable	90	4000	25000	A+	70789000
3 MAS LEDspot VLE D 4.9-50W GU10 940 60D		4.9	380	78	400	60	Dimmable	90	4000	25000	A+	70795100
1 CorePro LEDspot 5-50W GU10 827 36D DIM		5	350	70	650	36	Dimmable	80	2700	15000	A+	72137700
1 CorePro LEDspot 5-50W GU10 830 36D DIM		5	365	73	710	36	Dimmable	80	3000	15000	A+	72139100
1 CorePro LEDspot 5-50W GU10 840 36D DIM		5	380	76	710	36	Dimmable	80	4000	15000	A+	73024900
1 CorePro LEDspot 4.6-50W GU10 827 36D		4.6	355	77	700	36	Non-dimmable	80	2700	15000	A+	75251700
1 CorePro LEDspot 4.6-50W GU10 840 36D		4.6	390	84	770	36	Non-dimmable	80	4000	15000	A++	72839000
5 CorePro LEDspot 4.6-50W GU10 827 36D 5CT		4.6	355	77	700	36	Non-dimmable	80	2700	15000	A+	70029400
5 Corepro LEDspot 4.6-50W GU10 865 36D		4.6	390	84	770	36	Non-dimmable	80	6500	15000	A++	72841300
6 Corepro LEDspot 550lm GU10 830 120D		5	550	110	-	120	Non-dimmable	80	3000	15000	A+	68688100
6 Corepro LEDspot 550lm GU10 840 120D		5	550	110	-	120	Non-dimmable	80	4000	15000	A+	68690400
6 Corepro LEDspot 550lm GU10 865 120D		5	550	110	-	120	Non-dimmable	80	6500	15000	A+	68692800
1 CorePro LEDspot MV 6.5-65W GU10 830 36D	65	5	460	92	800	36	Non-dimmable	80	3000	15000	A++	74385000
1 CorePro LEDspot 5-65W GU10 840 36D ND		5	485	97	800	36	Non-dimmable	80	4000	15000	A++	74387400
4 MAS LED spot VLE D 6.2-80W GU10 930 36D	80	6.2	575	92	850	36	Dimmable	90	3000	40000	A++	70525100
4 MAS LED spot VLE D 650lm GU10 930 120D		6.2	650	104	200	120	Dimmable	90	3000	40000	A+	70609800
4 MAS LED spot VLE D 6.2-80W GU10 965 36D		6.2	575	92	850	36	Dimmable	90	6500	40000	A++	70607400
4 MAS LED spot VLE D 680lm GU10 940 120D		6.2	680	109	200	120	Dimmable	90	4000	40000	A+	70611100
4 MAS LED spot VLE D 6.2-80W GU10 940 36D		6.2	575	92	850	36	Dimmable	90	4000	40000	A++	70523700
4 MAS LED spot VLE D 680lm GU10 965 120D		6.2	680	109	200	120	Dimmable	90	6500	40000	A+	70613500
4 MAS LED spot VLE D 6.2-80W GU10 927 36D		6.2	575	92	850	36	Dimmable	90	2700	40000	A++	67541700
4 MAS LED spot VLE DT 6.2-80W GU10 927 36D		6.2	575	92	950	36	DimTone	90	2200-2700	40000	A++	66271400

The current dimmer list for high-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot LV GU5.3

1 MASTER LEDspot ExpertColor

2 MASTER LEDspot

3 MASTER LEDspot VLE

4 CorePro LEDspot

5 MASTER LEDspot LV DimTone

6 CorePro LEDspot MR16

7 LEDClassic MR16

8 MASTER LEDspot VLE

= Dimmable

= Non-dimmable

= DimTone

GU5.3

10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LED ExpertColor 6.5-35W MR16 927 10D	35	6.5	410	63	4600	15		97,0	2700	40000	A	73871900
1 MAS LED ExpertColor 6.5-35W MR16 927 24D		6.5	420	65	2200	24		97,0	2700	40000	A	73877100
1 MAS LED ExpertColor 6.5-35W MR16 927 36D		6.5	420	65	1300	36		97,0	2700	40000	A	73883200
1 MAS LED ExpertColor 6.5-35W MR16 927 60D		6.5	400	62	410	60		97,0	2700	40000	A	75751200
1 MAS LED ExpertColor 6.5-35W MR16 930 10D		6.5	430	66	5000	15		97,0	3000	40000	A	73873300
1 MAS LED ExpertColor 6.5-35W MR16 930 24D		6.5	440	68	2350	24		97,0	3000	40000	A+	73879500
1 MAS LED ExpertColor 6.5-35W MR16 930 36D		6.5	440	68	1400	36		97,0	3000	40000	A+	73885600
1 MAS LED ExpertColor 6.5-35W MR16 930 60D		6.5	440	68	440	60		97,0	3000	40000	A+	75753600
1 MAS LED ExpertColor 6.5-35W MR16 940 10D		6.5	440	68	5000	15		97,0	4000	40000	A+	73875700
1 MAS LED ExpertColor 6.5-35W MR16 940 24D		6.5	460	71	2350	24		97,0	4000	40000	A+	73881800
1 MAS LED ExpertColor 6.5-35W MR16 940 36D		6.5	460	71	1400	36		97,0	4000	40000	A+	73887000
1 MAS LED ExpertColor 6.5-35W MR16 940 60D		6.5	440	68	440	60		97,0	4000	40000	A+	75755000
3 MAS LEDspotLV DimTone 5-35W MR16 36D		5	345	69	600	36		80	2200-2700	25000	A+	81538000
3 MAS LEDspot VLE D 5.5-35W MR16 827 60D		5.5	450	82	500	60		80,0	2700	25000	A+	70829300
3 MAS LEDspot VLE D 5.5-35W MR16 830 60D		5.5	460	84	500	60		80,0	3000	25000	A+	70831600
3 MAS LEDspot VLE D 5.5-35W MR16 840 60D		5.5	490	89	550	60		80,0	4000	25000	A+	70833000
3 MAS LEDspot VLE D 5.5-35W MR16 827 36D		5.5	450	82	1000	36		80,0	2700	25000	A+	70823100
3 MAS LEDspot VLE D 5.5-35W MR16 830 36D		5.5	460	84	1000	36		80,0	3000	25000	A+	70825500
3 MAS LEDspot VLE D 5.5-35W MR16 840 36D		5.5	490	89	1100	36		80,0	4000	25000	A+	70827900
1 MAS LED ExpertColor 7.5-43W MR16 927 24D	43	7.5	485	65	2400	24		92,0	2700	40000	A	73538100
1 MAS LED ExpertColor 7.5-43W MR16 930 24D		7.5	500	67	2600	24		92,0	3000	40000	A	73540400
1 MAS LED ExpertColor 7.5-43W MR16 940 24D		7.5	520	69	2800	24		92,0	4000	40000	A	73542800
1 MAS LED ExpertColor 7.5-43W MR16 927 36D		7.5	485	65	1400	36		92,0	2700	40000	A	73544200
1 MAS LED ExpertColor 7.5-43W MR16 930 36D		7.5	500	67	1550	36		92,0	3000	40000	A	73546600
1 MAS LED ExpertColor 7.5-43W MR16 940 36D		7.5	520	69	1650	36		92,0	4000	40000	A	73548000

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot LV GU5.3 - Continued

1 MASTER LEDspot ExpertColor
2 MASTER LEDspot
3 MASTER LEDspot VLE
4 CorePro LEDspot
5 MASTER LEDspot LV DimTone
6 CorePro LEDspot MR16
7 MASTER LEDspot VLE

= Dimmable
= Non-dimmable
= DimTone

GU5.3
10 PACK

	Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
		W	W	lm	lm/W	cd	°			K	Hrs.		
	2 MAS LEDspot LV D 8-50W 827 MR16 24D		8	621	78	3100	24	◐	80	2700	40000	A+	81253200
	2 MAS LEDspot LV D 8-50W 827 MR16 36D		8	621	78	1700	36	◐	80	2700	40000	A+	81267900
	2 MAS LEDspot LV D 8-50W 830 MR16 24D		8	621	78	3250	24	◐	80	3000	40000	A+	81263100
	2 MAS LEDspot LV D 8-50W 830 MR16 36D		8	621	78	1700	36	◐	80	3000	40000	A+	81269300
	2 MAS LEDspot LV D 8-50W 840 MR16 24D		8	670	84	3350	24	◐	80	4000	40000	A+	81265500
	2 MAS LEDspot LV D 8-50W 840 MR16 36D		8	670	84	1800	36	◐	80	4000	40000	A+	81271600
	6 CorePro LEDspotLV ND 8-50W 830 MR16 50D		9	720	80	1400	50	✕	80	3000	15000	A+	52891400
	6 CorePro LEDspotLV ND 8-50W 840 MR16 36D		8	750	94	1400	36	✕	80	4000	15000	A+	52889100
	6 CorePro LEDspotLV ND 8-50W 840 MR16 50D		8	770	96	1400	50	✕	80	4000	15000	A+	52893800
	3 MAS LEDspot VLE D 7-50W MR16 827 36D	50	7	621	89	1500	36	◐	80	2700	25000	A+	81554000
	3 MAS LEDspot VLE D 7-50W MR16 827 60D		7	621	89	750	60	◐	80	2700	25000	A+	81560100
	3 MAS LEDspot VLE D 7-50W MR16 830 36D		7	630	90	1500	36	◐	80	3000	25000	A+	81556400
	3 MAS LEDspot VLE D 7-50W MR16 830 60D		7	630	90	750	60	◐	80	3000	25000	A+	81562500
	3 MAS LEDspot VLE D 7-50W MR16 840 36D		7	660	94	1650	36	◐	80	4000	25000	A+	81558800
	3 MAS LEDspot VLE D 7-50W MR16 840 60D		7	660	94	800	60	◐	80	4000	25000	A+	81564900
NEW	7 MAS LEDspot VLE D 5-50W GU10 827 36D 5CT		5	345	69	650	36	◐	80,0	2700	25000	A+	73950800
NEW	7 MAS LEDspot VLE D 5-50W GU10 830 36D 5CT		5	345	69	650	36	◐	80,0	3000	25000	A+	74716900
	4 CorePro LEDspot ND 7-50W MR16 840 36D		7	660	94	1500	36	✕	80	4000	15000	A+	81479600
	5 MAS LEDspotLV DimTone 7-50W MR16 36D		7	621	88	1000	36	DT	80	2200-2700	40000	A+	65820500

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot LV AR111

1 MASTER LEDspot LV AR111

= Dimmable

= Non-dimmable

G53

6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LEDspot LV D 11-50W 927 AR111 8D	50	11	560	51	8	8		90	2700	40000	A	57833900
1 MAS LEDspot LV D 11-50W 930 AR111 8D		11	580	53	8	8		90	3000	40000	A	57835300
1 MAS LEDspot LV D 11-50W 927 AR111 24D		11	560	51	24	24		90	2700	40000	A	51488700
1 MAS LEDspot LV D 11-50W 930 AR111 24D		11	580	53	24	24		90	3000	40000	A	51490000
1 MAS LEDspot LV D 11-50W 927 AR111 40D		11	550	50	40	40		90	2700	40000	A	51492400
1 MAS LEDspot LV D 11-50W 930 AR111 40D		11	570	52	40	40		90	3000	40000	A	51494800
1 MAS LEDspot LV D 15-75W 940 AR111 24D	75	15	830	55	24	24		90	4000	40000	A	71834600
1 MAS LEDspot LV D 15-75W 940 AR111 40D		15	830	55	40	40		90	4000	40000	A	71836000
1 MAS LEDspot LV D 15-75W 927 AR111 24D		15	800	53	24	24		90	2700	40000	A	51496200
1 MAS LEDspot LV D 15-75W 930 AR111 24D		15	810	54	24	24		90	3000	40000	A	51498600
1 MAS LEDspot LV D 15-75W 927 AR111 40D		15	800	53	40	40		90	2700	40000	A	51500600
1 MAS LEDspot LV D 15-75W 930 AR111 40D		15	810	54	40	40		90	3000	40000	A	51502000
1 MAS LEDspot LV D 20-100W 827 AR111 40D	100	20	1160	58	40	40		80	2700	25000	A	70745600
1 MAS LEDspot LV D 20-100W 830 AR111 24D		20	1200	60	24	24		80	3000	25000	A	70743200
1 MAS LEDspot LV D 20-100W 830 AR111 40D		20	1180	59	40	40		80	3000	25000	A	70747000
1 MAS LEDspot LV D 20-100W 840 AR111 24D		20	1250	63	24	24		80	4000	25000	A	72532000
1 MAS LEDspot LV D 20-100W 840 AR111 40D		20	1250	63	40	40		80	4000	25000	A	72534400
1 MAS LEDspot LV D 20-100W 827 AR111 24D		20	1180	59	24	24		80	2700	25000	A	51504400

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot LV MR11

1 CorePro LEDspot MR11

2 MASTER LEDspot LV MR11

= Dimmable
= Non-dimmable
MR11
12 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LED spot 2.3-20W 827 MR11 36D	20	2.3	184	80	400	36	✗	80	2700	15000	A++	65948600
2 MAS LEDspot LV 3.5-20W 827 MR11 24D		3.5	200.0	57	1000	24	✗	80.0	2700	40000	A+	41019600

LED spot MV PAR 20

1 MASTER LEDspot CLA PAR20

= Dimmable
= Non-dimmable
E27
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LEDspot CLA D 6-50W 827 PAR20 25D	50	6	500	83	1500	25	✓	80	2700	25000	A+	71356300
1 MAS LEDspot CLA D 6-50W 830 PAR20 25D		6	515	86	1500	25	✓	80	3000	25000	A+	71366200
1 MAS LEDspot CLA D 6-50W 840 PAR20 25D		6	540	90	1500	25	✓	80	4000	25000	A+	71368600
1 MAS LEDspot CLA D 6-50W 827 PAR20 40D		6	500	83	800	40	✓	80	2700	25000	A+	71370900
1 MAS LEDspot CLA D 6-50W 830 PAR20 40D		6	515	86	800	40	✓	80	3000	25000	A+	71372300
1 MAS LEDspot CLA D 6-50W 840 PAR20 40D		6	540	90	800	40	✓	80	4000	25000	A+	71374700

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot PAR30S

MASTER LEDspot CLA PAR30S

= Dimmable
= Non-dimmable
E27
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LEDspot CLA D 9.5-75W 827 PAR30S 25D	75	9.5	740	78	3500	25	✓	80	2700	25000	A+	71380800
1 MAS LEDspot CLA D 9.5-75W 830 PAR30S 25D		9.5	810	85	3500	25	✓	80	3000	25000	A+	71390700
1 MAS LEDspot CLA D 9.5-75W 840 PAR30S 25D		9.5	820	86	3500	25	✓	80	4000	25000	A+	71384600

LED spot PAR30L

MASTER LEDspot PAR30L

= Dimmable
= Non-dimmable
E27
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LEDspot ND 20W PAR30L E27 830 15D	35	20	1700	85	19000	15	✗	80	3000	25000	A+	61303700
1 MAS LEDspot ND 20W PAR30L E27 830 30D		20	1650	83	7000	30	✗	80	3000	25000	A+	61305100
1 MAS LEDspot ND 37W PAR30L E27 827 15D	70	37	3500	95	35000	15	✗	80	2700	25000	A+	61245000
1 MAS LEDspot ND 37W PAR30L E27 830 15D		37	3600	97	36000	15	✗	80	3000	25000	A+	61237500
1 MAS LEDspot ND 41W PAR30L E27 827 30D		41	3900	95	12500	30	✗	80	2700	25000	A+	61241200
1 MAS LEDspot ND 41W PAR30L E27 830 30D		41	4000	98	13000	30	✗	80	3000	25000	A+	61239900

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot PAR38

MASTER LEDspot CLA PAR38

= Dimmable
= Non-dimmable
E27
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 MAS LEDspot CLA ND 9-60W 827 PAR38 25D	60	9	750	83	1800	25	✗	80	2700	15000	A+	71456000
1 MAS LEDspot CLA D 13-100W 827 PAR38 25D	100	13	875	67	4000	25	●	80	2700	25000	A+	71376100

LED spot MV R39

CorePro LEDspot MV R39

= Dimmable
= Non-dimmable
E14
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDspot ND1.8-30W R39 E14 827 36D	30	1.8	150	83	250	36	✗	80	2700	15000	A++	81171900

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot MV R50

CorePro LEDspot MV R50

= Dimmable
= Non-dimmable
E14
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDspot ND1.4-25W R50 E14 827 36D	25	1.4	105	75	210	36	✗	80	2700	15000	A++	81173300
1 CorePro LEDspot ND2.8-40W R50 E14 827 36D	40	2.8	210	75	400	36	✗	80	2700	15000	A++	81175700
1 CorePro LEDspot D 4.3-60W R50 E14 827 36D	60	4.3	320	74	550	36	●	80	2700	15000	A+	81177100

LED spot MV R63

CorePro LEDspot MV R63

= Dimmable
= Non-dimmable
E27
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDspot ND 3-40W R63 E27 827 36D	40	3	210	70	400	36	✗	80	2700	15000	A+	81179500
1 CorePro LEDspot D 4.5-60W R63 E27 827 36D	60	4.5	345	76	620	36	●	80	2700	15000	A+	81181800

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED spot MV R80

CorePro LEDspot MV ND R80

= Dimmable

= Non-dimmable

E27

6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDspot ND 4-60W R80 E27 827 36D	60	4	345	86	620	36	✗	80	2700	15000	A+	81183200
1 CorePro LEDspot ND 8-100W R80 E27 827 36D	100	8	670	83	1100	36	✗	80	2700	15000	A+	81185600

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED linear R7S

1 CorePro LEDlinear R7S ND

2 CorePro LED R7S D



3 CorePro LEDlinear D 17.5

= Dimmable

= Non-dimmable

R7S

10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Luminous Intensity	Beam Angle	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W	cd	°			K	Hrs.		
1 CorePro LEDlinear ND 7.5-60W R7S 78mm 830	60	7.5	950	127	NA	360	✗	80	3000	15000	A++	71394500
1 CorePro LEDlinear ND 7.5-60W R7S 78mm 840		7.5	1000	133	NA	360	✗	80	4000	15000	A++	71396900
2 CorePro LEDlinear D 14-120W R7S 118 830	120	14	2000	143	NA	360	●	80	3000	15000	A++	71400300
3 CorePro LEDlinear D 17.5-150W R7S 118 830	150	17.5	2460	140	NA	360	●	80	3000	15000	A++	64673800
3 CorePro LEDlinear D 17.5-150W R7S 118 840		17.5	2460	140	NA	360	●	80	4000	15000	A++	64675200

LED capsule LV G4

1 CorePro LEDcapsule LV D

2 CorePro LEDcapsule LV

= Dimmable

= Non-dimmable

G4

12 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CorePro LEDcapsule LV 2-20W G4 827 D	20	2	200	100	✗	80	2700	15000	A++	57865000
2 CorePro LEDcapsule LV 2.5-28W G4 827	28	2.5	300	120	✗	80	2700	15000	A++	82694200
2 CorePro LEDcapsule LV 2.5-28W G4 830		2.5	300	120	✗	80	3000	15000	A++	82696600

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED lamps and tubes

LED capsule MV G9

1 CorePro LEDcapsule MV G9 D

2 CorePro LEDcapsule ND G9 25W

3 CorePro LEDcapsule ND G9 40W

4 CorePro LEDcapsule 2-25W

5 CorePro LEDcapsule 3.5-40W

6 CorePro LEDcapsule 3.5-40W

= Dimmable

= Non-dimmable

12 PACK

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
		W	W	lm	lm/W			K	Hrs.		
	1 CorePro LEDcapsule MV 2.3-25W G9 827 D	25	2.3	215	93	●	80	2700	15000	A++	57869800
	2 CorePro LEDcapsule ND 1.9-25W G9 830		1.9	210	111	✕	80	3000	15000	A++	72423100
NEW	4 CorePro LEDcapsule 2-25W ND G9 830 G		2	220	110	✕	80	3000	15000	A++	73502900
NEW	4 CorePro LEDcapsule 2-25W ND G9 827 G		2	200	100	✕	80	2700	15000	A++	73500500
	3 CorePro LEDcapsule ND 3.2-40W G9 830	40	3.2	400	125	✕	80	3000	15000	A++	81528100
NEW	5 CorePro LEDcapsule 3.5-40W ND G9 827 G		3.5	380	108	✕	80	2700	15000	A++	73506700
NEW	6 CorePro LEDcapsule 3.5-40W ND G9 830 G		3.5	400	114	✕	80	3000	15000	A++	73508100

The current transformer compatibility list and dimmer list for low-voltage LED lamps can be found on our website under Cases & Tools on: www.philips.com/ledlamps

LED Bulbs

LED bulb and LED stick E27

= Dimmable
= Non-dimmable
= DimTone
E27
6/10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CorePro LEDbulb 4-32W E27 830	32	4	350	87,5	✗	80	3000	15000	A+	41478100
2 MAS LEDbulb DT 6-40W E27 A60 CL	40	6	470	78	DimTone	80	2200-2700	25000	A+	48128800
3 MAS LEDbulb DT 5.5-40WE27 927-922 A60FR		5.5	470	85	DimTone	90	2200-2700	25000	A+	70709800
4 CorePro LEDbulb ND 5.5-40W A60 E27 827		5.5	470	85	✗	80	2700	15000	A+	57757800
4 CorePro LEDbulb ND 5-40W A60 E27 830		5	470	94	✗	80	3000	15000	A+	57993000
4 CorePro LEDbulb D 5-40W A60 E27 927		5	470	94	●	90	2700	15000	A+	66062800
4 CorePro LEDbulb ND 5-40W A60 E27 840		5	470	94	✗	80	4000	15000	A+	57779000
4 CorePro LEDbulb 6-40W 830 E27		5.5	470	85	✗	80	3000	15000	A+	49756200
5 CorePro LEDbulb 6-40W 840 E27		6	470	78,33	✗	80	4000	15000	A+	51036000
4 CorePro LEDbulb D 6-40W 827 E27		6	470	78,33	●	80	2700	15000	A+	47881300
4 CorePro LEDbulb D 6-40W A60 E27 827		6	470	78	●	80	2700	15000	A+	57749300
2 Corepro LEDbulb ND 6-40W E27 A60 CL		6	470	78	✗	80	2700	15000	A+	57223800
2 MAS LEDbulb DT 8.5-60W E27 A60 CL	60	8.5	806	95	DimTone	80	2200-2700	25000	A+	48132500
3 MAS LEDbulb DT 9-60W E27 927-922 A60 FR		9	806	90	DimTone	90	2200-2700	25000	A+	70711100
5 CorePro LEDbulb D 8.5-60W A60 E27 827		8.5	806	94	●	80	2200-2700	15000	A+	76270700
4 CorePro LEDbulb ND 8-60W A60 E27 827		8	806	100	✗	80	2700	15000	A+	57755400
4 CorePro LEDbulb ND 7.5-60W A60 E27 830		7.5	806	107	✗	80	3000	15000	A+	57771400
4 CorePro LEDbulb ND 8-60W A60E27 827 3CT/8		8	806	100	✗	80	2700	15000	A+	70033100
4 CorePro LEDbulb D 8.5-60W A60 E27 927		8.5	806	94	●	90	2700	15000	A+	66064200
4 CorePro LEDbulb D 8.5-60W A60 E27 827		8.5	806	94	●	80	2700	15000	A+	57747900
5 CorePro LEDbulb D 9.5-60W 827 E27		9.5	806	84,84	●	80	2700	15000	A+	74741300
5 CorePro LEDbulb D 9.5-60W 827 E27		9.5	806	84,84	●	80	2700	15000	A+	47879000
6 MAS LEDbulb DT 12-75WE27 927-922 A67 FR	75	12	1055	88	DimTone	90	2200-2700	25000	A+	82618800
5 CorePro LEDbulb D 11-75W A60 E27 827		11	1055	95	●	80	2200-2700	15000	A+	76274500
4 CorePro LEDbulb ND 10.5-75W A60 E27 830		10.5	1055	100	✗	80	3000	15000	A+	49752400

LED Bulbs

LED bulb and LED stick E27 – Continued

= Dimmable
= Non-dimmable
= DimTone
E27
6/10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
7 CorePro LED Stick ND 9.5-75W T38 E27 840	75	9.5	1050	110	✗	80	4000	15000	A+	81453600
8 MAS LEDbulb DT 14-100WE27 927-922 A67FR		12	1055	87	DimTone	90	2200-2700	25000	A+	69564400
5 CorePro LEDbulb 10.5-75W 865 E27		10.5	1055	105	✗	80	6500	15000	A+	49758600
5 CorePro LEDbulb ND 10-75W A60 E27 840		10	1055	105	✗	80	4000	15000	A+	51032200
5 CorePro LEDbulb ND 10-75W A60 E27 865		10	1055	105	✗	80	6500	15000	A+	49758600
5 CorePro LEDbulb D 11.5-75W A60 E27 827		11.5	1055	91,74	◯	80	2700	15000	A+	47877600
4 CorePro LEDbulb ND 13-100W A60 E27 827	100	13	1521	117	✗	80	2700	15000	A+	49074700
4 CorePro LEDbulb ND 13-100W A60 E27 830		13	1521	117	✗	80	3000	15000	A+	57767700
5 CorePro LEDbulb D 13-100W A60 E27 927		13	1521	117	◯	90	2700	15000	A+	66068000
9 CorePro LEDbulb D 13.5-100W A67 E27 827		13.5	1521	112,67	◯	80	2700	15000	A+	76278300
9 CorePro LEDbulb D 16-100W 827 E27		16	1521	95	◯	80	2700	15000	A+	47875200
5 CorePro LEDbulb ND 12.5-100W A60 E27 840		12.5	1521	121	✗	80	4000	15000	A+	51030800
5 CorePro LEDbulb ND 12.5-100W A60 E27 865		12.5	1521	121	✗	80	6500	15000	A+	57781300
4 CorePro LEDbulb ND 18.5-120W E27 827 A67	120	18.5	2000	108	✗	80	2700	15000	A+	70167600
10 CorePro LEDbulb ND 17-120WA67E27 827FR		17	2000	117	✗	80	2700	15000	A+	66216500
10 CorePro LEDbulb ND 15.5-120WA67E27 840FR		15.5	2000	129	✗	80	4000	15000	A++	66218900
10 CorePro LEDbulb ND 15.5-120WA67E27 865FR		15.5	2000	129	✗	80	6500	15000	A++	70171300
8 CorePro LEDbulb ND 19-150WA67E27 827FR	150	19	2500	131	✗	80	2700	15000	A++	66220200
8 CorePro LEDbulb ND 17.5-150WA67E27 840FR		17.5	2500	142	✗	80	4000	15000	A++	66222600
8 CorePro LEDbulb ND 22.5-150W E27 827 A80		22.5	2500	111.11	✗	80	2700	15000	A+	77035100

LED Bulbs

LED bulb and LED stick E27 – Continued

1 CorePro LEDbulb Non-Dimmable

2 CorePro LEDbulb Dimmable

3 CorePro LEDbulb Dimmable

4 CorePro LEDbulb Non-Dimmable

= Dimmable
= Non-dimmable
= DimTone
E27
6/10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CorePro LEDbulb ND 5.5-40W A60 B22 827	40	5.5	470	85	✗	80	2700	15000	A+	57765300
2 CorePro LEDbulb D 5-40W A60 B22 927		5	470	94	●	90	2700	15000	A+	66070300
2 CorePro LEDbulb D 8.5-60W A60 B22 927	60	8.5	806	94	●	90	2700	15000	A+	66072700
1 CorePro LEDbulb ND 8-60W A60 B22 827		8	806	100	✗	80	2700	15000	A+	57763900
3 CorePro LEDbulb 11-75W 827 B22	75	11	1055	95,91	✗	80	2700	15000	A+	51004900
4 CorePro LEDbulb ND 11-75W A60 B22 827		11	1055	95	✗	80	2700	15000	A+	57761500
3 CorePro LEDbulb D 13-100W A60 B22 927	100	13	1521	117	●	90	2700	15000	A+	66076500
4 CorePro LEDbulb ND 13-100W A60 B22 827		13	1521	117	✗	80	2700	15000	A+	51002500

CORD E27 Accessories

1 CORD classic E27

2 CORD modern E27

4 PACK

Product Type	Traditional	EOC code
	W	
1 CORD/classic/E27/gold 1CT EU	40	16777900
2 CORD/modern/E27/black 1CT EU		16776200

LED Bulbs

Classic LEDbulb E27

= Dimmable
= Non-dimmable
= DimTone
E27
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CLA LEDbulb D 5.5-40W A60 E27 827 CL	40	5.5	470	85	●	80	2700	15000	A+	70940500
9 CLA LED bulb ND 4-40W B22 827 A60 CL		4	470	118	✕	80	2700	15000	A++	76868600
10 CLA LEDbulb D 5-40W A60 B22 827 CL		5.5	470	85	●	80	2700	15000	A+	70942900
1 CLA LEDbulb ND 4.3-40W E27 827 A60 CL		4.3	470	109	✕	80	2700	15000	A++	80867200
1 CLA LEDbulb ND 4-40W A60 E27 827 CL		4.3	470	109	✕	80	2700	15000	A++	63086700
11 CLA LEDbulb D 7.5-48W A60 B22 820 GOLD		7,5	610	81,33	●	80	2000	15000	A+	70958000
5 CLA LEDbulb DT 6.7-40W E27 CRI90 A60 CL		6.7	470	70	DimTone	90	2700-2200	15000	A+	64616500
2 CLA LEDbulb D 8-50W A60 E27 822 GOLD	50	8	630	78	●	80	2200	15000	A+	84154900
1 CLA LEDbulb D 8-60W A60 E27 827 CL	60	8	806	100	●	80	2700	15000	A+	70944300
12 CLA LEDbulb D 8-60W A60 B22 827 CL		8	806	100	●	80	2700	15000	A+	70946700
12 CLA LEDbulb ND 7-60W B22 WW A60 CL		7	806	115	✕	80	2700	15000	A++	74277800
1 CLA LEDbulb ND 7-60W E27 WW A60 CL		7	806	115	✕	80	2700	15000	A++	74273000
6 CLA LEDbulb DT 9-60W E27 CRI90 G93 CL		9	806	89	DimTone	90	2700-2200	15000	A+	64656100
7 CLA LEDbulb 7-60W E27 827 A60 klar3pack		7	806	115	✕	80	2700	15000	A++	71007100
5 CLA LEDbulb DT 9-60W E27 CRI90 A60 CL		9	806	89	DimTone	80	2700-2200	15000	A+	64612700
4 CLA LEDbulb ND 8.5-75W A60 E27 827 CL	75	8.5	1055	124	✕	80	2700	15000	A++	64908100
4 CLA LEDbulb ND 8.5-75W E27 840 A60 CL1CT		8.5	1055	124	✕	80	4000	15000	A++	70424700
3 CLA LEDbulb D 12-100W A67 E27 827 CL	100	12	1521	126	●	80	2700	15000	A++	80631900
4 CLA LEDbulb ND 10.5-100W A60 E27 827 CL		10.5	1521	144	✕	80	2700	15000	A++	64910400
4 CLA LEDbulb ND 10.5-100W E27 840A60CL		10.5	1521	144	✕	80	4000	15000	A++	70412400
8 CLA LEDbulb ND 17-150W A67 E27 827 CL	150	17	2452	144	✕	80	2700	15000	A++	65784000

LED Bulbs

Classic LEDbulb ST64

= Dimmable
= Non-dimmable
= DimTone
E27
6/10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
2 CLA LEDbulb D 8-50W ST64 E27 822 GOLD	50	8	630	78		80	2200	15000	A+	81435200
2 CLA LEDbulb D 7-55W ST64 E27 825 GOLD	55	7	720	103		80	2500	15000	A+	57571000
1 CLA LEDbulb D 8-60W ST64 E27 827 CL	60	8	806	100		80	2700	15000	A+	81427700
1 CLA LEDbulb ND 7-60W E27 WW ST64 CL		7	806	115		80	2700	15000	A++	74275400
4 CLA LEDbulb ND 7-60W B22 WW ST64 CL		7	806	115		80	2700	15000	A++	74279200
3 CLA LEDbulb DT 9-60W E27 CRI90 ST64 CL		9	806	89		90	2700-2200	15000	A+	64652300

Classic LEDbulb spiral

= Dimmable
= Non-dimmable
= DimTone
E14 | E27
2/6/10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CLA LEDbulb SP ND 5-25W E27 GOLD G93 CL	25	5	250	50		80	2000	15000	A	74415400
2 CLA LEDbulb D 5.5-25W A60 E27 GOLD SP CL		5.5	250	45		80	2000	15000	A	68654300
3 CLA LEDbulb D 5.5-25W T32 E27 GOLD SP CL		5.5	250	45		80	2000	15000	A	68658100
4 CLA LEDbulb D 5.5-25W ST64 E27 GOLD SP C		5.5	250	45		80	2000	15000	A	68656700
5 LED classic-giant 40W E27 G200 GOLD DIM	40	6.5	470	72		80	2000	15000	A+	80347900
6 LED classic-giant 40W E27 A160 GOLD DIM		6.5	470	72		80	2000	15000	A+	80349300
7 LED classic-giant 40W E27 T65 GOLD DIM		6.5	470	72		80	2000	15000	A+	80351600

A-Shape LED

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard Incandescent lighting. The unique lamp design provides omni-directional light with excellent dimming performance.

A-Shape LED

1 A-Shape LED 75W A60 E27 WW

2 A-Shape LED 75W A60 E27 CW

3 A-Shape LED 100W A60 E27 CW

4 A-Shape LED 200W A110 E27 WW

5 A-Shape LED 200W A110 E27 CW

6 A-Shape LED 200W A110 E27 CDL

= Dimmable

= Non-dimmable

= DimTone

E27

6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W		°		K	Hrs.		
1 LED 75W A60 E27 WW 230V FR ND 2CT/SRT6	75	11	1055	95	✗	200	80	2700	15000	A+	72697300
2 LED 75W A60 E27 CW 230V FR ND 2CT/SRT6		10	1055	105	✗	200	80	4000	15000	A+	72699700
3 LED 100W A60 E27 CW 230V FR ND 2CT/SRT6	100	12.5	1521	121	✗	200	80	4000	15000	A+	72695900
4 LED 200W A110 E27 WW 230V FR ND 1PF/6	200	30	3450	115	✗	150	80	2700	15000	A+	66224000
5 LED 200W A110 E27 CW 230V FR ND 1PF/6		28	3450	123	✗	150	80	4000	15000	A+	66226400
6 LED 200W A110 E27 CDL 230V FR ND 1PF/6		28	3450	123	✗	150	80	6500	15000	A+	66228800

Benefits:

- Long life properties – lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- Contains no mercury
- Emits virtually no UV/IR light in the beam
- 3-year or 5-year limited warranty depending upon operating hours

LED Bulbs

Classic LEDglobes, giants & eyecatchers

= Dimmable

= Non-dimmable

E27

2/6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
LED classic 15W P45 E27 GOLD SP D SRT4	-	3,5	136	38	●	80	2000	-	A	67611700
5 LEDClassic 12W Heart E27 2000K GOLD ND	12	2.3	125	54.3	✕	80	2000	15000	A+	59349000
1 CLA LEDbulb ND 5-25W E27 2000K A160 GOLD	25	5	300	60	✕	80	2000	15000	A	76810500
6 LED giant 25W E27 A160 4000K smoky D		6.5	270	41.5	●	80	4000	15000	A	81510600
7 LED giant 25W E27 G200 4000K smoky D		6.5	270	41.5	●	80	4000	15000	A	81506900
8 LED giant 25W E27 T65 4000K smoky D		6.5	270	41.5	●	80	4000	15000	A	81512000
12 LED double layers 25W E27 smoky DIM		6.5	270	41	●	80	3000	15000	A	66660600
3 LEDClassic 30W Mushroom E27 2000K GOLD D	30	5	350	70.0	●	90	2000	15000	A+	59351300
11 LED Crystal_giant 35W E27 smoky DIM	35	6.5	400	61	●	80	2700	15000	A	66658300
13 LED diamond_giant 35W E27 CL DIM		4	400	100	●	80	3000	15000	A++	66662000
4 LEDClassic 40W Diamond E27 2700K CL D	40	5	500	100.0	●	80	2700	15000	A+	59353700
1 CLA LEDbulb D 8-50W G120 E27 822 GOLD	50	8	630	78	●	80	2200	15000	A+	81437600
9 LEDClassic 50W G120 E27 2700K CM D		8	700	87.5	●	80	2700	15000	A+	59341400
1 LEDClassic 50W G93 E27 2200K GOLD D		8	630	78.8	●	80	2200	15000	A+	59337700
2 CLA LEDbulb D 8-60W G93 E27 827 CL	60	8	806	100	●	80	2700	15000	A+	81431400
1 CLA LEDbulb ND 7-60W E27 WW G93 CL		7	806	115	✕	80	2700	15000	A++	74271600
10 LEDClassic 60W G120 E27 2700K CL D		8	806	100.8	●	80	2700	15000	A+	59339100

LED Candles & Lusters

LED candle

1 MASTER LEDcandle Clear E14

2 MASTER LEDcandle Clear E27

3 CorePro LEDcandle Frosted

4 MASTER LEDcandle BA38

= Dimmable
= Non-dimmable
= DimTone
E14 | E27
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 MAS LEDcandle DT 4-25W E14 B38 CL	25	4	250	63	DimTone	80	2200-2700	25000	A+	45368100
4 MAS LEDcandle DT 4-25W E14 BA38 CL		4	250	63	DimTone	80	2200-2700	25000	A+	45376600
3 CorePro LEDcandle ND 3.5-25W E14 840 B35 FR		3.5	290	82.86	Non-dimmable	80	4000	15000	A+	54348100
3 CorePro LEDcandle ND 4-25W E14 827 B35 FR		4	250	63	Non-dimmable	80	2700	15000	A+	78701300
1 MAS LEDcandle DT 6-40W E14 B38 CL	40	6	470	78	DimTone	80	2200-2700	25000	A+	45350600
4 MAS LEDcandle DT 6-40W E14 BA38 CL		6	470	78	DimTone	80	2200-2700	25000	A+	45354400
2 MAS LEDcandle DT 6-40W E27 B38 CL		6	470	78	DimTone	80	2200-2700	25000	A+	47479200
3 CorePro LEDcandle ND 5.5-40W E14 827 B35 FR		5.5	470	85	Non-dimmable	80	2700	15000	A+	76238600
3 CorePro LEDcandle ND 5.5-40W E14 840 B35 FR		5.5	520	94.55	Non-dimmable	80	4000	15000	A+	54356600
3 CorePro LEDcandle ND 5.5-40W E14 865 B35 FR		5.5	520	94.55	Non-dimmable	80	6500	15000	A+	74681300
1 MAS LEDcandle DT 8-60W B40 E14 827 CL	60	8	806	101	DimTone	80	2200-2700	25000	A+	55599600
3 CorePro LEDcandle ND 7-60W E14 827 B38 FR		7	806	115	Non-dimmable	80	2700	15000	A++	70299400
3 CorePro LEDcandle ND 7-60W E14 840 B38 FR		7	830	118	Non-dimmable	80	4000	15000	A++	70305200
3 CorePro LEDcandle ND 7-60W E14 865 B38 FR		7	830	118.57	Non-dimmable	80	6500	15000	A++	74685100

LED Candles & Lusters

Classic LEDcandle

1 Classic LEDcandle E14 Gold
2 Classic LEDcandle B35 Clear
3 Classic LEDcandle B35 Frosted
4 Classic LEDcandle BA35 Clear
5 Classic LEDcandle BA35 Frosted
6 Classic LEDcandle ST35 Clear
7 Classic LEDcandle E14 B35
8 Classic LEDcandle B35 GOLD
9 Classic LEDcandle GOLD BA35 Clear
10 Classic LEDcandle B35 Clear
11 Classic LEDcandle BA35 Clear
12 Classic LEDcandle B35 Clear
13 Classic LEDcandle B35 Clear

= Dimmable
= Non-dimmable
= DimTone

E14 | E27
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CLA LEDcandle D 3.5-15W B35 E14 GOLD SP	15	3.5	136	38	✓	80	2000	15000	A	68660400
2 CLA LEDcandle D 2.7-25W B35 E14 827 CL	25	2.7	250	93	✓	80	2700	15000	A++	70980100
2 CLA LEDcandle ND 2-25W B35 E14 827 CL		2	250	125	✗	80	2700	15000	A++	57407200
3 CLA LEDcandle ND 2.2-25W B35 E14 FR		2.2	250	113	✗	80	2700	15000	A++	70637400
4 CLA LEDcandle ND 2-25W BA35 E14 827 CL		2	250	125	✗	80	2700	15000	A++	57409600
5 CLA LEDcandle ND 2.2-25W BA35 E14 FR		2.2	250	113	✗	80	2700	15000	A++	70649700
6 CLA LEDcandle ND 2-25W ST35 E14 827 CL		2	250	125	✗	80	2700	15000	A++	57411900
7 CLA LEDcandle DT 3.5-25W E14 CRI90 B35 CL		3.5	250	71	DimTone	90	2700-2200	15000	A+	64622600
2 CLA LEDcandle ND 2.2-25W E14 840 B35 CL		2.2	250	113	✗	80	4000	15000	A++	64819000
8 CLA LEDcandle D 5-32W B35 E14 822 GOLD	32	5	350	70	✓	80	2200	15000	A+	81439000
9 CLA LEDcandle D 5-32W BA35 E14 822 GOLD		5	350	70	✓	80	2200	15000	A+	81443700
2 CLA LEDcandle D 5-40W B35 E14 827 CL	40	5	470	94	✓	80	2700	15000	A+	70982500
4 CLA LEDcandle D 5-40W BA35 E14 827 CL		5	470	94	✓	80	2700	15000	A+	70996200
2 CLA LEDcandle ND 4.3-40W E14 827 B35 CL		4.3	470	109	✗	80	2700	15000	A++	80853500
3 CLA LEDcandle ND 4.3-40W B35 E14 FR		4.3	470	109	✗	80	2700	15000	A++	70639800
10 CLA LEDcandle DT 6-40W E14 CRI90 B35 CL		6	470	78	DimTone	90	2700-2200	15000	A+	64628800
11 CLA LEDcandle DT 6-40W E14 CRI90 BA35 CL		6	470	78	DimTone	90	2700-2200	15000	A+	64634900
12 CLA LEDcandle ND 4.3-40W E14 840 B35 CL		4.3	470	109	✗	80	4000	15000	A++	64825100
13 CLA LEDcandle ND 6.5-60W B35 E14 827 CL	60	6.5	806	124	✗	80	2700	15000	A++	64912800
13 CLA LEDcandle ND 6.5-60W B35 E14 840 CL		6.5	806	124	✗	80	4000	15000	A++	64914200
3 CLA LEDcandle ND 6.5-60W B35 E14 827 FR		6.5	806	124	✗	80	2700	15000	A++	64922700
3 CLA LEDcandle ND 6.5-60W B35 E14 840 FR		6.5	806	124	✗	80	4000	15000	A++	64924100
3 CLA LEDcandle ND 6.5-60W B35 E14 865 FR		6.5	806	124	✗	80	6500	15000	A++	64926500

LED Candles & Lusters

Classic LEDcandle – Continued

1 Classic LEDcandle B22 Clear
2 Classic LEDcandle B35 Clear
3 Classic LEDcandle B35 Clear
4 Classic LEDcandle B35 Clear

E14 | E27
10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 CLA LEDcandle ND 2-25W B22 827 B35 CL	25	2	250	125	✗	80	2700	15000	A++	64821300
2 CLA LEDcandle ND 2-25W B35 B15 827 CL		2	250	125	✗	80	2700	15000	A++	76688000
1 CLA LEDcandle ND 2-25W B35 B22 827 CL		2	250	125	✗	80	2700	15000	A++	76690300
3 CLA LEDcandle D 5-40W B35 B22 827 CL	40	5	470	94	◐	80	2700	15000	A+	70984900
3 CLA LEDcandle ND 4.3-40W B15 827 B35 CL		4.3	470	109	✗	80	2700	15000	A++	80855900
4 CLA LEDcandle ND 4.3-40W B22 827 B35 CL		4.3	470	109	✗	80	2700	15000	A++	80857300

LED Candles & Lusters

Classic LEDLuster

1 Classic LEDLuster D E14 Clear
2 Classic LEDLuster ND E14 Clear
3 Classic LEDLuster D E27 Clear
4 Classic LEDLuster ND E27 Clear
5 Classic LEDLuster ND E14 Frosted
6 Classic LEDLuster ND E27 Frosted
7 Classic LEDLuster E14 GOLD
8 Classic LEDLuster E27 GOLD
9 Classic LEDbulb E14 Clear
10 Classic LEDLuster E27 Gold
11 Classic LEDLuster E14 Gold
12 Classic LEDLuster E27 Clear
13 Classic LEDLuster E14 Clear
14 Classic LEDLuster E14 Clear
15 Classic LEDLuster B22 Clear

= Dimmable
= Non-dimmable
= DimTone

E14 | E27

10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
10 CLA LEDLuster D 3.5-15W P45 E27 GOLD SP	15	3.5	136	38	●	80	2000	15000	A	68662800
11 CLA LEDLuster D 3.5-15W P45 E14 GOLD SP		3.5	136	38	●	80	2000	15000	A	68664200
1 CLA LEDLuster D 2.7-25W P45 E14 827 CL	25	2.7	250	93	●	80	2700	15000	A++	70986300
3 CLA LEDLuster D 2.7-25W P45 E27 827 CL		2.7	250	93	●	80	2700	15000	A++	70988700
2 CLA LEDLuster ND 2-25W P45 E14 827 CL		2	250	125	✕	80	2700	15000	A++	57413300
4 CLA LEDLuster ND 2-25W P45 E27 827 CL		2	250	125	✕	80	2700	15000	A++	57415700
15 CLA LEDLuster ND 2-25W P45 B22 827 CL		2	250	125	✕	80	2700	15000	A++	76696500
5 CLA LEDLuster ND 2.2-25W P45 E14 FR		2.2	250	113	✕	80	2700	15000	A++	70641100
6 CLA LEDLuster ND 2.2-25W P45 E14 FR		2.2	250	114	✕	80	2700	15000	A++	70645900
12 CLA LEDLuster DT 3.5-25W E27 CRI90 P45 CL		3.5	250	71	DimTone	90	2700-2200	15000	A+	64636300
13 CLA LEDLuster DT 3.5-25W E14 CRI90 P45 CL		3.5	250	71	DimTone	90	2700-2200	15000	A+	64638700
7 CLA LEDLuster D 5-32W P45 E14 822 GOLD	32	5	350	70	●	80	2200	15000	A+	81567000
8 CLA LEDLuster D 5-32W P45 E27 822 GOLD		5	350	70	●	80	2200	15000	A+	81441300
1 CLA LEDLuster D 5-40W P45 E14 827 CL	40	5	470	94	●	80	2700	15000	A+	70990000
3 CLA LEDLuster D 5-40W P45 E27 827 CL		5	470	94	●	80	2700	15000	A+	70992400
15 CLA LEDLuster D 5-40W P45 B22 827 CL		5	470	94	●	80	2700	15000	A+	70994800
2 CLA LEDLuster ND 4.3-40W E14 827 P45 CL		4.3	470	109	✕	80	2700	15000	A++	80971600
5 CLA LEDLuster ND 4.3-40W P45 E14 FR		4.3	470	109	✕	80	2700	15000	A++	70643500
4 CLA LEDLuster ND 4.3-40W E27 827 P45 CL		4.3	470	109	✕	80	2700	15000	A++	80973000
6 CLA LEDLuster ND 4.3-40W P45 E27 FR		4.3	470	109	✕	80	2700	15000	A++	70647300
12 CLA LEDLuster DT 6-40W E27 CRI90 P45 CL		6	470	78	DimTone	90	2700-2200	15000	A+	64642400
9 CLA LEDLuster ND 4.3-40W E14 840 P45 CL		4.3	470	109	✕	80	4000	15000	A++	64827500
14 CLA LEDLuster ND 6.5-60W P45 E14 827 CL	60	6.5	806	124	✕	80	2700	15000	A++	64916600
14 CLA LEDLuster ND 6.5-60W P45 E14 840 CL		6.5	806	124	✕	80	4000	15000	A++	64918000
5 CLA LEDLuster ND 6.5-60W P45 E14 827 FR		6.5	806	124	✕	80	2700	15000	A++	64928900

LED Candles & Lusters

Classic LEDLuster – Continued

4 Classic LEDLuster ND E27 Clear

5 Classic LEDLuster ND E14 Frosted

6 Classic LEDLuster ND E27 Frosted

= Dimmable

= Non-dimmable

E14 | E27

10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
5 CLA LEDLuster ND 6.5-60W P45 E14 840 FR		6.5	806	124	✗	80	4000	15000	A++	64930200
5 CLA LEDLuster ND 6.5-60W P45 E14 865 FR		6.5	806	124	✗	80	6500	15000	A++	64932600
4 CLA LEDLuster ND 6.5-60W P45 E27 827 CL	60	6.5	806	124	✗	80	2700	15000	A++	64920300
6 CLA LEDLuster ND 6.5-60W P45 E27 827 FR		6.5	806	124	✗	80	2700	15000	A++	64934000
6 CLA LEDLuster ND 6.5-60W P45 E27 840 FR		6.5	806	124	✗	80	4000	15000	A++	64936400

LED Candles & Lusters

LED luster

1 MASTER LEDLustre CL E14

2 CorePro Lustre Clear E14

3 CorePro Lustre Frosted E14

4 MASTER LEDLustre Clear E27

5 CorePro Lustre Clear E27

6 CorePro Lustre Frosted E27

7 CorePro Lustre Frosted E27

= Dimmable

= Non-dimmable

= DimTone

E14 | E27

10 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 MAS LEDlustre DT 4-25W E14 P48 CL	25	4	250	63	DimTone	80	2200-2700	25000	A+	45378000
4 MAS LEDlustre DT 4-25W E27 P48 CL		4	250	63	DimTone	80	2200-2700	25000	A+	45380300
3 CorePro lustre ND 3.5-25W E14 840 P45 FR		3.5	290	83	Non-dimmable	80	4000	15000	A+	54352800
6 CorePro lustre ND 4-25W E27 827 P45 FR		4	250	63	Non-dimmable	80	2700	15000	A+	78705100
2 CorePro lustre ND 4-25W E14 827 P45 CL		4	250	63	Non-dimmable	80	2700	15000	A+	50759900
5 CorePro lustre ND 4-25W E27 827 P45 CL		4	250	63	Non-dimmable	80	2700	15000	A+	50767400
6 CorePro lustre ND 4-25W E27 827 P45 FR		4	250	63	Non-dimmable	80	2700	15000	A+	78705100
3 CorePro lustre ND 4-25W E14 827 P45 FR		4	250	63	Non-dimmable	80	2700	15000	A+	78703700
1 MAS LEDlustre DT 6-40W E14 P48 CL	40	6	470	78	DimTone	80	2200-2700	25000	A+	45358200
4 MAS LEDlustre DT 6-40W E27 P48 CL		6	470	78	DimTone	80	2200-2700	25000	A+	45360500
2 CorePro lustre ND 5.5-40W E14 827 P45 CL		5.5	470	91	Non-dimmable	80	2700	15000	A+	45483100
5 CorePro lustre ND 5.5-40W E27 827 P45 CL		5.5	470	91	Non-dimmable	80	2700	15000	A+	50763600
6 CorePro lustre ND 5.5-40W E27 827 P45 FR		5.5	470	91	Non-dimmable	80	2700	15000	A+	50765000
3 CorePro lustre ND 5.5-40W E14 827 P45 FR		5.5	470	85	Non-dimmable	80	2700	15000	A+	47489100
2 Corepro lustre ND 5.5-40W E14 840 P45 CL		5.5	520	95	Non-dimmable	80	4000	15000	A+	54344300
3 CorePro lustre ND 5.5-40W E14 840 P45 FR		5.5	520	95	Non-dimmable	80	4000	15000	A+	54360300
3 CorePro lustre ND 5.5-40W E14 865 P45 FR		5.5	520	95	Non-dimmable	80	6500	15000	A+	74683700
1 MAS LEDlustre DT 8-60W P50 E14 827 CL	60	8	806	101	DimTone	80	2200-2700	25000	A+	58067700
3 CorePro lustre ND 7-60W E14 827 P48 FR		7	806	115	Non-dimmable	80	2700	15000	A++	70301400
6 CorePro lustre ND 7-60W E27 827 P48 FR		7	806	115	Non-dimmable	80	2700	15000	A++	70303800
3 CorePro lustre ND 7-60W E14 840 P48 FR		7	830	118	Non-dimmable	80	4000	15000	A++	70307600
3 CorePro lustre ND 7-60W E14 865 P48 FR		7	830	118	Non-dimmable	80	6500	15000	A++	74687500
7 CorePro lustre ND 7-60W E27 840 P48 FR		7	830	118	Non-dimmable	80	4000	15000	A++	70309000

Philips **LEDtube** The right LEDtube every time

Industry leading LED range of fluorescent tube replacements

- Best in class lumen performance
- Best compatibility
- Easy installation

For general applications, Universal is the tube of choice.

For more demanding applications: use our Selector tool.

Find the **right** solution in our range using the **Selector tool productfinder.lighting.philips.com**

MASTER Value LEDtube Universal T8

NEW

- Universal compatibility – compatible with all kinds of driver technologies (EM ballast, HF ballasts and direct mains)
- Glass platform – uniform light (large beam angle 240D – suitable for many applications)
- Ultra high lumen package – up to 3700 lumen
- InstantFit technology – for largest HF ballast compatibility, safety and ease and speed of installation

CorePro LEDtube T8 Universal

- Works on every driver technology (EM/HF/Mains)
- Up to 2700 lumen output
- 1 year typical payback time for 24/7 operation*
- Up to 3x longer lifetime*

MASTER LEDtube T5

- 50,000 hours lifetime
- Up to 155 lumen/Watt
- Up to 5600 lumen output

MASTER LEDtube T8 sensor

- Integrated motion sensor
- Automatic dimming based on movement
- No extra sensors or wiring needed
- Up to 70% energy saving*

CorePro LED PL-C, PL-L, PL-S & LED Circular

- Simple retrofit for fluorescent PL-C and PL-L lamps
- 30,000 hours life time
- Up to 60% energy saving*

*Compared to fluorescent lamps

LED Tubes

LED tube T8 / EM & MAINS

www.philips.com/ledtube

1 MASTER LEDtube EM

2 CorePro LED tube EM

3 MASTER LEDtube UE*

4 MASTER Value LEDtube T8

1 3 = ROTATING END (ONLY THE MASTER RANGE)

G13

10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube 600mm HO 8W840 T8	8	1050	131	160	83	4000	60000	A++	69749800
3 MAS LEDtube 600mm HO 8W865 T8	8	1050	131	160	83	6500	60000	A++	69751100
1 MAS LEDtube 600mm HO 8W830 T8	8	1000	125	160	83	3000	60000	A++	69747400
2 CorePro LEDtube 600mm 8W840	8	800	100	240	80	4000	30000	A+	71103300
2 CorePro LEDtube 600mm 8W865	8	800	100	240	80	6500	30000	A+	71105700
4 MAS LEDtube VLE 600mm HO 8W 830 T8	8	1000	125	240	83	3000	50000	A++	64679000
4 MAS LEDtube VLE 600mm HO 8W 840 T8	8	1050	131	240	83	4000	50000	A++	64681300
4 MAS LEDtube VLE 600mm HO 8W 865 T8	8	1050	131	240	83	6500	50000	A++	64683700
1 MAS LEDtube 900mm HO 12W 840 T8	12	1575	131	160	83	4000	60000	A++	68708600
2 MAS LEDtube 900mm HO 12W 865 T8	12	1575	131	160	83	6500	60000	A++	68710900
4 MAS LEDtube VLE 1200mm HO 14W 830 T8	14	2000	143	240	83	3000	50000	A++	64685100
4 MAS LEDtube VLE 1200mm HO 14W 840 T8	14	2100	150	240	83	4000	50000	A++	64687500
4 MAS LEDtube VLE 1200mm HO 14W 865 T8	14	2100	150	240	83	6500	50000	A++	64689900
3 MAS LEDtube 1200mm UE 14.5W 840 T8	14.5	2500	172	160	83	4000	70000	A++	73150500
3 MAS LEDtube 1200mm UE 14.5W 865 T8	14.5	2500	172	160	83	6500	70000	A++	73152900
1 MAS LEDtube 1200mm UO 16W 830 T8	16	2300	144	160	83	3000	50000	A++	68736900
1 MAS LEDtube 1200mm UO 16W 840 T8	16	2500	156	160	83	4000	50000	A++	68738300
1 MAS LEDtube 1200mm UO 16W 865 T8	16	2500	156	160	83	6500	50000	A++	68740600
4 MAS LEDtube VLE 1200mm UO 16W 830 T8	16	2300	144	240	83	3000	50000	A++	64697400
4 MAS LEDtube VLE 1200mm UO 16W 840 T8	16	2500	156	240	83	4000	50000	A++	64699800
4 MAS LEDtube VLE 1200mm UO 16W 865 T8	16	2500	156	240	83	6500	50000	A++	64701800
1 MAS LEDtube 1200mm HO 12.5W 830 T8	12.5	2000	160	160	80	3000	60000	A++	59235600
1 MAS LEDtube 1200mm HO 12.5W 840 T8	12.5	2100	168	160	80	4000	60000	A++	59237000
3 MAS LEDtube 1200mm HO 12.5W 865 T8	12.5	2100	168	160	80	6500	60000	A++	59239400
2 CorePro LEDtube 1200mm HO 18W 840 T8	18	2000	111	240	80	4000	30000	A+	80613500
2 CorePro LEDtube 1200mm 14.5W 840	14.5	1600	110	240	80	4000	30000	A+	71107100

* "UE" stands for Ultra Efficiency. These LED tubes are identical to the Ultra Output range but have a much higher efficiency (172 Lm / W)

LED Tubes

LED tube T8 / EM & MAINS

www.philips.com/ledtube

1 MASTER LEDtube EM

2 CorePro LED tube EM

3 MASTER LEDtube UE*

4 MASTER Value LEDtube T8

NEW

1 3 = ROTATING END (ONLY THE MASTER RANGE)

G13

10 PACK

	Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
		W	lm	lm/W	°		K	Hrs.		
	1 CorePro LEDtube 1200mm 14.5W865	14.5	1600	110	240	80	6500	30000	A+	71109500
	1 MAS LEDtube 1200mm UO 15.5W 830 T8	15.5	2300	148	160	83	3000	50000	A++	64721600
	1 MAS LEDtube 1200mm UO 15.5W 840 T8	15.5	2500	161	160	83	4000	50000	A++	64723000
	1 MAS LEDtube 1200mm UO 15.5W 865 T8	15.5	2500	161	160	83	6500	50000	A++	64725400
	1 MAS LEDtube 1500mm UO 23W 830 T8	23	3400	148	160	83	3000	50000	A++	64727800
	1 MAS LEDtube 1500mm UO 23W 840 T8	23	3700	161	160	83	4000	50000	A++	64729200
	1 MAS LEDtube 1500mm UO 23W 865 T8	23	3700	161	160	83	6500	50000	A++	64731500
	4 MAS LEDtube VLE 1500mm UO 24W 830 T8	24	3400	142	240	83	3000	50000	A++	64703200
	4 MAS LEDtube VLE 1500mm UO 24W 840 T8	24	3700	154	240	83	4000	50000	A++	64705600
	4 MAS LEDtube VLE 1500mm UO 24W 865 T8	24	3700	154	240	83	6500	50000	A++	64707000
	4 MAS LEDtube VLE 1500mm HO 20.5W 830 T8	20.5	2900	141	240	83	3000	50000	A++	64691200
	4 MAS LEDtube VLE 1500mm HO 20.5W 840 T8	20.5	3100	151	240	83	4000	50000	A++	64693600
	4 MAS LEDtube VLE 1500mm HO 20.5W 865 T8	20.5	3100	151	240	83	6500	50000	A++	64695000
	3 MAS LEDtube 1500mm UE 21.5W 840 T8	21.5	3700	172	160	83	4000	70000	A++	73154300
	3 MAS LEDtube 1500mm UE 21.5W 865 T8	21.5	3700	172	160	83	6500	70000	A++	73156700
	1 MAS LEDtube 1500mm UO 24W 830 T8	24	3400	142	160	83	3000	50000	A++	68742000
	1 MAS LEDtube 1500mm UO 24W 840 T8	24	3700	154	160	83	4000	50000	A++	68744400
	1 MAS LEDtube 1500mm UO 24W 865 T8	24	3700	154	160	83	6500	50000	A++	68746800
	1 MAS LEDtube 1500mm HO 18.2W 830 T8	18.2	2900	159	160	80	3000	50000	A++	59241700
	1 MAS LEDtube 1500mm HO 18.2W 840 T8	18.2	3100	170	160	80	4000	50000	A++	59243100
	1 MAS LEDtube 1500mm HO 18.2W 865 T8	18.2	3100	170	160	80	6500	50000	A++	59245500
	2 CorePro LEDtube 1500mm HO 24W 840 T8	24	2700	113	240	80	4000	30000	A+	80617300
	2 CorePro LEDtube 1500mm 20W 840	20	2200	110	240	80	4000	30000	A+	71091300
	2 CorePro LEDtube 1500mm 20W 865	20	2200	110	240	80	6500	30000	A+	71095100
NEW	4 MAS LEDtube VLE UN 1200mm UO 16W830 T8	16	2300	144	240	84	3000	50000	A++	73917100
NEW	4 MAS LEDtube VLE UN 1200mm UO 16W840 T8	16	2500	156	240	85	4000	50000	A++	73919500
NEW	4 MAS LEDtube VLE UN 1200mm UO 16W865 T8	16	2501	156	240	86	6500	50000	A++	73921800
NEW	4 MAS LEDtube VLE UN 1500mm UO 24W830 T8	24	3400	142	240	87	3000	50000	A++	73923200
NEW	4 MAS LEDtube VLE UN 1500mm UO 24W840 T8	24	3700	154	240	88	4000	50000	A++	73925600
NEW	4 MAS LEDtube VLE UN 1500mm UO 24W865 T8	24	3700	154	240	89	6500	50000	A++	73927000

* "UE" stands for Ultra Efficiency. These LED tubes are identical to the Ultra Output range but have a much higher efficiency (172 Lm / W)

LED Tubes

LED tube T8 / InstantFit (HF)

MASTER LEDtube HF 1

CorePro LEDtube HF 2

FRAGILE

1 = ROTATING END (ONLY THE MASTER RANGE)

G13

10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube HF 600mm HO 8W830 T8	8	1000	125	160	83	3000	50000	A+	74353900
1 MAS LEDtube HF 600mm HO 8W840 T8	8	1050	131	160	83	4000	50000	A+	74355300
1 MAS LEDtube HF 600mm HO 8W865 T8	8	1050	131	160	83	6500	50000	A+	74367600
2 CorePro LEDtube HF 600mm 9W840 T8 G	9	800	89	240	83	4000	30000	A	65217600
2 CorePro LEDtube HF 600mm 9W865 T8 G	9	800	89	240	83	6500	30000	A	65219000
1 MAS LEDtube HF 1200mm UO 16W840 T8	16	2500	156	160	83	4000	50000	A++	68796300
1 MAS LEDtube HF 1200mm UO 16W865 T8	16	2500	156	160	83	6500	50000	A++	68798700
1 MAS LEDtube HF 1200mm UO 16W830 T8	16	2350	147	160	83	3000	50000	A+	68800700
1 MAS LEDtube HF 1200mm HO 14W840 T8	14	2100	150	160	83	4000	50000	A++	68748200
1 MAS LEDtube HF 1200mm HO 14W865 T8	14	2100	150	160	83	6500	50000	A++	68750500
1 MAS LEDtube HF 1200mm HO 14W830 T8	14	2000	143	160	83	3000	50000	A+	68752900
2 CorePro LEDtube HF 1200mm 15W840 T8 G	15	1600	107	240	83	4000	30000	A+	58127800
2 CorePro LEDtube HF 1200mm 15W865 T8 G	15	1600	107	240	83	6500	30000	A+	58129200
1 MAS LEDtube HF 1500mm UO 24W840 T8	24	3700	154	160	83	4000	50000	A++	68802100
1 MAS LEDtube HF 1500mm UO 24W865 T8	24	3700	154	160	83	6500	50000	A++	68804500
1 MAS LEDtube HF 1500mm UO 24W830 T8	24	3500	146	160	83	3000	50000	A++	68806900
1 MAS LEDtube HF 1500mm HO 20W840 T8	20	3100	155	160	83	4000	50000	A++	68754300
1 MAS LEDtube HF 1500mm HO 20W865 T8	20	3100	155	160	83	6500	50000	A++	68756700
1 MAS LEDtube HF 1500mm HO 20W830 T8	20	2900	145	160	83	3000	50000	A+	68758100
2 CorePro LEDtube HF 1500mm 20W840 T8 G	20	2000	100	240	83	4000	30000	A+	59203800
2 CorePro LEDtube HF 1500mm 20W865 T8 G	20	2000	100	240	83	6500	30000	A+	59205200

LED Tubes

LED tube T8 / Universal (EM, Mains & HF)

MASTER LEDtube T8 / Universal 1

2

1 = ROTATING END G13 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube UN 1200mm UO 16W830 T8	16	2300	144	160	83	3000	50000	A++	72853600
1 MAS LEDtube UN 1200mm UO 16W840 T8	16	2500	156	160	83	4000	50000	A++	70537700
1 MAS LEDtube UN 1200mm UO 16W865 T8	16	2500	156	160	83	6500	50000	A++	70539100
2 CorePro LEDtube UN 1200mm HO 18W830 T8	18	1850	103	240	80	3000	30000	A+	80166600
2 CorePro LEDtube UN 1200mm HO 18W865 T8	18	2000	111	240	80	6500	30000	A+	80170300
2 CorePro LEDtube UN 1200mm HO 18W840 T8	18	2000	111	240	80	4000	30000	A+	80168000
2 CorePro LEDtube UN 1500mm HO 23W840 T8	23	2700	117	240	80	4000	30000	A+	80174100
2 CorePro LEDtube UN 1500mm HO 23W830 T8	23	2500	109	240	80	3000	30000	A+	80172700
2 CorePro LEDtube UN 1500mm HO 23W865 T8	23	2700	117	240	80	6500	30000	A+	80176500
1 MAS LEDtube UN 1500mm UO 24W830 T8	24	3400	142	160	83	3000	50000	A++	72851200
1 MAS LEDtube UN 1500mm UO 24W840 T8	24	3700	154	160	83	4000	50000	A++	70533900
1 MAS LEDtube UN 1500mm UO 24W865 T8	24	3700	154	160	83	6500	50000	A++	70535300

Dummy starter is always included with the EM / Mains and Universal LED tube.

Consult the ballast compatibility list for LED tubes via: www.philips.com/ledtube

LED Tubes

LED tube T8 / Specialties

MASTER LEDtube T8 Food 1

MASTER LEDtube HF Food 2

MASTER LEDtube sensor 3

1 2 = ROTATING END G13 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube 900mm 8.5W833 T8 FOOD	8.5	750	88	160	83	3300	50000	A+	76391900
1 MAS LEDtube 1200mm 12W833 T8 FOOD	12	1000	83	160	83	3300	50000	A+	76393300
2 MAS LEDtube HF 1200mm 16.5W833 T8 FOOD	16.5	1000	61	160	83	3300	50000	B	56616900
3 MAS LEDtube Sensor 1200mm HO 16.5W840 T8		2100	127	240	80	4000	50000	A++	80602900
3 MAS LEDtube Sensor 1200mm HO 16.5W865 T8		2100	127	240	80	6500	50000	A++	80604300
1 MAS LEDtube 1500mm 20W833 T8 FOOD	20	1680	84	160	83	3300	50000	A+	76395700
3 MAS LEDtube Sensor 1500mm HO 24W840 T8	24	3100	129	240	80	4000	50000	A++	80606700
3 MAS LEDtube Sensor 1500mm HO 24W865 T8		3100	129	240	80	6500	50000	A++	80608100

LED tube T5 / HF: High Output & Ultra Output

MASTER LEDtube T5 / HO 1

ROTATING END G5 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube HF 1500mm HO 26W 830 T5	26	3700	142	160	83	3000	50000	A+	68552500
1 MAS LEDtube HF 1500mm HO 26W 840 T5	26	3900	150	160	83	4000	50000	A++	68554900
1 MAS LEDtube HF 1500mm HO 26W 865 T5	26	3900	150	160	83	6500	50000	A++	68556300
1 MAS LEDtube HF 1200mm HO 26W 830 T5	26	3700	142	160	83	3000	50000	A+	70527800
1 MAS LEDtube HF 1200mm HO 26W 840 T5	26	3900	150	160	83	4000	50000	A++	70529200
1 MAS LEDtube HF 1200mm HO 26W 865 T5	26	3900	150	160	83	6500	50000	A++	70531500
1 MAS LEDtube HF 1500mm UO 36W 830 T5	36	5200	144	160	83	3000	50000	A++	70599500
1 MAS LEDtube HF 1500mm UO 36W 840 T5	36	5600	156	160	83	4000	50000	A++	70603900
1 MAS LEDtube HF 1500mm UO 36W 865 T5	36	5600	156	160	83	6500	50000	A++	70605300

LED Tubes

LED tube T5 / HF: High Efficiency

MASTER LEDtube T5 / HE 1

FRAGILE ROTATING END G5 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube HF 600mm HE 8W 830 T5	8	1000	125	200	83	3000	50000	A+	74323200
1 MAS LEDtube HF 600mm HE 8W 840 T5	8	1050	131	200	83	4000	50000	A+	74325600
1 MAS LEDtube HF 600mm HE 8W 865 T5	8	1050	131	200	83	6500	50000	A+	74327000
1 MAS LEDtube HF 1200mm HE 16.5W 830 T5	16.5	2300	139	200	83	3000	50000	A+	74329400
1 MAS LEDtube HF 1200mm HE 16.5W 840 T5	16.5	2500	152	200	83	4000	50000	A++	74331700
1 MAS LEDtube HF 1200mm HE 16.5W 865 T5	16.5	2500	152	200	83	6500	50000	A++	74333100
1 MAS LEDtube HF 1500mm HE 20W 830 T5	20	2800	140	200	83	3000	50000	A+	74335500
1 MAS LEDtube HF 1500mm HE 20W 840 T5	20	3000	150	200	83	4000	50000	A++	74337900
1 MAS LEDtube HF 1500mm HE 20W 865 T5	20	3000	150	200	83	6500	50000	A++	74339300

LED tube T5 / Mains: High Output

MASTER LEDtube T5 / Mains HO 1

These T5 LED tubes only work directly on mains (MAINS)

FRAGILE ROTATING END G5 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 MAS LEDtube 1500mm HO 26W 830 T5	26	3600	138	200	80	3000	50000	A++	81929600
1 MAS LEDtube 1500mm HO 26W 840 T5	26	3900	150	200	80	4000	50000	A++	81931900
1 MAS LEDtube 1500mm HO 26W 865 T5	26	3900	150	200	80	6500	50000	A++	81933300
1 MAS LEDtube 1200mm HO 26W 830 T5	26	3600	138	200	80	3000	50000	A++	81921000
1 MAS LEDtube 1200mm HO 26W 840 T5	26	3900	150	200	80	4000	50000	A++	81923400
1 MAS LEDtube 1200mm HO 26W 865 T5	26	3900	150	200	80	6500	50000	A++	81925800

LED Tubes & PL-lamps

LED starter

LED Starter

40 PACK

Product Type	EOC code
1 MASTER LEDtube Starter EMP GenII OP	81965400

LED PL-C / 2-pins

CorePro LED PL-C / 2-pins

Improved light output

ROTATING END

G24d-1 / G24d-2 / G24d-3

10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 CorePro LED PLC 4.5W 830 2P G24d-1	4.5	475	106	160	83	3000	30000	A++	70659600
1 CorePro LED PLC 4.5W 840 2P G24d-1	4.5	500	111	160	83	4000	30000	A++	70661900
1 CorePro LED PLC 6.5W 830 2P G24d-2	6.5	600	92	160	83	3000	30000	A+	54127200
1 CorePro LED PLC 6.5W 840 2P G24d-2	6.5	650	100	160	83	4000	30000	A+	54129600
1 CorePro LED PLC 8.5W 830 2P G24d-3	8.5	900	106	160	83	3000	30000	A+	54123400
1 CorePro LED PLC 8.5W 840 2P G24d-3	8.5	950	112	160	83	4000	30000	A+	54125800

LED PL-lamps

LED PL-C / 4-pins

CorePro LED PL-C / 4-pins

Consult the ballast compatibility list for PL-C lamps via: www.philips.com/ledtube

Improved light output | ROTATING END | G24q-1 / G24q-2 / G24q-3 | 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 CorePro LED PLC 4.5W 830 4P G24q-1	4.5	475	106	160	83	3000	30000	A+	70663300
1 CorePro LED PLC 4.5W 840 4P G24q-1	4.5	500	111	160	83	4000	30000	A+	70665700
1 CorePro LED PLC 6.5W 830 4P G24q-2	6.5	600	92	160	83	3000	30000	A+	54119700
1 CorePro LED PLC 6.5W 840 4P G24q-2	6.5	650	100	160	83	4000	30000	A+	54121000
1 CorePro LED PLC 9W 830 4P G24q-3	9	900	100	160	83	3000	30000	A+	54115900
1 CorePro LED PLC 9W 840 4P G24q-3	9	950	106	160	83	4000	30000	A+	54117300

LED PL-L

CorePro LED PL-L

ROTATING END | 2G11 | 10 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 CorePro LED PLL HF 16.5W 830 4P 2G11	17	2000	121	160	83	3000	30000	A+	73966200
1 CorePro LED PLL HF 16.5W 840 4P 2G11	17	2100	127	160	83	4000	30000	A+	73974700
1 CorePro LED PLL HF 16.5W 865 4P 2G11	17	2100	127	160	83	6500	30000	A+	73976100
1 CorePro LED PLL HF 24W 830 4P 2G11	24	3200	133	160	80	3000	30000	A+	82839700
1 CorePro LED PLL HF 24W 840 4P 2G11	24	3400	142	160	80	4000	30000	A+	82841000
1 CorePro LED PLL HF 24W 865 4P 2G11	24	3400	142	160	80	6500	30000	A+	82843400

LED PL-lamps

LED PL-S

1 CorePro LED PL-S

ROTATING END | PL-S | 20 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 CorePro LED PLS 5W 830 2P G23	5	520	104	120	80	3000	30000	A+	59666800
1 CorePro LED PLS 5W 840 2P G23	5	550	110	120	80	4000	30000	A+	59668200

CorePro LED tube Circular

1 CorePro LED Circular

G10q | 20 PACK

Product Type	LED	Lumen Output	Efficacy	Beam Angle	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	lm	lm/W	°		K	Hrs.		
1 CorePro LED PLC CorePro LED Circular 20W 840 G10q	20	2100	105	120	80	4000	30000	A+	66042000
1 CorePro LED PLC CorePro LED Circular 20W 865 G10q	20	2100	105	120	80	6500	30000	A+	66044400

Philips **TrueForce LED lamps**

Save energy and provide the perfect light for every space

Up to 50% energy savings*

6 kV surge protection

Plug & play: EM system compatible

High efficiency (>170 lm/W)

Industry leading LED lamps for HID replacement:

- Powerful light output, optically efficient
- Instant upgrade – no need to replace or modify fixture
- 50,000 hours life time, 5 years warranty

TrueForce LED **Road**

More features at a glance

PERFECT FIT — Using existing optics of conventional luminaire

CRI 180 — Pleasant white light with CRI 70

Optically efficient, emits light towards direction of use

TrueForce LED
Industrial and Retail

- Plug & play: EM system compatible
- Up to 65% energy savings*
- Pleasant white light (CRI 80)
- IP 40 rating

* Compared to conventional systems

TrueForce LED
Core HPL

- Similar look and feel as conventional HID SON/HPL lamps
- Perfect fit in HID luminaries on existing EM ballast or mains connection
- IP65 design suitable for indoor and outdoor applications

NEW

TrueForce LED Public (Urban/Road – HPL/SON)

The affordable LED solution for High Intensity Discharge (HID) lamp replacement, Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) lamps.

TrueForce LED Public (Urban/Road – HPL/SON)

www.philips.com/trueforce-led-lamps

1 TrueForce Urban 21W

2 TrueForce Urban 28W

3 TrueForce Urban 42W

4 TrueForce Urban 42W E40

= Dimmable
= Non-dimmable
E27
E40
6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce LED HPL ND 28-21W E27 830	80	21	2850	135	✗	80	3000	50000	A++	63814600
1 TForce LED HPL ND 30-21W E27 840	80	21	3000	142	✗	80	4000	50000	A++	63816000
2 TForce LED HPL ND 38-28W E27 830	125	28	3800	135	✗	80	3000	50000	A++	63818400
2 TForce LED HPL ND 40-28W E27 840	125	28	4000	142	✗	80	4000	50000	A++	63820700
3 TForce LED HPL ND 57-42W E27 830	125	42	5700	135	✗	80	3000	50000	A++	63822100
3 TForce LED HPL ND 60-42W E27 840	125	42	6000	142	✗	80	4000	50000	A++	63824500
4 TForce LED HPL ND 57-42W E40 830	200	42	5700	135	✗	80	3000	50000	A++	63826900
4 TForce LED HPL ND 60-42W E40 840	200	42	6000	142	✗	80	4000	50000	A++	63828300

TrueForce LED Public (Road/Area – SOX)

Philips TrueForce LED SOX lamp and external LED driver enhance the light quality with comfort and safety without having to replace the fixtures or sacrifice the light effect. An optional dimming function, for use at lower traffic intensities, it gives additional opportunities for energy savings.

TrueForce LED Public (Road/Area – SOX)

1 TrueForce LED SOX

This lamp only works with a specific LED driver*

= Dimmable

= Non-dimmable

B22d

6/20 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce LED SOX D 25-19W B22 740 FR	SOX 26W/35W	19	2500	131	◯	70	4000	50000	A+	78201900
1 TForce LED SOX D 40-31W B22d 740 FR	SOX 36W/55W	31	4000	129	◯	70	4000	50000	A+	69938600

TrueForce Core LED HPL

NEW

The new Philips TrueForce Core LED HPL lamps offer an easy and short payback solution to replace High Intensity Discharge (HID) lamps. They bring all the energy efficiency and long-life benefits of LED to HID replacement, while providing instant saving and low initial investment.
PerfectFit: Philips TrueForce Core LED HPL is designed with an optimal lamp size and light distribution in a familiar look & feel with conventional HID lamps. Its unique High-Power LED filament technology in a full glass bulb makes it possible. What's more, their special IP65 design means they can easily be retrofitted for outdoor and indoor applications.

TrueForce Core LED HPL

1 TrueForce Core LED HPL - 13W

2 TrueForce Core LED HPL - 18W

3 TrueForce Core LED HPL - 26W

= Dimmable

= Non-dimmable

E27

4 PACK

	Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
		W	W	lm	lm/W			K	Hrs.		
NEW	1 TForce Core LED HPL 13W E27 830 FR	50	13	2000	154	✕	80	3000	25000	A++	75025100
NEW	1 TForce Core LED HPL 13W E27 840 FR		13	2000	154	✕	80	4000	25000	A++	75027500
NEW	2 TForce Core LED HPL 18W E27 830 FR	80	18	3000	167	✕	80	3000	25000	A++	75029900
NEW	2 TForce Core LED HPL 18W E27 840 FR		18	3000	167	✕	80	4000	25000	A++	75031200
NEW	3 TForce Core LED HPL 26W E27 830 FR	125	26	4000	154	✕	80	3000	25000	A++	75033600
NEW	3 TForce Core LED HPL 26W E27 840 FR		26	4000	154	✕	80	4000	25000	A++	75035000

*TrueForce LED Road requires LED Driver to operate. It is recommended to use with Philips Xitanium LED driver model 9290009307xx/9290009892xx.

TrueForce LED Public (Road – SON)

TrueForce Road LED lamps are a high quality alternative for conventional lamps used in street lighting applications.
TrueForce Road LED utilizes optics of luminaires designed around HID and distributes light to exactly where it's needed.
It provides a crisp, white light (4,000K) and improved color rendering index of 70. This enhances people's sense of safety on roads, pedestrian and cycle paths, as well as in parks. It combines the right lumen package with high system efficacy to maximize energy saving.

TrueForce LED Public (Road – SON)

1 TrueForce LED Public

2 TrueForce LED Public

3 TrueForce LED Public

4 TrueForce LED Public

= Dimmable
= Non-dimmable
E27
E40
4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce LED Road 40-25W E27 730	50	25	4000	160	✗	70	3000	50000	A++	63251900
1 TForce LED Road 42-25W E27 740	50	25	4200	168	✗	70	4000	50000	A++	63253300
2 TForce LED Road 55-35W E27 730	70	35	5500	157	✗	70	3000	50000	A++	81115300
2 TForce LED Road 60-35W E27 740	70	35	6000	171	✗	70	4000	50000	A++	81117700
3 TForce LED Road 84-55W E40 730	100	55	8400	152	✗	70	3000	50000	A++	63904400
3 TForce LED Road 90-55W E40 740	100	55	9000	163	✗	70	4000	50000	A++	63906800
4 TForce LED Road 112-68W E40 730	100-150	68	11200	164	✗	70	3000	50000	A++	63908200
4 TForce LED Road 120-68W E40 740	100-150	68	12000	176	✗	70	4000	50000	A++	63910500

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. Products are available in 2 versions. With unique lamp design and compatibility (InstantFit), you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear or you can also choose for Direct Mains options, both enabling the same benefits of LED HID replacement. Multiple beam angle options and high color rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL) – Instant Upgrade - Plug & Play on EM

1 TrueForce LED HPI

This lamp only works with a specific LED driver

= Dimmable

= Non-dimmable

E40

4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce LED HPI ND 110-88W E40 840 60D	HPL/HPI/SON 250W	88	11000	125	✗	80	4000	50000	A+	71378500
1 TForce LED HPI ND 110-88W E40 840 120D		88	11000	125	✗	80	4000	50000	A+	71382200
1 TForce LED HPI ND 200-145W E40 840 60D	HPL/HPI/SON 400W	145	20000	137	✗	80	4000	50000	A+	71386000
1 TForce LED HPI ND 200-145W E40 840 120D		145	20000	137	✗	80	4000	50000	A+	71388400

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL) – Mains - Direct Mains operation

1 TrueForce LED HB MV

= Dimmable

= Non-dimmable

E40

4 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce LED HB MV ND 120-100W E40 840 NB	HPL/HPI/SON 250W	100	12000	120	✗	80	4000	50000	A+	59676700
1 TForce LED HB MV ND 120-100W E40 840 WB		100	12000	120	✗	80	4000	50000	A+	59678100
1 TForce LED HB MV ND 200-160W E40 840 NB	HPL/HPI/SON 400W	160	20000	125	✗	80	4000	50000	A+	59670500
1 TForce LED HB MV ND 200-160W E40 840 WB		160	20000	125	✗	80	4000	50000	A+	59672900

TrueForce Core LED Industrial and Retail

Philips TrueForce Core LED I&R lamps offer an easy LED solution to replace High Intensity Discharge (HID) lamps.
Customers can easily retrofit TrueForce Core LED I&R lamps while bypassing the existing ballast and enhance the lighting quality.

TrueForce Core LED Industrial and Retail

1 TrueForce Core HB MV ND 24W

2 TrueForce Core HB MV ND 35W

3 TrueForce Core HB MV ND 42W

= Dimmable

= Non-dimmable

E27

6 PACK

Product Type	Traditional	LED	Lumen Output	Efficacy	Dimmable	CRI	Color Temp.	Lifetime	EEL	EOC code
	W	W	lm	lm/W			K	Hrs.		
1 TForce Core HB MV ND 26-24W E27 830	55W CFL, 40W HID	24	2600	108	✗	80	3000	20000	A+	59728300
1 TForce Core HB MV ND 28-24W E27 840		24	2800	116	✗	80	4000	20000	A+	59730600
2 TForce Core HB MV ND 37-35W E27 830	65W CFL, 55W HID	35	3700	105	✗	80	3000	20000	A+	59732000
2 TForce Core HB MV ND 40-35W E27 840		35	4000	114	✗	80	4000	20000	A+	59734400
3 TForce Core HB MV ND 48-42W E27 830	75W CFL,70W HID	42	4800	114	✗	80	3000	20000	A+	59716000
3 TForce Core HB MV ND 50-42W E27 840		42	5000	119	✗	80	4000	20000	A+	59718400

All you need to know, right at your finger tips

We know that installation is about finding the right solutions.

Visit our webpage created especially for installers and find:

- All latest product information
- Selector tools to help you select the right product for your customers
- Installation videos
- Training

Visit: www.philips.com/installer

© 2020 Signify Holding. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

https://www.lighting.philips.com/main/support/purchase/installer

https://www.lighting.philips.com/main/home