IMAGEO WiZ SPOTS 2X5W B 27-65K TW

Offering a contemporary design and warm or cool white light, the WiZ Imageo smart build-on spotlight in black has two adjustable spots so you can light up your space with smart light. Use with your existing Wi-Fi to control with the WiZ app or your voice.

PRODUCT HIGHLIGHTS

- Tunable white
- Plate Dimensions: 8*25 cm
- IP20/Metal/Black

EAN:

Smart lighting functionalities easy to set up
Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!

Matter Certified
This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.

Exclusive SpaceSense™ light that turns on with movement
WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection.It´s simple. It´s SpaceSense. It´s WiZ.



Monitor your energy consumption
Get an overview of the energy consumption of your lights with the WiZ app. Easily access a weekly or daily report to help you stay on top of your energy consumption at home.

Set the right ambience with tunable warm to cool white light
Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

Control smart lighting the way you like it
WiZ enables you to control smart lighting in multiple ways. Adjust lights with your smartphone, voice, the WiZ remote control or by using the existing wall switch to toggle between two favourite modes. Works with Google Home, Alexa and Siri Shortcuts.

EAN:

wizconnected.com

SPECIFICATIONS

BULB CHARACTERISTICS
Intended use: Indoor
Lamp shape: Rectangle

DESIGN AND FINISHING
Colour: Black
Material: Metal

DURABILITY
Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000

EXTRA FEATURE/ACCESSORY INCL.
Adjustable spot head: Yes
Dimmable with remote control: Yes
LED integrated: No
LED lamp(s) included: Yes
Remote control included: No

LIGHT CHARACTERISTICS
Colour rendering index (CRI): 90
Warm-up time to 60% light: <2

MISCELLANEOUS
Especially designed for: Functional

OTHER CHARACTERISTICS
Efficacy: 69 lm/W

POWER CONSUMPTION
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT
Net weight: 0.62 kg
Height: 12.3 cm
Length: 25 cm
Width: 10.5 cm

SERVICE
Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS
Lifetime up to: 15,000 h
Lumen output bulb included: 345 lm
Total lumen output fixture: 690
Light colour: 2700-6500
Fixture dimmable: Wireless Dim – Do not use with a dimmer
LED: Yes
Built-in LED: Yes
Energy class included light source: G
Number of bulbs: 2
Wattage bulb included: 4.9
Maximum wattage replacement bulb: 5 W
IP code: IP20
Class of protection: Class I
Light source replaceable: Yes

signify

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: