



PHILIPS  
myLiving  
Suspension light  
40946 DEW  
chrome  
LED

40946/11/C0

# Decorate your home with light

Bring stunning effects to your living room with a suspension light that adds a touch of modern playfulness, with the light either on or off.

## **Premium quality**

- Premium glass crystals for sparkling light effect
- Premium aesthetic elegant chrome finish

## **Control**

- Convenient brightness control 3-level step dimming

## **Durability**

- Long life LED light source

# PHILIPS

# Highlights

## Premium glass crystals for sparkling light effect

For a sophisticated and timeless style, the glass crystals create a charming sparkling effect.

## Premium aesthetic elegant chrome finish

The elegant chrome finish on this item adds a touch of timeless sophistication to any space.

## Convenient brightness control 3-level step dimming

Convenient 3-level step dimming allows you to choose the brightness level that you need.

## Long life LED light source

Provides you with a long term lighting investment which offers equal quality light years down the line.

# Specifications

## Design and finishing

- Color: chrome
- Material: glass

## Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Historical
- Type: Suspension light
- EyeComfort: No

## Power consumption

- Energy Efficiency Label: Built in LED

## Product dimensions & weight

- Height maximum: 150 cm
- Height minimum: 40 cm
- Length: 61.9 cm
- Net weight: 3.455 kg
- Width: 61.9 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 1200 lm
- Mains power: Range 220 V - 240 V
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 38 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 6947830432363
- Height: 34.8 cm
- SAP Gross Weight EAN (Piece): 6.500 kg
- Weight: 6.500 kg
- Net Weight: 3.455 kg
- SAP Length (Piece): 0.000 mm
- SAP Width (Piece): 0.000 mm
- Width: 42.6 cm
- Length: 59.1 cm



Issue date: 2019-12-02  
Version: 0.91

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)