Up and Down Wall Spotlight

Have fun with light patterns on your walls and create an ambience with colour. Our Up and Down Wall Light for Indoor illuminates up and down, producing interesting shapes of light, shadow, and colour, and giving character to your room.

PRODUCT HIGHLIGHTS

- Full colour
- Dimensions: 15 cm (Height) * 9.2 cm (Length) * 6.8 cm (Width)
- IP20/Metal/Black

EAN:

Smart lighting functionalities easy to set up
Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!

Matter Certified
This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.

Exclusive SpaceSense™ light that turns on with movement
WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and get the lights to turn on and off automatically with motion detection.It´s simple. It´s SpaceSense. It´s WiZ.

Set up lights to follow your own schedule
Automate your smart lights to follow your daily or weekly routines. Schedule your lights to turn on in the morning or before you arrive home, and to keep them off to save energy, when they are not necessary.

Millions of colours and changing light modes to make your day
Choose any light colour you like or simply apply a dynamic light mode that we've designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.

Set the right ambience with tunable warm to cool white light
Choose from a wide range of energising cool white to soft warm white light, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

EAN:

SPECIFICATIONS

BULB CHARACTERISTICS
Intended use: Indoor
Lamp shape: Rectangle

DESIGN AND FINISHING
Colour: Black
Material: Metal

DURABILITY
Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 50,000

EXTRA FEATURE/ACCESSORY INCL.
Adjustable spot head: No
Dimmable with remote control: Yes
LED integrated: No
LED lamp(s) included: Yes
Remote control included: No

LIGHT CHARACTERISTICS
Colour rendering index (CRI): 90
Warm-up time to 60% light: <2

MISCELLANEOUS
Especially designed for: Functional

OTHER CHARACTERISTICS
Lamp current: 60 mA
Efficacy: 69 lm/W

POWER CONSUMPTION
Voltage: 220-240 V

PRODUCT DIMENSIONS AND WEIGHT
Net weight: 0.64 kg
Height: 15 cm
Length: 9.2 cm
Width: 6.8 cm

SERVICE
Warranty: 2 year(s)

TECHNICAL SPECIFICATIONS
Lifetime up to: 15,000 h
Lumen output bulb included: 345 lm
Total lumen output fixture: 690
Light colour: 2200-6500 (RGB)
Fixture dimmable: Wireless Dim – Do not use with a dimmer
LED: Yes
Built-in LED: Yes
Energy class included light source: F
Number of bulbs: 2
Wattage bulb included: 4.7
Maximum wattage replacement bulb: 5 W
IP code: IP20
Class of protection: Class I
Light source replaceable: Yes

signify

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: