

PHILIPS

Muscari floor light

Hue White

LED integrated

Aluminium

Smart control with Hue bridge*

Control with your voice*



45040/48/MO



Light for your moment

Automate your lights with the Philips Hue White Muscari LED floor light. Dimmable and with soft uniform light distribution, it lets you experience seamless smart control and schedule your light for home automation, wherever you are.

Light for your moments

- Wake up and go to sleep naturally
- Installation free dimming
- Requires a Philips Hue bridge
- Set timers for your convenience
- Control it your way



Highlights

Wake up and go to sleep



Philips Hue will help get you out of bed the way you like it, helping you start your day feeling refreshed. The light brightness increases gradually mimicking the effect of sunrise and helps you wake up naturally, instead of being woken up by the loud sound of an alarm clock. Start your day, the right way. In the evening, the relaxing warm white light helps you to unwind, relax and prepare your body for a good night's sleep.

Installation free dimming




Experience guaranteed smooth dimming with Philips Hue. Not too bright. Not too dark. Just right. No need for wires, an electrician or installation

Requires a Philips Hue bridge



Connect your Philips Hue lights with the bridge to control your lights from your smart phone or tablet via the Philips Hue app.

Timers for your convenience



Philips Hue can make it seem like you're home when you're not, using the schedule function in the Philips Hue app. Set the lights to come on at a pre-set time, so the lights are on when you arrive home. You can even set rooms to light up at different times. And of course, you can let the lights turn off gradually in the night, so you never have to worry whether you've left any lights on. Connection with the Philips Hue bridge required for this functionality.

Control it your way

Connect Philips Hue lights with the Philips Hue bridge to enjoy optimal control of lights from your smart devices via the Philips Hue app. Alternatively, add switches to your system to activate your lights. Set timers, notifications, alarms and more for the full Philips Hue experience. Philips Hue works with Amazon Alexa*, Apple HomeKit, Google Home* and DingDong* for a seamless voice control. Turn your lights on and off, change your color ambiances and recall your pre-set scenes conveniently with your voice.

Specifications

Design and finishing

- Color: Champagne Gold
- Material: metal

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Floor lamp
- EyeComfort: No

Power consumption

- Energy Efficiency Label (EEL): Built in LED

Product dimensions & weight

- Height: 160 cm
- Length: 31 cm
- Net weight: 2.200 kg
- Width: 31 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 600 lm
- Bulb technology: 100-240 V
- Light color: 2700 Hue White
- Mains power: 50-60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 12 W
- Maximum wattage replacement bulb: 15 W
- IP code: IP20
- Class of protection: III - safe extra low voltage
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 8718696153062
- Net weight: 2.200 kg
- Gross weight: 10.100 kg
- Length: 0.000 mm
- Width: 0.000 mm
- Material number (12NC): 915005291401



Issue date: 2020-10-12
Version: 0.428

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com