

PHILIPS

Garnea Hue White
Ambience Downlight

Hue White ambience

Integrated LED

High quality material

Smart control with Hue bridge*

Control with your voice*



51108/31/H5



Easy smart lighting

This retrofit recessed downlight offers thousands of shades of white light at your fingertips. Control via Bluetooth to instantly turn on and off and the dim in one room, or pair with a Hue Bridge to unlock the full suite of features.

Light for your moments

- Wake up and go to sleep naturally
- Smart control, home and away
- Set timers for your convenience
- Installation free dimming
- Control with your voice
- Create your ambience with warm white to cool daylight
- Relax, read, concentrate and energize with light recipes
- Control it your way

Highlights

Wake up and go to sleep




Philips Hue will help get you out of bed the way you like it, helping you start your day feeling refreshed. The light brightness increases gradually mimicking the effect of sunrise and helps you wake up naturally, instead of being woken up by the loud sound of an alarm clock. Start your day, the right way. In the evening, the relaxing warm white light helps you to unwind, relax and prepare your body for a good night's sleep.

Smart control, home and away




With the Philips Hue iOS and Android apps you can control your lights remotely wherever you are. Check if you have forgotten to switch your lights off before you left your home, and switch them on if you are working late.

Timers for your convenience




Philips Hue can make it seem like you're home when you're not, using the schedule function in the Philips Hue app. Set the lights to come on at a pre-set time, so the lights are on when you arrive home. You can even set rooms to light up at different times. And of course, you can let the lights turn off gradually in the night, so you never have to worry whether you've left any lights on.

Installation free dimming



Experience guaranteed smooth dimming with Philips Hue. Not too bright. Not too dark. Just right. No need for wires, an electrician or installation

Control with your voice



Philips Hue works with Amazon Alexa, Apple HomeKit and Google Home, powered by the Google Assistant, to allow you to control your lights with your voice. Turn your lights on and off. Dim to the desired brightness for a perfect ambiance. Even recall pre-set scenes, change colors and more - all without lifting a finger.

Create your ambiance



Set the right ambiance for any moment and decorate your home with warm to cool white light. Enjoy a relaxing atmosphere with warm white light or a cozy, ambiance to wind down in. Delight in a clear and bright setting with natural white light or cool day light for your daily routine.

Light for your daily routines



Light influences our mood and behavior. Philips Hue can help you to customize your daily routines into

moments you can enjoy. Enjoy a hearty breakfast with cool and bright white daylight that helps to energize your body and mind. Stay focused in reading and writing with finely tuned, bright white light. Indulge in your bedtime regime with a soft glow of warm white light for the perfect end to the day.

Control it your way

Connect Philips Hue lights with the Philips Hue bridge to enjoy optimal control of lights from your smart devices via the Philips Hue app. Alternatively, add switches to your system to activate your lights. Set timers, notifications, alarms and more for the full Philips Hue experience. Philips Hue works with Amazon Alexa*, Apple HomeKit, Google Home* and DingDong* for a seamless voice control. Turn your lights on and off, change your color ambiances and recall your pre-set scenes conveniently with your voice.

Specifications

Design and finishing

- Color: white
- Material: synthetics

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Functional
- EyeComfort: No

Power consumption

- Energy Efficiency Label (EEL): Built in LED

Product dimensions & weight

- Cut out length: 15 cm
- Cut out width: 15 cm
- Length: 17.5 cm
- Net weight: 0.253 kg
- Recessed distance: 6.5 cm
- Width: 16 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 900 lm
- Mains power: 230 V
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 10.5 W
- Maximum wattage replacement bulb: 10.5 W
- IP code: IP20
- Class of protection: II - double insulated
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC - product: 6947830439744
- Net weight: 0.253 kg
- Gross weight: 0.346 kg
- Height: 178.000 mm
- Length: 88.000 mm
- Width: 187.000 mm
- Material number (12NC): 915005754501



Issue date: 2020-11-23
Version: 0.414

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.