

# LIGHTOLIER

by  Signify

## On-site options for brilliance & comfort



**Downlighting**

Commercial retrofit  
downlight



# Bright, brighter, brightest you choose

Varying ceiling heights? Indecisive customers? The easy-install **Lightolier Commercial retrofit downlight** is an ideal solution.

The Commercial retrofit downlight, with its adjustable lumen output switch, will reduce onsite time and headaches for busy installers. For example, our 8" downlight gives you the choice of 1000, 1500 and 2300 lumens and can be installed into a junction box or existing frame (refer

to the specification sheet for the list of compatible frames). So... if your hospital waiting room has three different ceiling heights, you won't need three different fixtures for the space.

This reliable light is perfect for retrofit or new construction applications including



offices, hotels, healthcare spaces, retail stores, multi-family developments and assisted living facilities. The Commercial retrofit downlight is energy star

rated and will allow you further cost savings through local rebates where available.



## Multi-level ceilings, no problem...


This waiting area has a 12 foot ceiling, while the hallway is nine. Simply use the switch on the back of the fixtures to raise or lower the lumen output and control light levels and visual comfort.




## Flexibility with sizing.....

Use size to enhance the design and lighting effect of your space. With four sizes to choose from, combining smaller fixtures with larger ones can deliver the amount of light you need, while creating zones and division.


4" Round




6" Round



8" Round



9.5" Round



# Make a bright choice

## for your next downlight installation



- Adjustable lumen output switch allows you to make choices before you install
- Great for different ceiling heights and different light level needs
- Sturdy metal clips provide a solid fit and easy installation
- Out-of-the-box pre-wired with flexible metal conduit and easy-twist quick connector
- Universal voltage 120-277V
- 50,000 hour rated life (L70)
- 5 year warranty

### Fixture

example: CR4R10927UW

Family	Size/Lumens	CRI	CCT	Voltage	Finish
<b>CR</b>		<b>9</b>		<b>U</b>	<b>W</b>
CR Commercial retrofit downlight	<b>4R10</b> 4" Round - 500lm/750lm/1000lm <b>6R15</b> 6" Round- 700lm/1000lm/1500lm <b>8R23</b> 8" Round- 1000lm/1500lm/2300lm <b>10R30</b> 9.5" Round- 1500lm/2000lm/3200lm	<b>9</b> 90CRI	<b>27</b> 2700K <b>30</b> 3000K <b>35</b> 3500K <b>40</b> 4000K	<b>U</b> 120/277V	<b>W</b> White

Visit [signify.com/warranties](http://signify.com/warranties) for more information on the standard 5-year limited warranty.



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation  
 200 Franklin Square Drive,  
 Somerset, NJ 08873  
 Telephone 855-486-2216

Signify Canada Ltd.  
 281 Hillmount Road,  
 Markham, ON, Canada L6C 2S3  
 Telephone 800-668-9008

[www.lightolier.com](http://www.lightolier.com)