

PHILIPS

Table lamp

Jabiru

anthracite

LED



66016/93/P3



Reliable desk lighting

Explore limitless possibilities with ultra flexible Philips Jabiru LED desklight. Angle your brightness to perfection, or adjust height and distance on your workspace. Light designed to go the miles for you with a superb light experience.

Light effect

- Cool white light

Easy to experience

- Flexible directional light

Advanced LED light

- Energy efficient & longer lasting
- Integrated LED light source

Control

- Multi-level step dimming


Highlights

Cool white light



Cool white light provides a comforting and cosy environment.

Flexible directional light



Luminaire allows you to change the direction of your light to suit your needs.

Integrated LED light source

Integrated LED light source for the perfect light ambience with less maintenance and lamp replacement.

Multi-level step dimming

Intuitive multi-level brightness control setting gives you great control over your lights and to create the light ambience that you need.

Energy efficient

Philips energy-saving lamps help to conserve energy and save electricity bills while doing your bit for the environment.

Specifications

Design and finishing

- Colour: anthracite
- Material: synthetics

Extra feature/accessory incl.

- Dimmer and on/off switch on article: Yes
- On/off switch on article: Yes

Miscellaneous

- Especially designed for: Home office and Study, Living Room and Bedroom
- Type: Table lamp
- EyeComfort: No

Power consumption

- Energy efficiency label (EEL): A

Product dimensions and weight

- Height: 38.6 cm
- Length: 14 cm
- Net weight: 0.441 kg
- Width: 32.8 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Total lumen output fixture: 390 lm
- Mains power: Range 100 V–240 V, 50–60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built-in LED: No
- Energy class included light source: A
- Fixture is compatible with bulb(s) of class: A+ to E
- Number of bulbs: 1
- Wattage bulb included: 4.5 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated
- Light source replaceable: No



Issue date: 2023-11-08
Version: 0.621

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com