

PHILIPS

Compact fluorescent
Stick bulb

Genie

11 W (60 W)

B22 cap

Cool daylight

220-240V

8718291214875



Spend a little, save a lot

This Philips Economy light bulb is the "value for money" option when you require a basic energy-saving bulb in a compact design. Lasting up to 6 years, this compact bulb will save up to 80% energy and money.

Superb performance in compact design

- Saves up to 80% energy

High performance bright light

- Soft, easy on the eyes light

Saves energy and money

- Long lifetime - lasting up to 6 years

Highlights

Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year.

So reduce your energy bill and start saving Now.

Soft, easy on the eyes light

Energy-saving lamps from the Philips Softone series are designed to provide a gentle, diffused light, perfect for general home lighting. Choose between different color temperatures to create the atmosphere you want.

Long lifetime - up to 6 years



Philips energy-saving bulbs are designed to last. With a lifetime of up to 6 years, you can avoid the hassle and cost of frequently replacing bulbs, while saving energy year in, year out.

Specifications

Characteristics

- Shape: Stick
- Dimmable: No
- Socket: B22

Bulb dimensions

- Height: 125 mm
- Width: 44.1 mm

Durability

- Average life (at 2.7 hrs/day): 6 year(s)
- Lumen maintenance factor: 0.8
- Nominal lifetime: 6,000 hour(s)
- Number of switch cycles: 5,000

Light characteristics

- Application: Comfortable light, Extra brightness, Soft light
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 570 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: <2

Other characteristics

- Lamp current: 50 mA

Power consumption

- Power factor: 0.85
- Voltage: 220 - 240 V
- Wattage: 11 W
- Wattage equivalent: 60 W

Rated values

- Rated lifetime: 6,000 hour(s)
- Rated luminous flux: 570 lumen
- Rated power: 11 W

Packaging dimensions and weight

- EAN/UPC - product: 8718291214878
- Net weight: 0.065 kg
- Gross weight: 0.079 kg
- Height: 12.900 cm
- Length: 4.600 cm
- Width: 4.600 cm
- Material number (12NC): 929689680605



Issue date: 2020-11-26
Version: 0.391

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com