

PHILIPS

Downlight

Functional

Meson

White



8718696173978



Superior light and style

Attractive when switched on or off, this Philips LED downlight is the perfect match for your home's interiors, offering light which is easy on the eyes.

Designed for your living- and bedroom

- Perfect to relax and socialise

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution

Safety

- No harmful UV radiation

High quality LED light that lasts for decades

- Reduced glare. Increased comfort.

Highlights

Perfect to relax and socialise

The living room is the heart of any home - a place where families gather to relax and guests socialise. Lighting for your living- and bedroom has to be flexible and easy to adjust to its different uses throughout the day. Careful placement of different light sources and playing with light layering helps create the feeling of space and to give the room a warm and welcoming feel.

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

EyeComfort with Interlaced optics

Interlaced optics technology enhances the overall lighting experience in your every-day life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional
- Type: Downlight

Product dimensions & weight

- Cut out length: 8 cm
- Cut out width: 8 cm
- Height: 4.55 cm
- Length: 9.5 cm
- Net weight: 0.046 kg
- Recessed distance: 7.25 cm
- Width: 9.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 95 mm
- Total lumen output fixture: 235
- Light color: 3000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 3.5
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696173978
- Net weight: 0.050 kg
- Gross weight: 0.092 kg
- Height: 9.700 cm
- Length: 5.400 cm
- Width: 9.600 cm
- Material number (12NC): 915005818301



Issue date: 2021-03-02
Version: 0.131

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com