

# PHILIPS

Recessed spot light

myLiving

COB Pro

White

8718696681831



## Superior light and style

The sleek Philips Spot Light COB Pro recessed spot in aluminium lies flat on your ceiling for a clean silhouette. Directable light enhances the decor

### Designed for your living- and bedroom

- Create a stylish and welcoming atmosphere

### Light effect

- Bright and focused beam

### Material & finishing

- Durable aluminum housing

### Durability

- Long life span up to 30,000 hours

# Highlights

## Create a stylish atmosphere

This light is designed around the latest tastes, trends and lifestyles to blend effortlessly into your décor and define the localised ambience you have always desired.

## Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

## Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

# Specifications

## Design and finishing

- Color: White
- Material: metal

## Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

## Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Living- & Bedroom

## Product dimensions and weight

- Net weight: 0.23 kg
- Cut out length: 9.5 cm
- Cut out width: 9.5 cm
- Height: 5.2 cm
- Length: 10.5 cm
- Width: 10.5 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 35,000 hour(s)
- Diameter: 105 mm
- Total lumen output fixture: 1080
- Light color: 4000
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC – product: 8718696681831
- Net weight: 0.230 kg
- Gross weight: 0.250 kg
- Height: 7.200 cm
- Length: 13.000 cm
- Width: 11.200 cm
- Material number (12NC): 929001951941



Issue date: 2023-11-08  
Version: 0.34

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)