

# PHILIPS

Recessed spot light

myLiving

AstraSpot

White

8718696716441



## Durable and bright

Elegant spotlight with focussed beam to highlight the objects, walls and décor. With Tilt the light beam can be redirected on certain objects

### Match your interior

- Compact design

### Light effect

- Bright and focused beam

### Material & finishing

- Durable aluminum housing

### Durability

- Long life span up to 15,000 hours

# Highlights

## Compact design

Compact size allows luminaire to be placed in small spaces.

## Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Design and finishing

- Color: White
- Material: metal

## Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: No

## Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Living- & Bedroom

## Product dimensions & weight

- Cut out length: 7.7 cm
- Cut out width: 7.7 cm
- Height: 5.6 cm
- Length: 8.2 cm
- Net weight: 0.14 kg
- Width: 8.2 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 82 mm
- Total lumen output fixture: 475
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 7
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8718696716441
- Net weight: 0.140 kg
- Gross weight: 0.160 kg
- Height: 6.800 cm
- Length: 11.000 cm
- Width: 10.000 cm
- Material number (12NC): 919215850657



Issue date: 2022-07-26  
Version: 0.28

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)