

PHILIPS

Lightstrip Outdoor 2-metre

Hue White and Colour
Ambiance

1 x 2 metre lightstrip


White and coloured light

Power supply unit included

Smart control with Hue Bridge*



8718696804773



Limitless possibilities

Completely flexible, the outdoor 2 meter light strip lets you shape and bend the way you want. Line a winding outdoor path or let it meander up a wall or column; with the included clips and screws, you can install it anywhere.

Limitless possibilities

- Power supply and plug included
- Beautify your backyard with outdoor lighting
- Connect to your Hue Bridge for full smart lighting control
- Weatherproof light strip
- Flexible light strip to shape and bend
- Perfectly uniform, diffused strip lighting

Highlights

Power supply and plug included



This unit pack comes with all the elements you need to get started, including a lightstrip and outdoor power supply. So all you have to do is unpack, install where you want and turn them on.

Connect to the Hue Bridge



This product requires a connection to the Hue Bridge to unlock the full smart control and features. Control your lights using the Philips Hue app, set timers, routines, add or remove lights and more. *Hue Bridge sold separately

Flexible light strip



Completely flexible, the outdoor light strip lets you shape, bend and manipulate it to shine its light the way you want. Line a winding outdoor path or let it meander up a wall or column; with the included clips and screws, you can install it anywhere.

Beautify your backyard



Give your garden a chance to shine as brightly as your home. Over 16 million colours and 50,000 shades of warm and cool white light allow you to decorate the outside just like the inside, whether you're illuminating a walkway or shining a spotlight on your favourite part of the patio.

Weatherproof light strip



The outdoor light strip can withstand all weather conditions, from small puddles of water to a downpour that lasts for hours.

Perfectly uniform and diffused



Philips Hue outdoor strip light features a special coating that diffuses, or scatters, the emitted white or coloured light. There's no need to hide the light strip, whether you're using it for direct or indirect lighting – all you see is pure light.

Specifications

Design and finishing

- Colour: multi colour
- Colour(s): multi
- Material: silicone

Environmental

- Operational humidity: 5% <H<95% (non-condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Colour changing (LED): Yes
- Diffused light effect: Yes
- Dimmable: Yes
- LED integrated: Yes

Guarantee

- 2 years: Yes

Lightstrip

- Colour temperature: 2000–6500 K
- Cut-ability: No
- Extendibility: No
- Input Voltage: 220V–240V
- Max. standby power: 0.5 W
- Wattage: 19 W
- Lumen output: 850 lm at 4000K, 740 lm at 2200K, 760 lm at 2700K, 900 lm at 6500K

Power consumption

- Wattage: 19 W

Product dimensions and weight

- Length: 199 cm
- Width: 1.1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 h
- Lifetime: 25000 h
- IP code: IP67
- Class of protection: II – double insulated
- Extra features: Diffused light effect

What's in the box

- Power adapter: 1



Issue date: 2023-11-08
Version: 0.1247

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com