

# PHILIPS

Bulb

LED

3W (30W)

E27 cap

White

8718696820766



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

### **Energy saving**

- Lamp reducing their energy consumption

### **Create a warm atmosphere**

- A simple LED for everyday use

### **Light beyond illumination**

- Instant on

# Highlights

**Energy saving**  
A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

**Instant on**

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Frosted

## Bulb dimensions

- Height: 10.4 cm
- Width: 5.8 cm

## Durability

- Average life (at 2.7 hrs/day): 8 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 8,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 130 degree(s)
- Color rendering index (CRI): 70
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 280 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 30 mA

## Power consumption

- Power factor: >0.4
- Voltage: 220-240 V
- Wattage: 3 W
- Wattage equivalent: 30 W

## Rated values

- Rated beam angle: 130 degree(s)
- Rated lifetime: 8,000 hour(s)
- Rated luminous flux: 280 lumen
- Rated power: 3 W

## Packaging dimensions and weight

- EAN/UPC - product: 8718696820766
- Net weight: 0.050 kg
- Gross weight: 0.064 kg
- Height: 9.800 cm
- Length: 5.700 cm
- Width: 5.700 cm
- Material number (12NC): 929001892967



Issue date: 2020-08-03  
Version: 0.437

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)