

PHILIPS

Bulb

LED

9W (80W)

E27 cap

White

8718696845370



Warm white light, no compromise on light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

Energy saving

- Lamp reducing their energy consumption

Create a warm atmosphere

- A simple LED for everyday use

Light beyond illumination

- Instant on

Highlights

Energy saving

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 10.4 cm
- Weight: 0.05 kg
- Width: 5.8 cm

Durability

- Average life (at 2.7 hrs/day): 8 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 8,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Color consistency: 7SDCM
- Color rendering index (CRI): 70
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 900 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 80 mA
- Efficacy: 100 lm/W

Packaging information

- Product family: Mainstream

Power consumption

- Power factor: >0.5
- Voltage: 220-240 V
- Wattage: 9 W
- Wattage equivalent: 80 W
- Energy Efficiency Label (EEL): 3 Tick

Rated values

- Rated beam angle: 130 degree(s)
- Rated lifetime: 8,000 hour(s)
- Rated luminous flux: 900 lumen
- Rated power: 9 W

Packaging dimensions and weight

- EAN/UPC - product: 8718696845370
- Net weight: 0.050 kg
- Gross weight: 0.060 kg
- Height: 9.800 cm
- Length: 5.700 cm
- Width: 5.700 cm
- Material number (12NC): 929001899837



Issue date: 2023-11-08
Version: 0.436

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com