

PHILIPS

Bulb (Dimmable)

LED

8.5W-60W

B22

Warm Glow

Dimming

8718699654931



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Light beyond illumination

- Dimmable
- Instant on

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10%

of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Instant on

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11 cm
- Weight: 0.06 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 45 mA
- Efficacy: 94 lm/W

Packaging information

- EAN: 8718699654931
- EOC: 871869965493100
- Product title: LEDBulb 8.5-60W A60 B22 2700K FR D AU/BC

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 8.5 W
- Wattage equivalent: 60(60W GLS, 14W CFL)) W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight

- Length: 11 cm

Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lumen
- Rated power: 8.5 W

Technical specifications

- Frequency: 50-60 Hz



Issue date: 2021-02-19
Version: 0.71

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com