

**PHILIPS**

Spot

LED

5W-50W

GU5.3

Warm White

8718699675738



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

**Choose for a sustainable solution**

- Safe for any room and convenient to recycle

# Highlights

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

## Bulb dimensions

- Height: 4.6 cm
- Weight: 0.048 kg
- Width: 5.1 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 390 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 580 mA
- Efficacy: 78 lm/W

## Packaging information

- EAN: 8718699675738
- EOC: 871869967573800
- Product title: LEDspots 5-50W MR16 830 60D 4PK

## Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A+

## Product dimensions & weight

- Length: 4.6 cm

## Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 400 cd
- Rated power: 5 W

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718699675738
- Net weight: 0.200 kg
- Gross weight: 0.239 kg
- Height: 12.400 cm
- Length: 5.100 cm
- Width: 10.500 cm
- Material number (12NC): 929001280494



Issue date: 2021-04-29  
Version: 0.18

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)