



PHILIPS
LED
Spot
5W-50W
GU5.3
Cool White

8718699675752

Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

Choose for a sustainable solution

- Safe for any room and convenient to recycle

PHILIPS

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

Bulb dimensions

- Height: 4.6 cm
- Weight: 0.048 kg
- Width: 5.1 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Light Color Category: Cool White
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 580 mA
- Mercury content: 0 mg
- Efficacy: 82 lm/W

Packaging information

- EAN: 8718699675752
- EOC: 871869967575200
- Product title: LEDspots 5-50W MR16 840 60D 4PK

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W

Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 h
- Rated peak intensity: 420 cd
- Rated power: 5 W

Packaging dimensions & weight

- EAN/UPC - product: 8718699675752
- Net weight: 0.200 kg
- Gross weight: 0.239 kg
- Height: 12.400 cm
- Length: 5.100 cm
- Width: 10.500 cm
- Material number (12NC): 929001280594
- EAN/UPC - Case: 8718699675769
- Weight product including package: 0.000 kg
- Weight product without package: 0.050 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000
- SAP EAN/UPC - Set: 8718699675752



Issue date: 2020-05-17
Version: 0.14

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com