

PHILIPS

Downlight

Functional

Star Surface

White

8718699687847



Comfortable LED light that's easy on your eyes

Philips Star Surface light fits perfectly in all your general spaces for a clean look. It is compact and easy to install and provides a soft uniformed glow through its quality synthetic diffuser

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Available in Warm White, Cool White or Cool Daylight

Safety

- No harmful UV radiation

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Available in Warm White, Cool White or Cool Daylight

Different light colors can affect mood: warm white is perfect for relaxation,

cool white for concentration and cool daylight for energizing you

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: White
- Material: plastic

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions and weight

- Net weight: 0.25 kg
- Height: 2.5 cm
- Length: 30 cm
- Width: 30 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 300 mm
- Total lumen output fixture: 1700
- Light color: 6500
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 22
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718699687847
- Net weight: 0.450 kg
- Gross weight: 0.610 kg
- Height: 31.000 cm
- Length: 31.000 cm
- Width: 4.000 cm
- Material number (12NC): 929001951618



Issue date: 2023-11-08
Version: 0.50

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com