PHILIPS

Ceiling light

Functional

UltraGlow ceiling light

Cool Day light

15W, Square



8718699690120



High quality LED Ceiling light designed to last for years

Philips LED ceiling lights provide light that is designed for the comfort of your eyes.

Easy to experience
- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect
- Bright light with uniform distribution

Premium quality
- EyeComfort - light that's easy on the eyes

Durability
- Long life span up to 25,000 hours

Highlights

Suitable for low ceilings Slim design
Bright light with uniform distribution
To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Eyecomfort
Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they
meet EyeComfort requirements. Philip s LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Long life span up to 25,000 hours
Philips LED technology extends your product's lifetime up to 25,000 hours

Specifications

Design and finishing
- Color: White
- Material: plastic

Extra feature/accessory incl.
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics
- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

Miscellaneous
- Especially designed for: Functional

Product dimensions and weight
- Net weight: 0.185 kg
- Cut out length: 14 cm
- Cut out width: 14 cm
- Height: 2.2 cm
- Length: 16 cm
- Width: 16 cm

Service
- Warranty: 2 year(s)

Technical specifications
- Lifetime up to: 25,000 hour(s)
- Diameter: 160 mm
- Total lumen output fixture: 1125
- Light color: 6500
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 15
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight [15W Square AP LED Plus (CDL)]

- EAN/UPC - product: 8718696573754
- Net weight: 0.248 kg
- Gross weight: 0.316 kg
- Height: 17.200 cm
- Length: 18.000 cm
- Width: 4.800 cm
- Material number (12NC): 929001951775

Packaging dimensions and weight [15W Square AP Plus UltraGlow LED DL(CDL)]

- EAN/UPC - product: 8718696573754
- Net weight: 0.248 kg
- Gross weight: 0.316 kg
- Height: 17.200 cm
- Length: 18.000 cm
- Width: 4.800 cm
- Material number (12NC): 929002629401

Issue date: 2023-11-08
Version: 0.176

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com