

PHILIPS

Spot

LED

5W-50W

GU5.3

Warm White

8718699691134



Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them

safe for any room and convenient to recycle.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

Bulb dimensions

- Height: 4.6 cm
- Weight: 0.042 kg
- Width: 5.1 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 390 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: poc

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 580 mA
- Efficacy: 78 lm/W

Packaging information

- EAN: 8718699691134
- EOC: 871869969113400
- Product title: LEDClassic 5-50W MR16 830 60D 2pack

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W

Product dimensions & weight

- Length: 4.6 cm

Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 h
- Rated peak intensity: 400 cd
- Rated power: 5 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8718699691134
- Net weight: 0.080 kg
- Gross weight: 0.109 kg
- Height: 14.800 cm
- Length: 4.800 cm
- Width: 4.800 cm
- Material number (12NC): 929001280492



Issue date: 2022-09-16
Version: 0.24

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com