

**PHILIPS**

Downlight

Functional

Star Fit

White

8718699697549



## Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

### **Sustainable light solutions**

- High quality LED light

### **Light effect**

- Natural diffused light

### **Mounting**

- Integrated driver with connector for easy installation.

### **Durability**

- Long life span up to 15,000 hours

# Highlights

## High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

## Natural diffused light

Softens light to avoid glare and sharp, uncomfortable and direct light.

## Integrated driver with connector for easy installation.

Allows for safe and easy installation with no knowledge or wiring required.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Design and finishing

- Color: White
- Material: plastic

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional

## Product dimensions & weight

- Cut out length: 8 cm
- Cut out width: 8 cm
- Height: 5.2 cm
- Length: 10.6 cm
- Net weight: 0.07 kg
- Width: 10.6 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 106 mm
- Total lumen output fixture: 280
- Light color: 4000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 4
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8718699697549
- Net weight: 0.067 kg
- Gross weight: 0.112 kg
- Height: 11.000 cm
- Length: 7.000 cm
- Width: 12.700 cm
- Material number (12NC): 929002248302



Issue date: 2020-11-11  
Version: 0.16

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.