

PHILIPS

Lightstrip Outdoor 2 meter
with 40W Power Supply

Hue White and color
ambiance

1 x 2 meter lightstrip


White and colored light

Power supply unit included

Smart control with Hue Bridge*



8718699709969



Limitless possibilities

Completely flexible, the outdoor 2 meter light strip lets you shape and bend the way you want. Line a winding outdoor path or let it meander up a wall or column; with the included clips and screws, you can install it anywhere.

Limitless possibilities

- Power supply and plug included
- Beautify your backyard with outdoor lighting
- Connect to your Hue Bridge for full smart lighting control
- Weatherproof light strip
- Flexible light strip to shape and bend
- Perfectly uniform, diffused strip lighting

Highlights

Power supply and plug included



This unit pack comes with all elements you need to get started, this includes a lightstrip and outdoor power supply. So all you have to do is unpack, install where you like and turn them on.

Beautify your backyard



Give your garden a chance to shine as bright as your home. Over 16 million colors and 50,000 shades of warm and cool white light allow you to decorate the outside just like the inside, whether you're illuminating a walkway or shining a spotlight on your favorite part of the patio.

Connect to the Hue Bridge




This product requires a connection to the Hue Bridge to unlock the full smart control and features. Control your lights using the Philips Hue app, set timers, routines, add or remove lights and more. *Hue Bridge sold separately

Weatherproof light strip



The outdoor light strip can withstand all weather conditions, from small puddles of water to a downpour that lasts for hours.

Flexible light strip



Completely flexible, the outdoor light strip lets you shape, bend, and manipulate it to shine its light the way you want. Line a winding outdoor path or let it meander up a wall or column; with the included clips and screws, you can install it anywhere.

Perfectly uniform and diffused



Philips Hue outdoor strip light features a special coating that diffuses, or scatters, the emitted white or colored light. There's no need to hide the light strip, whether you're using it for direct or indirect lighting • all you see is pure light.

Specifications

Design and finishing

- Color: Multi Color
- Material: Silicone

Environmental

- Operational humidity: 5% <H<95% (non condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Color changing (LED): Yes
- Diffused light effect: Yes
- Dimmable: Yes
- LED integrated: Yes

Guarantee

- 2 years: Yes

Light characteristics

- Color rendering index (CRI): >80

Lightstrip

- Color temperature: 2000-6500 K
- Cut ability: No
- Extendibility: No
- Input Voltage: 220V-240V
- Lifetime: 25,000 h
- Max. standby power: 0.5 W
- Wattage: 19 W
- Width: 11 mm
- Length: 78 inch
- Width: 0.43 inch

Miscellaneous

- Type: Light Strips

Packaging information

- EAN: 8718699709952

Power consumption

- Wattage: 19 W
- Standby power consumption: 0.50 W

Product dimensions and weight

- Net weight: 0.337 kg
- Net weight: 0.743 lb
- Height: 2 cm
- Length: 199 cm
- Width: 1.1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lumen output at 4000K: 850 lm
- Lifetime up to: 25,000 h
- Lifetime: 25,000 h
- Mains power: Range 220 V – 240 V
- Energy class included light source: G
- IP code: IP67
- Class of protection: II – double insulated
- Extra features: Diffused light effect
- Replaceability of light source: Non-Replaceable LED light source
- Replaceability of control gears: Replaceable control gear by end-user
- Lumen output at 2700K: 760 lm

What's in the box

- Power adapter: 1

What's supported

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above
- Philips Hue Bluetooth App: IOS 15 and above, Android 9.0 and above

Packaging dimensions & weight

- EAN/UPC – product: 8718699709952
- Net weight: 0.95 kg
- Gross weight: 1.77 kg
- Height: 210 mm
- Length: 96 mm
- Width: 210 mm
- Material number (12NC): 929002289009



Issue date: 2024-02-02
Version: 0.219

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com