

PHILIPS

Ceiling light

Functional

CL200

White

8718699748494



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes

Easy to experience

- Easy installation

Light effect

- Uniform light distribution

Safety

- No harmful UV radiation

Premium quality

- EyeComfort - light that's easy on the eyes
- Easy to clean

Durability

- Long life span up to 15,000 hours

Highlights

Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

Eye comfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality,

output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: white
- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Power consumption

- Voltage: 220-240 V

Product dimensions & weight

- Height: 6.8 cm
- Length: 32 cm
- Net weight: 0.44 kg
- Width: 32 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 320 mm
- Total lumen output fixture: 1500
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 17
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8718699748494
- Net weight: 0.170 kg
- Gross weight: 0.720 kg
- Height: 7.000 cm
- Length: 35.200 cm
- Width: 35.200 cm
- Material number (12NC): 915005773907



Issue date: 2020-09-27
Version: 0.39

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com