

# PHILIPS

Bulb 60W A60 B22

LED

8W-60W

B22

Warm White



8718699769468



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Type of glass: Frosted
- Lamp Finish: Frosted
- Bulb material: Plastic

## Lamp dimensions

- Height: 11 cm
- Width: 6 cm

## Design and finishing

- Material: Plastic

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 100 lm/W

## Packaging information

- EAN: 8718699769468
- EOC: 871869976946800
- Product title: LED 60W A60 B22 WW FR ND 1SRT4

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 11 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 391863

## The bulb

- Colour consistency: 6

**Packaging dimensions and weight**

**[LED 60W A60 B22 WW FR ND 1SRT4]**

- EAN/UPC – product: 8718699769468
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm
- Material number (12NC): 929001233903

**Packaging dimensions and weight**

**[LED 60W A60 B22 WW FR ND 1SRT4 UK]**

- EAN/UPC – product: 8718699769468
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm
- Material number (12NC): 929001233996



Issue date: 2024-02-02  
Version: 0.253

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)