

PHILIPS

Bulb

LED

8W-60W

E27

Cool White



8718699782757



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Lamp dimensions

- Height: 12.2 cm
- Weight: 0.081 kg
- Width: 6.3 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 78 mA
- Efficacy: 100 lm/W

Packaging information

- EAN: 8718699782757
- EOC: 871869978275700
- Product title: LED Sensor 60W A60 E27 CW FR ND SRT4

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 12.2 cm

Rated values

- Rated beam angle: 280 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 8 W

Technical specifications

- Frequency: 50-60 Hz

The bulb

- Colour consistency: 6

Bulb characteristics

- EAN/UPC - product: 8718699782757
- Rated beam angle: 280 degree(s)
- Height: 12.2 cm
- Average life (at 2.7 hrs/day): 15 a
- Lamp current: 78 mA
- Net weight: 0.074 kg
- Rated lifetime: 15,000 h
- Colour consistency: 6
- Intended use: Indoor
- Weight: 0.081 kg
- Lumen maintenance factor: 70%
- Colour consistency: 6SDCM
- Gross weight: 0.098 kg
- EAN: 8718699782757
- Rated luminous flux: 806 lm
- Lamp shape: Non-directional bulb
- Width: 6.3 cm
- Colour rendering index (CRI): 80
- Height: 14.600 cm
- EOC: 871869978275700
- Socket: E27
- Number of switch cycles: 50,000
- Colour temperature: 4000 K
- EyeComfort: Yes
- Length: 6.500 cm
- Product title: LED Sensor 60W A60
E27 CW FR ND SRT4
- Power factor: 0.5
- Rated power: 8 W
- Technology: LED
- Light Colour Category: Cool White
- Width: 6.300 cm
- Voltage: 220-240 V
- Type of glass: Frosted
- Nominal luminous flux: 806 lm
- Material number (12NC):
929002058831
- Wattage: 8 W
- Length: 12.2 cm
- Starting time: <0.5 s
- Wattage equivalent: 60 W
- Warm-up time to 60% light: Instant
full light
- Colour Code: 840 | CCT of 4000K
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.288

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com