

PHILIPS

Bulb


LED

10W-75W

B22

Cool Daylight

8719514258082



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes
- No visible flicker
- Long life bulb - Lasts up to 10 years

Choose for a sustainable solution

- Safe for any room and convenient to recycle
- You can trust what the Philips packaging is saying.

Create the right light for your home

- Perfect for general room lighting

Light beyond illumination

- A simple LED for everyday use

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Perfect for general lighting



Contemporary lighting with Philips LED standard bulbs for use in table lamps, floor lamps, and pendant fixtures. Ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 10.1 cm
- Weight: 0.05 kg
- Width: 5.6 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 5,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 900 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 50 mA
- Efficacy: 90 lm/W

Packaging information

- Product family: LED
- EAN: 8719514258082
- EOC: 871951425808200
- Product title: Ace Saver 10W CW B22

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage: 10 W
- Wattage equivalent: 75 W

Product dimensions and weight

- Length: 10.7 cm

Rated values

- Rated luminous flux: 900 lumen
- Rated power: 10 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8719514258082
- Net weight: 44.000 g
- Gross weight: 58.000 g
- Height: 10.300 cm
- Length: 5.650 cm
- Width: 5.650 cm
- Material number (12NC): 929002264613



Issue date: 2023-11-08
Version: 0.158

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com