

# PHILIPS

Downlight

Functional

Prime Plus

White

8719514258662



## High quality LED light designed to last for years

Philips LED luminaires provide light that is designed for the comfort of your eyes.

### **Easy to experience**

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### **Light effect**

- Bright light with uniform distribution

### **Premium quality**

- EyeComfort - light that's easy on the eyes

### **Durability**

- Long life span up to 25,000 hours

# Highlights

## Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Long life span up to 25,000 hours

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## Design and finishing

- Color: White
- Material: plastic

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

## Light characteristics

- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional

## Product dimensions & weight

- Cut out length: 15.2 cm
- Cut out width: 15.2 cm
- Height: 2.1 cm
- Length: 17 cm
- Net weight: 0.155 kg
- Width: 17 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 25,000 hour(s)
- Diameter: 170 mm
- Total lumen output fixture: 900
- Light color: 6500
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class II

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514258662
- Net weight: 0.199 kg
- Gross weight: 0.269 kg
- Height: 17.200 cm
- Length: 18.000 cm
- Width: 4.800 cm
- Material number (12NC): 929002248380



Issue date: 2023-01-06  
Version: 0.42

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)