

PHILIPS

Recessed spot light

myLiving

Thin Trim COB

White

8719514265684



Comfortable light with a slimmer fit

Thin Trim COB has very minimalistic trim which blends well with the ceiling. This COB provides focussed 36 degree light beam to highlight the objects and the light source is deep recessed so gives glare free light

Match your interior

- Expressive and elegant form

Light effect

- Bright and focused beam

Premium quality

- Durable and impact resistant die-cast aluminum housing

Durability

- Long life span up to 30,000 hours

Highlights

Expressive and elegant form

A clean, modern design provides elegance and sophistication to your rooms.

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

- Color: White
- Material: metal

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: No

Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom

Product dimensions and weight

- Net weight: 0.22 kg
- Cut out length: 8.1 cm
- Cut out width: 8.1 cm
- Height: 12 cm
- Length: 9.2 cm
- Width: 9.2 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 35,000 hour(s)
- Diameter: 92 mm
- Total lumen output fixture: 1260
- Light color: 3000
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 18
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC – product: 8719514265684
- Net weight: 0.220 kg
- Gross weight: 0.300 kg
- Height: 14.000 cm
- Length: 10.700 cm
- Width: 9.700 cm
- Material number (12NC): 929001951972



Issue date: 2023-11-08
Version: 0.28

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com