

PHILIPS

Desk Lamp

Disinfection

24W

8719514286023



Home disinfection

The Philips UV-C disinfection desk lamp can effectively deactivate viruses, bacteria, molds and spores, in a matter of minutes. Built-in sensors and timers provide an added layer of protection for you and your family.

Disinfect your home from germs

- Disinfect your home from germs
- Simple to Use
- Fast disinfection
- Motion Sensor
- Expertize
- Dedicated driver design

Highlights

Disinfect your home from germs

All bacteria and viruses tested to date respond to UV-C disinfection. In laboratory tests, our UV-C light sources reduced SARS-CoV-2 (the virus that causes COVID-19) infectivity on a surface to below detectable levels in as few as 9 seconds

Simple to Use

The Philips UV-C desk lamp is easy to use. With a concise control panel and step-by-step voice guide to help you use it in the most effective way.

Fast disinfection

With the Philips UV-C desk lamp you can disinfect surfaces and objects in any room in a matter of minutes

Motion Sensor

Because exposure to UV-C can harm eyes and skin, Philips UV-C lights have an added layer of protection with built-in sensors that detect people and pets

Expertize

Philips has 35+ years experience in UV-C lighting and strong application expertize.

Dedicated driver design

Besides the high quality of the Philips UV-C tube, the dedicated driver design helps maximize the disinfection effectiveness.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: UV-C Desk Lamp
- Technology: UV-C

Durability

- Nominal lifetime: 9,000 hour(s)
- Number of switch cycles: 20,000

Packaging information

- EAN: 8719514286023
- EOC: 871951428602300
- Product title: UVC disinfection desk lamp 24W S Indo

Power consumption

- Voltage: 220/240 V
- Wattage: 24 W

Product dimensions & weight

- Height: 24.7 cm
- Length: 12 cm
- Net weight: 0.8 kg
- Width: 12 cm

Packaging dimensions and weight

- EAN/UPC - product: 8719514286023
- Net weight: 0.812 kg
- Gross weight: 1.072 kg
- Height: 28.100 cm
- Length: 16.400 cm
- Width: 16.400 cm
- Material number (12NC): 929002472907



Issue date: 2023-11-08
Version: 0.223

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com