

PHILIPS

Wall light

Led outdoor

22 W

Metal

Chrome

3000 K

919215000122



Superior Illumination

Polished chrome finish. White glass shade. Optimum performance

Light effect

- Provides a bright white light
- Special formulated coating insures a more glare-free light

Sustainable light solutions

- High quality LED light

Beacon of trust

- You can trust what the Philips packaging is saying

Premium quality

- Durable metallic housing

Highlights

Superior light quality
Diffused glare-free light
High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Durable metallic housing

Specifications

Bulb characteristics

- Intended use: Outdoor

Design and finishing

- Color: Chrome
- Material: Metal

Extra feature/accessory incl.

- Anti rust anti dust: Yes
- Centerpiece: Yes
- Diffused light effect: Yes
- LED integrated: Yes
- Made for LED only: Yes
- Perfectly suited for up/down mounting: Yes
- Photometric data available: Yes
- Premium quality material: Yes
- Resistant high quality material: Yes
- Warm White Light: Yes
- Waterproof: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom
- Style: Expressive
- Type: Wall Lights
- EyeComfort: Yes

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 2000
- Bulb technology: LED
- Light color: 2700/4000/6500
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 22
- IP code: IP20

Packaging dimensions and weight

- Net weight: 1.29 kg
- Gross weight: 0.31 kg
- Height: 13.8 cm
- Length: 59 cm
- Width: 10.3 cm
- Material number (12NC): 919215000122



Issue date: 2024-02-02
Version: 0.303

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com