

PHILIPS

Wall light

Led outdoor

10 W

Aluminium

Grey

IP 65

919215850777



IP 44 fixtures ideal for gardens

Grey powder coated aluminium fixture. Sleek design. Warm white light

Ease of use

- Moisture resistant

Light effect

- Provides a bright white light

Sustainable light solutions

- High quality LED light

Beacon of trust

- You can trust what the Philips packaging is saying

Premium quality

- Die-casted aluminum for a premium look and feel

Highlights

Moisture resistant
Superior light quality
High quality LED light



The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Premium materials



Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Specifications

Bulb characteristics

- Intended use: Outdoor

Design and finishing

- Color: grey
- Material: aluminium

Extra feature/accessory incl.

- Anti rust anti dust: Yes
- Bi-directional light beams: Yes
- Centerpiece: Yes
- Diffused light effect: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Made for LED only: Yes
- Perfectly suited for up/down mounting: Yes
- Photometric data available: Yes
- Premium quality material: Yes
- Resistant high quality material: Yes
- Warm White Light: Yes
- Waterproof: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Expressive
- Type: Wall light

Power consumption

- Energy Efficiency Label (EEL): Built in LED

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output light fixture: 670
- Bulb technology: LED
- Light color: 3000K
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 10
- IP code: IP65
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696763049
- Net weight: 0.800 kg
- Gross weight: 0.850 kg
- Height: 7.500 cm
- Length: 17.500 cm
- Width: 11.000 cm
- Material number (12NC): 919215850777



Issue date: 2020-10-12
Version: 0.257

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com