

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED BULBS

INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

🕒
15,000h

⊗
non dimmable



MZD LED 40W E27 840 A60 ND 1CT/6

12NC: **929002060332**
EAN1: **3139188161436**

5 WATT **>** **40** WATT **4000 K**
500 lm



MZD LED 100W E27 827 A67 FR ND 1CT/6

12NC: **929001252932**
EAN1: **3139188161535**

14 WATT **>** **100** WATT **2700 K**
1521 lm

Product type	Lamp Type	Energy consumption	Switch Cycle (times)	Color temperature K	Lumen output lm	Dimensions W x H	12NC	EAN1
MZD LED 40W E27 840 A60 ND 1CT/6	A60	5	15000	4000	470	60 x 105	929002060332	3139188161436
MZD LED 40W E27 827 A60 ND 1CT/6	A60	5	15000	2700	470	60 x 105	929002061732	3139188161412
MZD LED 40W A60 E27 865 FR ND 1CT/6	A60	5	15000	6500	470	60 x 105	929002060732	3139188162266
MZD LED 60W A60 E27 827 FR ND 1CT/6	A60	9	15000	2700	806	60 x 105	929001913132	3139188161450
MZD LED 60W A60 B22 WW FR ND RF 1BC 1CT/6	A60	9	15000	2700	806	60 x 105	929001913532	3139188162969
MZD LED 60W A60 E27 CDL FR ND 1CT/6	A60	9	15000	6500	806	60 x 105	929001913432	3139188162327
MZD LED 60W A60 E27 840 FR ND 1CT/6	A60	9	15000	4000	806	60 x 105	929001913332	3139188161474
MZD LED 60W A60 E27 840 FR ND 2CT/5*	A60	9	15000	4000	806	60 x 105	929001913333	3139188163522
MZD LED 75W A60 E27 827 FR ND 1CT/6	A60	11	15000	2700	1055	60 x 120	929001365532	3139188161498
MZD LED 75W A60 E27 840 FR ND 1CT/6	A60	10	15000	4000	1055	60 x 120	929001365632	3139188161511
MZD LED 75W A60 E27 865 FR ND 1CT/6	A60	10	15000	6500	1055	60 x 120	929001359132	3139188162488
MZD LED 100W E27 827 A67 FR ND 1CT/6	A67	14	15000	2700	1521	60 x 120	929001252932	3139188161535
MZD LED 100W A60 E27 CDL FR ND 1CT/6	A67	14	15000	6500	1521	60 x 120	929001359232	3139188162501

* Multipack

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED BULBS

INSTANT ENERGY SAVINGS

80
CRI

220-240 Vac

15,000h

non dimmable

Product type	Lamp Type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm			
MZD LEDCLA 40W A60 E27 827 CL ND 1CT/10	A60	5	20000	2700	470	60 x 104	929001890032	3139188163768
MZD LEDCLA 40W A60 E27 840 CL ND 1CT/10	A60	5	20000	4000	470	60 x 104	929002214432	3139188163782
MZD LEDCLA 60W A60 E27 827 CL ND 1CT/10	A60	7	20000	2700	806	60 x 104	929001387332	3139188163805
MZD LEDCLA 60W A60 E27 840 CL ND 1CT/10	A60	7	20000	4000	806	60 x 104	929002062532	3139188163829
MZD LEDCLA 75W A60 E27 827 CL ND 1CT/10	A60	8	20000	2700	1055	60 x 104	929002061032	3139188163843
MZD LEDCLA 75W A60 E27 840 CL ND 1CT/10	A60	8	20000	4000	1055	60 x 104	929002060432	3139188163867
MZD LEDCLA 100W A70 E27 827 CL ND 1CT/10	A70	11	20000	2700	1521	70 x 126	929002062132	3139188164086
MZD LEDCLA 100W A70 E27 840 CL ND 1CT/10	A67	14	15000	4000	1521	65x120	929002214132	3139188164208



**MZD LEDCLA 40W A60 E27
827 CL ND 1CT/10**

12NC: **929001890032**
EAN1: **3139188163768**

5 WATT **>** **40** WATT **2700 K**
470 lm



**MZD LEDCLA 100W A70 E27
827 CL ND 1CT/10**

12NC: **929002062132**
EAN1: **3139188164086**

11 WATT **>** **100** WATT **2700 K**
1521 lm