

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED TUBES FOR BRIGHTER LIGHTING

A⁺
EEI label

80
CRI


⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⊗
non dimmable

Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	8718696717455
MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	8718696717479
MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	8718696717417
MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	8718696717431
MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	8718696717370
MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	8718696717394
MZD LED PLC 7.5W 840 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	3139188162983
MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	3139188163003
MZD LED PLC 9W 840 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	3139188163027
MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	3139188163041



**MZD LED tube 1200mm
14.5W 840**

12NC: **929001855832**
EAN1: **8718696717417**

14.5 WATT > **36** WATT **4000 K**
1600 lm



**MZD LED PLC
7.5W 865**

12NC: **929001879132**
EAN1: **3139188163003**

7.5 WATT > **13** WATT **6500 K**
806 lm

**GREAT LIGHT,
SOLID DESIGN**

MAZDA TSHAPES FOR BRIGHTER LIGHTING

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⊗
non dimmable

Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LED 26-24W E27 830 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	929001937632	3139188164260
MZD LED 28-24W E27 840 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	929001937732	3139188164284
MZD LED 48-42W E27 830 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	929001938232	3139188164222
MZD LED 50-42W E27 840 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	929001938332	3139188164246



**MZD LED 26-24W E27
830 HB 1CT/6**

12NC: **929001937632**
EAN1: **3139188164260**

24 WATT **40** WATT **3000 K**
2600 lm



**MZD LED 50-42W E27
840 HB 1CT/6**

12NC: **929001938332**
EAN1: **3139188164246**

42 WATT **70** WATT **4000 K**
5000 lm