


**GREAT LIGHT,
SOLID DESIGN**

MAZDA INDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS

Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
	lm	W	K					
Batten								
MAZDA BN007C LED32S/840 PSU L1200	3200	32	4000	IP20		I	911401800480	8710163338040
Wallmount								
MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	4000	IP65 / IK06		II	911401800880	8710163338088
MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	4000	IP54 / IK06	Yes	II	911401800780	8710163338071
Waterproof								
MAZDA WT007C LED17S/740 PSU L600	1700	17	4000	IP65 / IK06		II	911401800980	8710163338774
MAZDA WT007C LED34S/740 PSU L1200	3400	34	4000	IP65 / IK06		II	911401800580	8710163338057
MAZDA WT007C LED54S/740 PSU L1500	5400	54	4000	IP65 / IK06		II	911401800680	8710163338064



**MAZDA BN007C LED32S/840
PSU L1200**

12NC: **911401800480**
EAN1: **8710163338040**

1200 mm
IP20




**MAZDA WL007C LED13S/740
PSU RND MDU WH**

12NC: **911401800880**
EAN1: **8710163338088**

IP54 / IK06

Silver trim included
Motion sensor



**MAZDA WT007C LED54S/740
PSU L1500**

12NC: **911401800680**
EAN1: **8710163338064**

1500 mm
IP65 / IK06

**GREAT LIGHT,
SOLID DESIGN**

MAZDA INDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS



**MZD DN020B LED12/830
16W 220-240V WH**

12NC: **929002219402**
EAN1: **3139188163645**

3000 K
1200 lm



**MZD SL252 EC RD 070
3W 27K W HV 06**

12NC: **929002222432**
EAN1: **3139188164000**

2700 K
200 lm

Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
	lm	W	K					
Downlights								
MZD DN020B LED12/830 16W 220-240V WH	1200	16	3000	IP20 / IK03		II	929002219402	3139188163645
MZD DN020B LED12/840 16W 220-240V WH	1200	16	4000	IP20 / IK03		II	929002219502	3139188163669
MZD DN020B LED12/865 16W 220-240V WH	1200	16	6500	IP20 / IK03		II	929002219602	3139188163683
MZD DN020B LED20/830 24W 220-240V WH	2000	24	3000	IP20 / IK03		II	929002219702	3139188163706
MZD DN020B LED20/840 24W 220-240V WH	2000	24	4000	IP20 / IK03		II	929002219802	3139188163720
MZD DN020B LED20/865 24W 220-240V WH	2000	24	6500	IP20 / IK03		II	929002219902	3139188163744
Spots								
MZD SL252 EC RD 070 3W 27K W HV 06	200	3	2700	IP20 / IK03		II	929002222432	3139188164000
MZD SL252 EC RD 070 3W 40K W HV 06	210	3	4000	IP20 / IK03		II	929002222532	3139188164024
MZD SL252 EC RD 070 5W 27K W HV 06	330	5	2700	IP20 / IK03		II	929002222632	3139188164048
MZD SL252 EC RD 070 5W 40K W HV 06	350	5	4000	IP20 / IK03		II	929002222732	3139188164062