

# LÂMPADAS LED MAZDA

## POUPANÇA ENERGÉTICA IMEDIATA

**80**

CRI



220-240 Vac



15,000h



Não regulável



**MZD LED 40W E27 840 A60 ND 1CT/6**

12NC: **929002060332**  
EOC: **16143601**

**5** WATT **40** WATT **4000 K**  
**500 lm**



**MZD LED 100W E27 827 A67 FR ND 1CT/6**

12NC: **929001252932**  
EOC: **16153500**

**14** WATT **100** WATT **2700 K**  
**1521 lm**

Tipo de produto	Forma	Consumo de energia	Número de ligações	Temperatura de cor	Fluxo luminoso	Dimensões W x H	12NC	EOC
				K	lm			
MZD LED 40W E27 840 A60 ND 1CT/6	A60	5	15000	4000	470	60 x 105	929002060332	16143601
MZD LED 40W E27 827 A60 ND 1CT/6	A60	5	15000	2700	470	60 x 105	929002061732	16141201
MZD LED 40W A60 E27 865 FR ND 1CT/6	A60	5	15000	6500	470	60 x 105	929002060732	16226601
MZD LED 60W A60 E27 827 FR ND 1CT/6	A60	9	15000	2700	806	60 x 105	929001913132	16145002
MZD LED 60W A60 E27 CDL FR ND 1CT/6	A60	9	15000	6500	806	60 x 105	929001913432	16232701
MZD LED 60W A60 E27 840 FR ND 1CT/6	A60	9	15000	4000	806	60 x 105	929001913332	16147402
MZD LED 75W A60 E27 827 FR ND 1CT/6	A60	11	15000	2700	1055	60 x 120	929001365532	16149801
MZD LED 75W A60 E27 840 FR ND 1CT/6	A60	10	15000	4000	1055	60 x 120	929001365632	16151101
MZD LED 75W A60 E27 865 FR ND 1CT/6	A60	10	15000	6500	1055	60 x 120	929001359132	16248800
MZD LED 100W E27 827 A67 FR ND 1CT/6	A67	14	15000	2700	1521	60 x 120	929001252932	16153500
MZD LED 100W E27 840 A67 FR ND 1CT/6	A67	14	15000	4000	1521	60 x 120	929001365832	16155901
MZD LEDGlobe 100W E27 827 G93 FR ND 1CT/6	G93	14	15000	2700	1521		929001804632	16338600
MZD LEDGlobe 100W E27 865 G93 FR ND 1CT/6	G93	14	15000	6500	1521		929001804732	16340900
MZD LED 100W A60 E27 CDL FR ND 1CT/6	A67	14	15000	6500	1521	60 x 120	929001359232	16250100

GREAT LIGHT,  
SOLID DESIGN

# LÂMPADAS LED MAZDA

## POUPANÇA ENERGÉTICA IMEDIATA

80

CRI



220-240 Vac



15,000h



Não regulável

Tipo de produto	Forma	Consumo de energia	Número de ligações	Temperatura de cor	Fluxo luminoso	Dimensões W x H	12NC	EOC
				K	lm			
MZD LEDCLA 40W A60 E27 827 CL ND 1CT/10	A60	5	20000	2700	470	60 x 104	929001890032	16376800
MZD LEDCLA 40W A60 E27 840 CL ND 1CT/10	A60	5	20000	4000	470	60 x 104	929002214432	16378200
MZD LEDCLA 60W A60 E27 827 CL ND 1CT/10	A60	7	20000	2700	806	60 x 104	929001387332	16380500
MZD LEDCLA 60W A60 E27 840 CL ND 1CT/10	A60	7	20000	4000	806	60 x 104	929002062532	16382900
MZD LEDCLA 75W A60 E27 827 CL ND 1CT/10	A60	8	20000	2700	1055	60 x 104	929002061032	16384300
MZD LEDCLA 75W A60 E27 840 CL ND 1CT/10	A60	8	20000	4000	1055	60 x 104	929002060432	16386700
MZD LEDCLA 100W A70 E27 827 CL ND 1CT/10	A70	11	20000	2700	1521	70 x 126	929002062132	16408600
MZD LEDCLA 100W A70 E27 840 CL ND 1CT/10	A67	14	15000	4000	1521	65x120	929002214132	16420800



MZD LEDCLA 40W A60 E27  
827 CL ND 1CT/10

12NC: **929001890032**  
EOC: **16376800**

5 WATT > 40 WATT 2700 K  
470 lm



MZD LEDCLA 100W A70 E27  
827 CL ND 1CT/10

12NC: **929002062132**  
EOC: **16408600**

11 WATT > 100 WATT 2700 K  
1521 lm