

# TUBOS LED MAZDA

## ILUMINAÇÃO MAIS BRILHANTE

**A<sup>+</sup>**  
EEI label

**80**  
CRI


**⚡**  
220-240 Vac

**🕒**  
25,000h

**ON/OFF**  
50,000x

**⚠️**  
Não regulável

Tipo de produto	Forma	LED	Input atual	Frequência	Dimensões	12NC	EOC
		W	mA	Hz	mm		
MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	71745500
MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	71747900
MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	71741700
MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	71743100
MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	71737000
MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	71739400
MZD LED PLC 7.5W 840 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	16298300
MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	16300300
MZD LED PLC 9W 840 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	16302700
MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	16304100



**MZD LED tube 1200mm  
14.5W 840**

12NC: **929001855832**  
EOC: **71741700**

**14.5** WATT > **36** WATT      **4000 K**  
**1600 lm**



**MZD LED PLC  
7.5W 865**

12NC: **929001879132**  
EOC: **16300300**

**7.5** WATT > **13** WATT      **6500 K**  
**806 lm**

# DESCARGA LED MAZDA

## ILUMINAÇÃO MAIS BRILHANTE

**A<sup>+</sup>**  
EEI label

**80**  
CRI

**⚡**  
220-240 Vac

**🕒**  
25,000h

**ON  
OFF**  
50,000x

**⚠️**  
Não regulável

Tipo de produto	Forma	LED	Input atual	Frequência	Dimensões	12NC	EOC
		W	mA	Hz	mm		
MZD LED 26-24W E27 830 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	929001937632	16426000
MZD LED 28-24W E27 840 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	929001937732	16428400
MZD LED 48-42W E27 830 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	929001938232	16422200
MZD LED 50-42W E27 840 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	929001938332	16424600



**MZD LED 26-24W E27  
830 HB 1CT/6**

12NC: **929001937632**  
EOC: **16426000**

**24** WATT **40** WATT **3000 K**  
**2600 lm**



**MZD LED 50-42W E27  
840 HB 1CT/6**

12NC: **929001938332**  
EOC: **16424600**

**42** WATT **70** WATT **4000 K**  
**5000 lm**