



Product description	PILA LED 60W E27 WW A60 ND	PILA LED 15W E14 WW T25 ND	PILA LED 40W A60 E27 WW FR DIM 1CT/6	PILA LED 60W A60 E27 WW FR DIM 1CT/6
Light output (lm)	806	140	470	1055
Power (W)	9.5	15	6	9
сст (к)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240 / 50 Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	Yes	Yes
Lamp shape	Bulb	Bulb	A60	A60
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A+	A++	A+	A+
EAN	8718696485385	8718696485408	8727900964318	8727900964332
12NC				

Benefits • Energy efficient

Solutions for different ambiences





Product description	PILA LED 60W E27 CW A60 ND	PILA LED 75W A60 E27 CW FR ND 1CT/6	PILA LED 100W A67 E27 CW FR ND 1CT/6	PILA LED 60W A60 E27 WW FR ND 1CT/6
Light output (lm)	850	1100	1521	810
Power (W)	9.5	10	13	8
ССТ (К)	4000	4000	4000	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	200-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	No
Lamp shape	Bulb	A60	A67	A60
Color	Cool White	Cool White	Cool White	Warm White
Energy efficiency class	A+	A+	A+	A+
EAN	8718696491089	8727900964134	8727900964714	8727900964073
12NC				

Benefits ► Energy efficient

Solutions for different ambiences





Benefits • Energy efficient

Solutions for different ambiences





Product description	PILA LED 100W E27 WW A67 FR ND	Pila LEDClassic 60W A60 E27 WW ND	PILA LED 40W A60 E27 WW FR ND 1CT/6	Pila LEDClassic 40W A60 E27 WW ND 1CT/1
Light output (lm)	1521	806	1521	1055
Power (W)	15.5	7	14	12
ССТ (К)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	No
Lamp shape	Bulb	A60	A67	Bulb
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A+	A++	A+	A+
EAN	8718696526934	8727900963939	8727900963977	8718696526910
12NC				

Benefits • Energy efficient

Solutions for different ambiences





Product description	PILA LED 40W E27 CW A60 ND	PILA LED 40W E27 WW A60 ND	PILA LED 60W A60 E27 CW FR ND 1CT/6	PILA LED 75W A60 E27 WW FR ND 1CT/6
Light output (lm)	500	470	810	1055
Power (W)	5.5	5.5	7.5	10
ССТ (К)	4000	2700	4000	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	No
Lamp shape	Bulb	Bulb	A60	A60
Color	Cool White	Warm White	Cool White	Warm White
Energy efficiency class	A+	A+	A+	A+
EAN	8718696491065	8718696485361	8727900964097	8727900964110
12NC				

Benefits • Energy efficient

Solutions for different ambiences