



BUILT FOR SMALL AND MEDIUM PROJECTS



High-end residential



Multi-residential




Restaurant



Hospitality



Shop



EASY COMMISSIONING

Complicated wiring is now a thing of the past. Save time with the WiZ Pro Setup app for direct effortless and wireless commissioning, even when on-site Wi-Fi is not installed yet.



LOCAL WIRELESS CONTROL


Once you have the lights up and running, anyone can enjoy simple control via local accessories such as WiZ Pro smart switches, remotes and sensors.

CONNECTED LIGHTING FOR WELCOMING SPACES


Turning any application into a warm and inviting environment for guests, clients and home owners has become one of the key features that businesses look for in a connected lighting package. Now all this and more is available in one affordable turnkey solution enabling ambience creation – WiZ Pro.

Transform your own lighting into connected fixtures with WiZ Pro drivers, bridge boxes and customizable modules or choose between a wide range of lamps and accessories to market under your own brand. Opt for reliable everyday connectivity that caters to the needs of all stakeholders with the WiZ platform.

Enjoy the variety of connected lighting benefits:




Easy local and remote control of your lights



Various light scenes to fit your application



Automate lights for better energy efficiency



APP CONTROL

Once the lighting installation is connected to Wi-Fi, end users can control the lights from anywhere with the WiZ app. Customize your lighting to fit your application or choose between a variety of pre-designed light modes for a rich experience.



ADVANCED FACILITIES MANAGEMENT

WiZ Pro Dashboard goes even further by allowing (multiple) lighting installation(s) control and remote site management. Get actionable light insights and monitoring with a clear overview of the entire installation, once it's connected to Wi-Fi.

A SOFTWARE SOLUTION FOR EACH STAKEHOLDER

Enjoy hassle-free wireless installation and local control with the WiZ app, as well as full control with cloud connectivity with WiZ Pro Setup app and WiZ Pro Dashboard. Enable a solution for each stakeholder with the WiZ Pro software suite that comes embedded within your WiZ Pro hardware.

WiZ PRO SETUP APP

WiZ Pro is plug-and-play, so basic set up is easy with the WiZ Pro Setup app through wireless direct commissioning, no gateway or Wi-Fi needed. Follow the step-by-step instructions on screen: add your products, decide which room you want them to be in and perform tests to make sure they work before you hand it over. Wireless accessories ensure easy, local control for everyday connectivity.



WiZ APP

Be a lighting designer, mix and match light modes or enjoy pre-defined Scenes to create the perfect ambience - to enhance the shopping experience or to entertain clients and friends when they come and visit. Discover the special human-centric lighting feature - Circadian Rhythm - which offers a smooth transition from cool white early in the cycle to warm white later on.



WiZ PRO DASHBOARD

Get the full picture and visualize where your lights are located within a space once you upload the area's floor plan. Set and supervise remotely the status of your lights and devices in any and all the locations you're managing. Each light's usage will be reported, including their remaining lifespan for predictive maintenance.



CREATE YOUR OWN WELCOMING SPACE. GET IN TOUCH WITH US TODAY.

WiZ Pro is an innovative new way to turn your OEM lighting products into smart solutions that create warm and comfortable ambiances. To know more about WiZ Pro and get in touch with a local representative, access wizconnected.com/en-us/business/pro.

BRING YOUR PRODUCTS ONTO THE WiZ PLATFORM

Choose from a wide range of WiZ Pro drivers, lamps and luminaires. If you want your own WiZ Pro products, our team will work with you to create a tailor-made solution. More WiZ Pro hardware products will be coming soon.



DRIVERS

Product name	12NC	Housing mm	Dimming range %	Output power range W	Output current A	Output voltage range V	Life time h
Xitanium 8W 0.15/0.2A 42V WiZ DM 230V	929003483606	115x45x29	10-100	4.5-8.4	0.15/0.2	30-42dc	50000
Xitanium 8W 0.15/0.2A 42V WiZ TW 230V	929003483706	115x45x29	10-100	4.5-8.4	0.15/0.2	30-42dc	50000
Xitanium 13W 0.25/0.3A 42V WiZ DM 230V	929003483806	115x45x29	10-100	7.5-12.6	0.25/0.3	30-42dc	50000
Xitanium 13W 0.25/0.3A 42V WiZ TW 230V	929003483906	115x45x29	10-100	7.5-12.6	0.25/0.3	30-42dc	50000
Xitanium 44W 0.7-1.05A 42V WiZ DM 230V	929002890006	108x68x32	10-100	21-44	0.7/0.8/0.9/1.05	30-42dc	50000
Xitanium 44W 0.7-1.05A 42V WiZ TW 230V	929002890106	108x68x32	10-100	21-44	0.7/0.8/0.9/1.05	30-42dc	50000

BRIDGE BOXES

Product name	12NC	Housing mm	Dimming range %	Dimming method	Input voltage V	No. of output channel	Life time h
WiZ Pro Phase-cut Bridge Box I 220-240V	929002613409	87.5x41x28	10-100	Trailing-Edge	220-240AC	1	50000
WiZ Pro 1-10V Bridge Box I 220-240V	929002613509	87.5x41x28	1-10.5V	1-10V	220-240AC	1	50000
WiZ Pro DW Bridge Box I 12-24V	929002499409	87.5x41x28	5-100	PWM	12-24DC	1	50000
WiZ Pro TW Bridge Box I 12-24V	929002499509	87.5x41x28	5-100	PWM	12-24DC	2	50000
WiZ Pro RGBTW Bridge Box I 12-24V	929002613309	87.5x41x28	5-100	PWM	12-24DC	5	50000

LED LAMPS

Product name	12NC	Cap	Bulb shape	Lamp wattage claim W	CCT K	Lumen lm	CRI	Life time h
WiZ Pro PAR16 GU10 TW 4.9W 230V	929002448371	GU10	PAR16	4.9	2700-6500	345	90	15000
WiZ Pro PAR16 GU10 RGBTW 4.9W 230V	929002448471	GU10	PAR16	4.9	2200-6500	345	90	15000
WiZ Pro C37 E14 TW 4.9W 230V	929002448771	E14	C37	4.9	2700-6500	470	90	15000
WiZ Pro C37 E14 RGBTW 4.9W 230V	929002448871	E14	C37	4.9	2200-6500	470	90	15000
WiZ Pro A60 E27 TW 8W 230V	929002383571	E27	A60	8	2700-6500	806	90	25000
WiZ Pro A60 E27 RGBTW 8W 230V	929002383671	E27	A60	8	2200-6500	806	90	25000
WiZ Pro A60 B22 TW 8W 230V	929002383771	B22	A60	8	2700-6500	806	90	25000
WiZ Pro A60 B22 RGBTW 8W 230V	929002383871	B22	A60	8	2200-6500	806	90	25000
WiZ Pro A67 E27 TW 13W 230V	929002449671	E27	A67	13	2700-6500	1521	90	15000
WiZ Pro A67 E27 RGBTW 13W 230V	929002449771	E27	A67	13	2200-6500	1521	90	15000
WiZ Pro G95 E27 TW 11W 230V	929002451071	E27	G95	11	2700-6500	1055	90	25000
WiZ Pro G95 E27 RGBTW 11W 230V	929002383971	E27	G95	11	2200-6500	1055	90	25000

LED STRIPS

Product name	12NC	Plug type	Cord length mm	Lamp wattage claim W	CCT K	Lumen lm	CRI	Life time h
WiZ Pro LED Strip 2M Kit-C	929002681171	EU plug	1500	20	2200-6500 (RGB)	1600	80	15000
WiZ Pro LED Strip 2M Kit-G	929002681271	BS plug	1500	20	2200-6500 (RGB)	1600	80	15000
WiZ Pro LED Strip 1M Ext-1	929002681471	-	-	11	2200-6500 (RGB)	800	80	15000

ACCESSORIES

Product name	12NC	Housing mm	Input voltage V	Control terminals	Signal range m	Life time h
WiZ Pro Switch Module 220-240V	929003484281	45x45x18.3	220-240AC	9	15	50000
WiZ Pro Switch Module 9-40V	929003484381	45x45x18.3	9-40DC	9	15	50000

WIRELESS ACCESSORIES

Product name	12NC	Housing cm	Color	Control distance m	Radio Protocol	Power Source battery	Battery Life year
WiZ Pro Remote Control	929002426871	13.5x3.8x1.5	Black	15	Wi-fi /2.4GHz	2x LR03 AAA	1
WiZ Pro Wireless Sensor	929002422371	6.2x6.2x5	White	15	Wi-fi /2.4GHz	2x LR03 AAA	1

MODULES

WiZ Pro modules are designed to fit your custom product specifications. Operating on Wi-Fi + Bluetooth standard protocols, the modules enable the wireless IoT benefits brought by the WiZ Pro smart lighting platform, as well as ease of installation and scalability. Due to their small size, you have the flexibility to integrate them in a range of luminaire designs. Enabling various dynamic light scenes with Tunable White and a variation of colors, the WiZ Pro modules cater to the needs of any application. To find out how you can benefit from integrating WiZ Pro modules into your products, please contact the WiZ team via wizconnected.com/en-us/business/pro.