

# SmartBright Slim Panel G2


## RC09IV

Mounting Instruction/安裝說明書

V1.0





Type/ 型號	CCT (K)	Power(W) /功率	LEDs	Lumen Output (lm) /流明輸出(lm)	Dimension /尺寸 LxWxH (mm)	kg	Voltage /電壓	Frequency /頻率
RC09IV LED36S/840 PSU W60L60 TW SI	4000	40	208	3600	603X603X36	2.15	100-240V~	50/60Hz
RC09IV LED36S/865 PSU W60L60 TW SI	6500							




Please do not put any pressure on the back and the driver.  
請不要使背板和驅動受力

### Power connection/電源連接




### A Visible Profile Ceiling Mounting(VPC) / 嵌入式安裝



委製/進口商：台灣飛利浦照明股份有限公司  
地址：台北市南港區園區街3-1號15樓之一  
產地：荷蘭飛利浦照明授權於中國製造  
電話：0800-808-268


# PHILIPS

## B Plaster Ceiling Version Mounting(PCV) / 石膏板安裝




Cutout size/石膏板開口尺寸  
 W60L60: 580\*580mm (+/-2mm)  
 W30L120: 280\*1180mm (+/-2mm)  
 Ceiling thickness/石膏板厚度  
 : 8mm-16mm


1



2



3




4



5


These 4 springs are not included in package.  
 If the customer need to use, please buy it.  
 PCV Accessory 12 NC: 9114 017 24242  
 這4個彈簧不包含在包裝裏面。  
 如果客戶需要，請購買。  
 PCV附件12NC: 9114 017 24242

## C Suspension Mounting (SUS) / 懸吊安裝




These 4 suspension wires are not included in package.  
 If the customer need to use, please buy it.  
 Suspension kit Accessory 12 NC: 9114 017 24252  
 這4個吊鏈不包含在包裝裏面。如果客戶需要，請購買。  
 懸吊附件12 NC: 9114 017 24252

## Safety Chain / 安全鏈



The product (include A、B mounting types) should install safety chain  
 (Safety chain is not included in package.)

產品(包括A、B兩種安裝方式) 需要安裝安全鏈 (安全鏈不包含在包裝裏面)



Please read this manual carefully before using the product.

1. For indoor use only.
2. Do not switch on before complete installation.
3. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
4. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
5. The luminaire shall not be covered with thermal insulation or similar material under any circumstance.
6. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
7. The luminaire is complied with IEC 60598 and GB 7000.
8. The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc. must be avoided during the use and storage.

在使用產品前請仔細閱讀這個安裝說明書：

1. 僅適用於室內燈具；
2. 接線過程中，切勿通電；
3. 此燈具應由有資格的電工安裝，接線要符合IEE電氣標準或國家標準；
4. 如果此燈具的外部軟纜或軟線損壞了，該線要由製造商或其服務代理商或一個類似的有資格的人來更換，以避免發生危險；
5. 燈具不能被隔熱或類似材料覆蓋；
6. 此燈具的光源應由製造商或其服務代理商或一個類似的有資格的人來更換；
7. 此燈具是依據IEC60598所製造；
8. 此燈具避免在腐蝕性環境或者含有有害物質，例如硫化物，鹵化物，鄰苯二甲酸酯等環境中存儲和使用。
9. 限用物質含有情況標示資訊請參考飛利浦網址<http://www.deco.philips.com.tw/RoHS>

維修方式：

若燈具出現故障，請立即停止使用並關閉電源，聯絡專業人員處理。