



產品說明

MASTER PL-C 4 Pin

省電型精巧螢光燈管精巧型長電弧低壓水銀放電燈管套管內含 4 個平行細長螢光燈管

优点

- 每次開燈，無論時間長短，都能展現最佳的照明狀態
- 使用壽命長，光量輸出不衰減

特点

- 4 接腳基座，無點燈器和電容
- 燈管特性取決於操作條件與採用何種控制裝置
- 可調光

应用

- 適用於專業或居家環境的一般或輔助照明
- 嵌入式或吸頂式嵌燈、壁燈、桌燈和吊燈

安全提示


- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 4 Pin

Versions



二维绘图



Product

MASTER PL-C 13W/827/4P 1CT/5X10CC

MASTER PL-C 26W/827/4P 1CT/5X10CC

MASTER PL-C 26W/840/4P 1CT/5X10BOX

MASTER PL-C 26W/830/4P 1CT/5X10CC

應用

能源效益標章 (EEL)	A
汞 (Hg) 含量 (標稱)	1.4 mg

控制調光

可調光	是
-----	---

基本資訊

壽命 (預熱故障率 50%) (標稱)	13000 h
額定 LSF 預熱 2000 h	99 %
額定 LSF 預熱 4000 h	98 %
額定 LSF 預熱 6000 h	97 %
額定 LSF 預熱 8000 h	90 %

照明科技

顯色指數 (Nom)	82
額定 LLMF 2000 h	92 %
額定 LLMF 4000 h	87 %
額定 LLMF 6000 h	83 %
額定 LLMF 8000 h	81 %

溫度

設計溫度 (標稱)	28 °C
-----------	-------

應用

Order Code	Full Product Name	能源消耗 kWh/1000 h
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10CC	15 kWh
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10CC	29 kWh
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10CC	29 kWh
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	29 kWh

運作和電氣

MASTER PL-C 4 Pin

Order Code	Full Product Name	燈具電流 (標稱)	功率 (額定)(標稱)
927907182701	MASTER PL-C 13W/827/4P 1CT/ 5X10CC	0.170 A	13.0 W
927907382701	MASTER PL-C 26W/827/4P 1CT/ 5X10CC	0.335 A	26.0 W

Order Code	Full Product Name	燈具電流 (標稱)	功率 (額定)(標稱)
927907383001	MASTER PL-C 26W/830/4P 1CT/ 5X10CC	0.335 A	26.0 W
927907384002	MASTER PL-C 26W/840/4P 1CT/ 5X10BOX	0.335 A	26.0 W

基本資訊

Order Code	Full Product Name	接口
927907182701	MASTER PL-C 13W/827/4P 1CT/5X10CC	G24Q-1
927907382701	MASTER PL-C 26W/827/4P 1CT/5X10CC	G24Q-3

Order Code	Full Product Name	接口
927907383001	MASTER PL-C 26W/830/4P 1CT/5X10CC	G24Q-3
927907384002	MASTER PL-C 26W/840/4P 1CT/5X10BOX	G24Q-3

照明科技 (1/2)

Order Code	Full Product Name	色碼	色彩名稱	相關色溫 (標稱)	光效 (額定) (Nom)
927907182701	MASTER PL-C 13W/ 827/4P 1CT/5X10CC	827	白熾 白色	2700 K	69 lm/W
927907382701	MASTER PL-C 26W/ 827/4P 1CT/5X10CC	827	白熾 白色	2700 K	67 lm/W

Order Code	Full Product Name	色碼	色彩名稱	相關色溫 (標稱)	光效 (額定) (Nom)
927907383001	MASTER PL-C 26W/ 830/4P 1CT/5X10CC	830	暖白色 (WW)	3000 K	67 lm/W
927907384002	MASTER PL-C 26W/ 840/4P 1CT/5X10BOX	840	冷白色 (CW)	4000 K	67 lm/W

照明科技 (2/2)

Order Code	Full Product Name	光通量 (標稱)	光通量 (額定)(標稱)
927907182701	MASTER PL-C 13W/827/4P 1CT/ 5X10CC	925 lm	925 lm
927907382701	MASTER PL-C 26W/827/4P 1CT/ 5X10CC	1800 lm	1800 lm

Order Code	Full Product Name	光通量 (標稱)	光通量 (額定)(標稱)
927907383001	MASTER PL-C 26W/830/4P 1CT/ 5X10CC	1800 lm	1800 lm
927907384002	MASTER PL-C 26W/840/4P 1CT/ 5X10BOX	1800 lm	1800 lm

