



# Perfect sparkle, simple use

# MASTERColour CDM-R Elite

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

### **Benefits**

- High-efficiency lamp producing crisp white sparkling light that makes merchandise look irresistible
- · Lamp is easy to install and provides superior light from start to finish
- Stable color and lumen output over life keeps your store attractive season after season
- · Unique crisp white sparkling light makes merchandise irresistible
- Easy to install and replace, reducing installation and relamping costs
- · Unrivalled combination of high lumen output and excellent lumen maintenance

# Features

- · Crisp white sparkling light
- Excellent colour rendering (Ra 90) and high efficacy
- $\boldsymbol{\cdot}$  Excellent color rendering, with extra red
- · Unparalleled lumen maintenance
- · High efficacy combined with unparalleled lumen maintenance
- · UV-blocking front glass to reduce risk of merchandise fading
- · Fits in simple open luminaires
- · Fits in simple open luminaires
- UV-blocking front glass
- Easy to install and replace

# **MASTERColour CDM-R Elite**

## **Application**

- · Accent and display lighting retail
- · Accent lighting in retail and hospitality
- · General and decorative indoor lighting
- · General and decorative lighting

### **Warnings and Safety**


- · Use only with electronic control gear
- · Use only with electronic control gear
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Versions



LPPR CDM-R-E 0005

# Dimensional drawing






Product	D (max)	C (max)
MC CDM-R Elite 35W/930 E27 PAR30L 30D	97 mm	123 mm


# **MASTERColour CDM-R Elite**

### **Accent Diagrams**



Accent Diagram - MC CDM-R Elite 35W/930 E27 PAR30L 30D

# **Beam Diagrams**



Beam diagram - MC CDM-R Elite 35W/930 E27 PAR3OL 30D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.