

High performance, extra low mercury

Advantage T8

Philips Advantage T8 lamps are an energy-efficient solution and offer high lumen output.

Benefits

- Reduced impact on the environment without sacrificing performance
- Better for the environment--only 1.7mg of mercury with ALTO II Technology

Features

- High lumens enable multiple system options to maximize energy savings and reduce lighting costs
- Fully dimmable without burn-in
- · Available in multiple wattages: 17W, 25W, and 32W
- Available in multiple color temperatures: 3000K, 3500K, 4100K & 5000K

Application

· Ideal for applications requiring maximum light output.

Warnings and Safety

- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- · See: www.lamprecycle.org or 1-800-555-0050

Advantage T8


Versions



G13, T8

Dimensional drawing

Product
F32T8/ADV830 ALTO 30PK
F32T8/ADV835 ALTO 30PK
F32T8/ADV841 ALTO 30PK
F32T8/ADV850 ALTO 30PK



Approval and application		
Energy Saving Product	Energy Saving	
Mercury (Hg) Content (Nom)	1.7 mg	
Picogram Per Lumen Hour	24 pg/lm.h	
Operating and electrical		
Power (Nom)	32 W	
General information		
Cap-Base	G13	
Life 12-Hr Instant Start [Hrs]	30000 h	
Life 12-Hr Programstart [Hrs]	36000 h	
Life 3-Hr Instant Start [Hrs]	24000 h	
Life 3-Hr Program Start [Hrs]	30000 h	
Mechanical and housing		
Bulb Shape	Т8	

Light technical (1/2)

					Color
				Correlated Color	Rendering
Order Code	Full Product Name	Color Code	Color Designation	Temperature (Nom)	Index (Nom)
280800	F32T8/ADV830 ALTO 30PK	Advantage 830	Advantage 830	3000 K	85
280818	F32T8/ADV835 ALTO 30PK	Advantage 835	Advantage 835	3500 K	85
280859	F32T8/ADV841 ALTO 30PK	Advantage 841	Advantage 841	4100 K	85
280891	F32T8/ADV850 ALTO 30PK	Advantage 850	Advantage 850	5000 K	82

Light technical (2/2)

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
280800	F32T8/ADV830 ALTO 30PK	3000 lm	3100 lm
280818	F32T8/ADV835 ALTO 30PK	3000 lm	3100 lm

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Nom)
280859	F32T8/ADV841 ALTO 30PK	3000 lm	3100 lm
280891	F32T8/ADV850 ALTO 30PK	2935 lm	3025 lm

Advantage T8



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.