



# Retail Sales T8

## Retail Sales T8

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Versions




G13, T8

G13, T8

## Retail Sales T8

### Dimensional drawing



#### Product

F15T8 BRIGHT WHITE/18 ALTO SL6

F15T8/COOL WHITE PLUS/18 ALTO SL 6

F15T8/NATURAL SUNSHINE SL6

#### Product

F15T8/PLANT/18 6PK

#### General Information

Cap-Base G13

#### Mechanical and Housing

Bulb Shape T8

### Approval and Application

Order Code	Full Product Name	Energy	
		Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
392266	F15T8/PLANT/18 6PK	-	5.0 mg
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	-	2.0 mg

Order Code	Full Product Name	Energy	
		Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	A	2.0 mg
392290	F15T8/NATURALSUNSHINE 6/1	B	2.0 mg

### Operating and Electrical

Order Code	Full Product Name	Lamp		Power (Rated) (Nom)
		Current (Nom)	Voltage (Nom)	
392266	F15T8/PLANT/18 6PK	-	-	15 W
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	0.335 A	55 V	15.5 W

Order Code	Full Product Name	Lamp		Power (Rated) (Nom)
		Current (Nom)	Voltage (Nom)	
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	0.335 A	55 V	15.5 W
392290	F15T8/NATURALSUNSHINE 6/1	0.335 A	55 V	15.5 W

### General Information

## Retail Sales T8

Order Code	Full Product Name	Life To 10%	Life To 50%	Life 3-Hr Start [Hrs]
		Failures (Nom)	Failures (Nom)	
392266	F15T8/PLANT/18 6PK	-	-	7500 h
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	10000 h	13000 h	-

Order Code	Full Product Name	Life To 10%	Life To 50%	Life 3-Hr Start [Hrs]
		Failures (Nom)	Failures (Nom)	
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	10000 h	13000 h	-
392290	F15T8/NATURALSUNSHINE 6/1	10000 h	13000 h	-

### Light Technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated Color	Color	Lumen	Lumen	Lumen
				Temperature (Nom)	Rendering Index (Nom)	Maintenance 10000 h (Nom)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Nom)
392266	F15T8/PLANT/18 6PK	7	Plant and Aquarium (PLANT)	-	-	-	-	-
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	830	Soft White	3000 K	83	-	93 %	88 %
392290	F15T8/NATURALSUNSHINE 6/1	950	Natural Sunshine (NS)	5000 K	97	-	90 %	82 %

### Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux (Nom)
392266	F15T8/PLANT/18 6PK	410 lm
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	830 lm

Order Code	Full Product Name	Luminous Flux (Nom)
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	990 lm
392290	F15T8/NATURALSUNSHINE 6/1	750 lm

### Controls and Dimming

Order Code	Full Product Name	Dimmable
392266	F15T8/PLANT/18 6PK	-
392076	F15T8/COOL WHITE PLUS/18 ALTO 6PK	Yes

Order Code	Full Product Name	Dimmable
392126	F15T8 BRIGHT WHITE/18 ALTO 6PK	Yes
392290	F15T8/NATURALSUNSHINE 6/1	Yes

