



Double Ended Linear

Double Ended Linear

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright,white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs.High lumen output provides light where you need it.

Benefits

- Provides high lumen output.
- Available in several lengths to meet specific applications.


Features

- Bright, white light.
- Available in wide range of wattages.
- Recessed Single Contact (RSC).
- Available in 100,150, 250, 300, and 500 watts.

Application

- Ideal for work lights, torchieres, sconces, outdoor security fixtures.

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
BC300T3Q/CL/TP 120V 6/2PK	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
BC500T3Q/CL/2CD/TP	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
PLUS PRO S 500W R7s 120V 1CT/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

Double Ended Linear

General Information	
Cap-Base	R7S
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	120 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3

General Information

Order Code	Full Product Name	Operating Position
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	UNIVERSAL
924735334596	BC500T3Q/CL/2CD/TP	UNIVERSAL
924884936301	BC300T3Q/CL/TP 120V 6/2PK	P4

Light Technical

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	19.0 lm/W	9,500 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
924735334596	BC500T3Q/CL/2CD/TP	19.0 lm/W	9,500 lm
924884936301	BC300T3Q/CL/TP 120V 6/2PK	16 lm/W	5,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
924735334593	PLUS PRO S 500W R7s 120V 1CT/12	4.17 A	500 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
924735334596	BC500T3Q/CL/2CD/TP	4.17 A	500 W
924884936301	BC300T3Q/CL/TP 120V 6/2PK	2.5 A	300 W

