



Crisp white light

Plusline Large (double ended)

PlusLine Large flood delivers maximum light output to light up large areas like outdoor, buildings and shops.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime


Features

- Superior quality of light with excellent color rendering (Ra=100)
- Lifetime: 2000 hours

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums.
Decorative outdoor: billboards, exhibitions and parking areas

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline L 1000W R7s 240V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline L 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

Plusline Large (double ended)

General Information	
Cap-Base	R7s
Rated Lifetime (Hours)	2,000 hour(s)
Switching Cycle	8,000
Nominal lifetime	2,000 hour(s)
Operating Position	P4
Light Technical	
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Warm-up time to 60% light	instant full light s
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932143203	Plusline L 1000W R7s 230V 1CT/10	21.5 lm/W	21,500 lm
923932145703	Plusline L 1000W R7s 240V 1CT/10	21.5 lm/W	21,500 lm
923932243203	Plusline L 1500W R7s 230V 1CT/10	22 lm/W	33,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
923932143203	Plusline L 1000W R7s 230V 1CT/10	4.35 A	230 V	1,000 W
923932145703	Plusline L 1000W R7s 240V 1CT/10	4.17 A	240 V	1,000.0 W

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
923932243203	Plusline L 1500W R7s 230V 1CT/10	6.52 A	230 V	1,500.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932143203	Plusline L 1000W R7s 230V 1CT/10	1000 kWh
923932145703	Plusline L 1000W R7s 240V 1CT/10	1000 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932243203	Plusline L 1500W R7s 230V 1CT/10	1500 kWh

