



# Brighten your home with infinite possibilities

## DuraMax Deco Bent Tip

Philips DuraMax® Long Life Decorative bent tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative bent tip bulbs are available in a variety of wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

### Benefits

- Philips DuraMax long life decorative bent tip light bulbs last longer than standard incandescent, significantly reducing the hassle of replacing light bulbs that burn out too quickly.
- Philips DuraMax decorative bent tip bulbs add a pleasant touch to home décor.

### Features

- Lasts at Least OneYear!\*
- Available in a variety of wattages.
- Frosted light bulbs provide soft white light.
- Clear light bulbs provide decorative sparkle.
- Candelabra base.
- Available in 15 watt clear and 25, 40, and 60 watt clear and frost.
- \*Based on an average of hours usage per day/7 days per week. Hours differ between products, and there are exceptions. See individual products for detail

### Application

- Ideal for general or ambient lighting in wall sconces, chandeliers, and other decorative light fixtures.

# DuraMax Deco Bent Tip

## Versions





E26, BA9 1/2, Clear



E12, BA9, Clear

## Dimensional drawing



Product
---------

BC40BA9-1/2/CL/LL 120V 6/4
----------------------------

Product
---------

BC25BA9C/CL/LL 6/4
--------------------

BC40BA9C/CL/LL 6/4
--------------------

Operating and electrical	
Voltage (Nom)	120 V
General information	
Main Application	Decorative
Operating Position	Base Down +/- 90 D
Rated Lifetime (Hours)	2000 h
Mechanical and housing	
Bulb Finish	Clear

# DuraMax Deco Bent Tip

## Operating and electrical

Order Code	Full Product Name	Power (Nom)
167601	BC40BA9-1/2/CL/LL 120V 6/4	40 W
167197	BC25BA9C/CL/LL 6/4	25 W

Order Code	Full Product Name	Power (Nom)
167205	BC40BA9C/CL/LL 6/4	40 W

## General information

Order Code	Full Product Name	Cap-Base
167601	BC40BA9-1/2/CL/LL 120V 6/4	E26
167197	BC25BA9C/CL/LL 6/4	E12

Order Code	Full Product Name	Cap-Base
167205	BC40BA9C/CL/LL 6/4	E12

## Light technical

Order Code	Full Product Name	Luminous Flux (Nom)
167601	BC40BA9-1/2/CL/LL 120V 6/4	300 lm
167197	BC25BA9C/CL/LL 6/4	150 lm

Order Code	Full Product Name	Luminous Flux (Nom)
167205	BC40BA9C/CL/LL 6/4	300 lm

## Mechanical and housing

Order Code	Full Product Name	Bulb Shape
167601	BC40BA9-1/2/CL/LL 120V 6/4	BA-9 1/2
167197	BC25BA9C/CL/LL 6/4	BA9

Order Code	Full Product Name	Bulb Shape
167205	BC40BA9C/CL/LL 6/4	BA9

