



Brighten your home with infinite possibilities

DuraMax Deco Blunt Tip

Philips DuraMax® Long Life Decorative blunt tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative blunt tip bulbs are available in a variety of shapes, sizes and wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

Benefits

Features

Application

DuraMax Deco Blunt Tip

Versions




E26, B13, Clear



E12, B10 1/2, Clear

Dimensional drawing



Product

BC25B10-1/2C/CL/LL 120V 6/2TP

BC60B10-1/2C/CL/LL 120V 6/2TP

BC40B10-1/2C/CL/LL 120V 6/2TP

Product

BC40B13/CL/LL 120V 6/2 TP

Operating and Electrical

Voltage (Nom) 120 V

General Information

Main Application Decorative

Operating Position Base Down +/-
90 D

Rated Lifetime (Hours) 2000 h

Mechanical and Housing

Bulb Finish Clear

DuraMax Deco Blunt Tip

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
168286	BC40B13/CL/LL 120V 6/2 TP	40 W
168245	BC25B10-1/2C/CL/LL 120V 6/2TP	25 W

Order Code	Full Product Name	Power (Rated) (Nom)
168252	BC40B10-1/2C/CL/LL 120V 6/2TP	40 W
168260	BC60B10-1/2C/CL/LL 120V 6/2TP	60 W

General Information

Order Code	Full Product Name	Cap-Base
168286	BC40B13/CL/LL 120V 6/2 TP	E26
168245	BC25B10-1/2C/CL/LL 120V 6/2TP	E12

Order Code	Full Product Name	Cap-Base
168252	BC40B10-1/2C/CL/LL 120V 6/2TP	E12
168260	BC60B10-1/2C/CL/LL 120V 6/2TP	E12

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
168286	BC40B13/CL/LL 120V 6/2 TP	300 lm
168245	BC25B10-1/2C/CL/LL 120V 6/2TP	150 lm

Order Code	Full Product Name	Luminous Flux (Nom)
168252	BC40B10-1/2C/CL/LL 120V 6/2TP	300 lm
168260	BC60B10-1/2C/CL/LL 120V 6/2TP	550 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
168286	BC40B13/CL/LL 120V 6/2 TP	B13
168245	BC25B10-1/2C/CL/LL 120V 6/2TP	B-10 1/2

Order Code	Full Product Name	Bulb Shape
168252	BC40B10-1/2C/CL/LL 120V 6/2TP	B-10 1/2
168260	BC60B10-1/2C/CL/LL 120V 6/2TP	B-10 1/2

