



# Product Description

## Standard Candle B35 clear

Flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with E-base

### Benefits

- At their best in decorative glass chandeliers and wall brackets with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

### Features

- Slender, crystal-clear lamps designed for sparkling highlights
- Creates a classic sparkling atmosphere

### Application



- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 clear

Versions



Dimensional drawing



Product	D	C (max)
Stan 25W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm
Stan 40W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm
Stan 60W E14 230V B35 CL 1CT/10X10F	35 mm	100 mm

Product	D	C (max)
Stan 40W E27 230V B35 CL 1CT/10X10F	35 mm	96.5 mm

# Standard Candle B35 clear

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35

## General Information

Order Code	Full Product Name	Cap-Base
01160250	STAN 25W E14 230V B35 CL 1CT/10X10F	E14
01167150	STAN 60W E14 230V B35 CL 1CT/10X10F	E14
01163350	STAN 40W E14 230V B35 CL 1CT/10X10F	E14
05669650	STAN 40W E27 230V B35 CL 1CT/10X10F	E27

## Light Technical

Order Code	Full Product Name	Luminous Flux
01160250	STAN 25W E14 230V B35 CL 1CT/10X10F	215 lm
01167150	STAN 60W E14 230V B35 CL 1CT/10X10F	670 lm

Order Code	Full Product Name	Luminous Flux
01163350	STAN 40W E14 230V B35 CL 1CT/10X10F	410 lm
05669650	STAN 40W E27 230V B35 CL 1CT/10X10F	390 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
01160250	STAN 25W E14 230V B35 CL 1CT/10X10F	25 W
01167150	STAN 60W E14 230V B35 CL 1CT/10X10F	60 W

Order Code	Full Product Name	Power Consumption
01163350	STAN 40W E14 230V B35 CL 1CT/10X10F	40 W
05669650	STAN 40W E27 230V B35 CL 1CT/10X10F	40 W

