



# **Product Description**

## Standard Candle B35 frosted

Flame-shaped bulb with inside-frosted glass and vacuum- or gas-filled bulb with Bor E-base

#### **Benefits**

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

#### **Features**

- · Slender, frosted lamps
- $\cdot$  Creates a low glare atmosphere

#### **Application**

- $\boldsymbol{\cdot}$  Home use in living and dining rooms, bedrooms, halls and studies
- $\boldsymbol{\cdot}$  Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- · Clubs and social areas
- Ballrooms
- · Shops and boutiques
- Churches

## **Standard Candle B35 frosted**


### Versions






LPPR ICANBSTD B22 B35 CL

## Dimensional drawing







Product	D	C (max)
Stan 40W E14 230V B35 FR U 1CT/6X50CT	35 mm	100 mm

## **Standard Candle B35 frosted**

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35

#### **General Information**

Order Code	Full Product Name	Cap-Base
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	E14
921485644299	230V 25W BC PEARL CANDLE	B22

#### **Light Technical**

Order Code	Full Product Name	Luminous Flux
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	410 lm

Order Code	Full Product Name	Luminous Flux
921485644299	230V 25W BC PEARL CANDLE	205 lm

#### Operating and Electrical

Order Code	Full Product Name	Power Consumption
926000205011	Stan 40W E14 230V B35 FR U 1CT/6X50CT	40 W

Order Code	Full Product Name	Power Consumption
921485644299	230V 25W BC PEARL CANDLE	25 W



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.